



Save Money



Save Time



Peace of Mind

OHB, the most versatile LED High Bay in the industry, is designed for a wide variety of segments and applications while delivering the lowest total cost of ownership with industry leading performance and reliability to customers. The OHB is an energy-efficient one-for-one replacement of linear fluorescent and HID fixtures and is the ideal high bay fixture for use in industrial, manufacturing, warehousing, and retail applications.

An integrated Wavelinx and Wavelinx Lite wireless sensor is also available for deploying a sensor network that not only meets code requirements but creates a foundation for IoT value-added applications.




LM79 / LM80
Compliant



OHB LED Optimized High Bay

Metalux



Features		Benefits	Result
Construction	Available in 2ft and 4ft lengths	Design flexibility	✓
	Diffused lens	Added protection and optical control	✓
	Rigid, steel center channel and mechanically attached end caps	Added strength and durability	✓
	Compact, scalable platform	Easy to install in any space	⌚
Performance	DLC Standard and Premium level efficacy up to 210 lumens per watt	Significant energy savings	💰
	Precision designed optical performance	Optimal light distribution for intended space	✓
	Integrated Wavelinx and Wavelinx Lite sensor available	Wireless, code-compliant, cost-effective	💰 ⌚
	5-year warranty	Guaranteed quality	✓

High Efficacy versions also available

Energy and Performance Data (Standard Efficacy)

OHB - SE 5000K 80CRI											
Catalog Number	Lumen Output					Watts 277V	Efficacy (LPW)				
	N	MFL	MCL	W	NL		N	MFL	MCL	W	NL
OHB-9SE	8801	8660	8873	8819	8801	54	163	160	164	163	163
OHB-12SE	12221	12025	12321	12246	12852	76	161	158	162	161	169
OHB-15SE	15141	14899	15266	15173	15924	97	156	154	158	157	165
OHB-18SE	18940	18637	19096	18979	19919	111	171	168	172	171	180
OHB-24SE	24453	24062	24655	24504	25717	148	165	163	167	166	174
OHB-30SE	30482	29994	30733	30545	32057	181	169	166	170	169	177
OHB-36SE	36788	36200	37092	36865	38690	226	163	160	164	163	171

N=Narrow Distribution, MFL=Medium Distribution, Frosted Lens, MCL=Medium Distribution, Clear Lens, W=Wide Distribution, NL=No Lens

OHBL SE - 5000K 80CRI									
Catalog Number	Lumen Output				Watts 277V	Efficacy (LPW)			
	N	MFL	MCL	W		N	MFL	MCL	W
OHBL-12SE	12428	12229	12530	12454	70	177	174	178	177
OHBL-15SE	15346	15101	15473	15378	87	176	173	178	177
OHBL-18SE	18487	18191	18639	18525	105	175	173	177	176
OHBL-24SE	24442	24051	24644	24493	138	178	175	179	178
OHBL-30SE	30424	29937	30675	30487	174	175	172	177	175
OHBL-36SE	35190	34627	35481	35263	211	167	164	168	167
OHBL-48SE	49110	48324	49515	49212	299	164	162	166	165
OHBL-60SE	60473	59506	60973	60599	359	169	166	170	169
OHBL-72SE	74006	72822	74617	74160	415	178	175	180	179
OHBL-90SE	91248	89788	92001	91438	530	172	169	174	173
OHBL-100SE	99513	97921	100335	99720	592	168	165	169	168



N=Narrow Distribution, MFL=Medium Distribution, Frosted Lens, MCL=Medium Distribution, Clear Lens, W=Wide Distribution



Cooper Lighting Solutions
 1121 Highway 74 South
 Peachtree City, GA 30269
 P: 770-486-4800
 www.cooperlighting.com

Canada Sales
 5925 McLaughlin Road
 Mississauga, Ontario L5R 1B8
 P: 905-501-3000
 F: 905-501-3172

© 2022 Cooper Lighting Solutions
 All Rights Reserved
 Printed in USA
 Publication No. SA507012EN
 September 21, 2022 5:40 PM