



Save Money



Save Time



Peace of Mind

The ST LED strip features 0-10V dimming and CCT selectable options in stock. Use the ST to replace fluorescent strip lights for increased energy savings and rebates. The ST comes with a continuous row mount aligner, tool-less channel cover, universal voltage driver, 3500, 4000 or 5000K selectable CCT options and a five year warranty.



ST Linear LED Strip

0-10V Dimming / CCT Select

Metalux



	Features	Benefits	Result
Construction	Full length and standard width channel design	No painting required. Ideal for any retrofit LFL project	✓
	Tool-less channel cover, integrated LEDs and wireless access from below	Simple install and maintenance for life of product	⌚
	Surface, chain or toggle mount	Ideal for new construction or retrofit	⌚
	Continuous row mount aligner included	Add-on length as needed regardless of application or layout	💰
Performance	0-10V Dimming, 4000K, Double lens	Additional savings and control; DLC Utility Rebate qualified	💰
	Up to 118 lm/W	Save over 40% energy over existing LFL strips	💰
	Classic single or double lens tube appearance	One for one replacement of 2 or 4-lamp LFL strips	✓
	DLC®, 5-year warranty, 50K life hours at L70	Certified and guaranteed performance	⌚

Replace conventional lamp technology



- ✗ No dimming
- ✗ 20k hours avg lamp life
- ✗ Mercury content

Traditional lamp-base	Energy	LED Integrated	Energy Savings
T12 2600 lm	80W 5200 lm	LED 41W	48%
T8 3100 lm	64W 6200 lm	LED 40W	38%
T5 2900 lm	56W 5800 lm	LED 40W	29%

LED Energy Savings – Long life



- ✓ 0-10V dimming
- ✓ L70@50K (TM-21), over 23 years
- ✓ No Mercury content
- ✓ Optional Emergency Battery

Ordering Information and Performance Data

Catalog Number	UPC	CCT (K)	Min. CRI	Delivered lumens*	Watts*	Efficacy (lm/W)*	Controls	Input current (A)	
								120V	277V
2ST2L2040	080083150960	4000K	80	2228	19	117	0-10V Dimming	0.165	0.075
4ST2L4040	080083150984	4000K	80	4642	40	116	0-10V Dimming	0.34	0.15
8ST2L8040	080083151004	4000K	80	9007	78	115	0-10V Dimming	0.65	0.29
2ST2L20SC3	080083241569	3500K	80	2233	19	117	0-10V Dimming	0.165	0.075
		4000K		2320		122			
		5000K		2258		119			
4ST2L40SC3	080083241583	3500K	80	4607	40	115	0-10V Dimming	0.34	0.15
		4000K		4760		119			
		5000K		4653		116			
8ST2L80SC3	080083242207	3500K	80	8970	78	115	0-10V Dimming	0.65	0.29
		4000K		9275		119			
		5000K		9060		116			

* For 120V



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2022 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. SA51931922
April 28, 2022 1:54 PM