

HALO[®]

Remodel Solutions

Go Faster!

IMPROVED
HALO Canless EZ-Trim

(1) Downlight | (1) Lamp*



LOWER
INSTALLED COST**

* Sold by others.

** Less installation steps = less labor cost.



TRADITIONAL
HALO Remodel Housing

(1) Downlight | (1) Trim | (1) Lamp*



SAME
HEIGHT

SAME
GREAT
LOOK

Top 3 Reasons to Buy Canless EZ-Trim

1

FASTER
INSTALLATION

Less Steps
to Install



2


FEWER
COMPONENTS

Easier Ordering
Less Boxes

3

COMPLETE
SELECTION

3, 4, 6-inch and
shallow options



Canless EZ-Trim Series



CEZ3125GU10WBCAT

3-inch, shallow
GU10 lamp



CEZ4125GU10WBCAT

4-inch, shallow
GU10 lamp



CEZ6126GU24WBCAT

6-inch, shallow
GU24 lamp



CEZ6125GU24WBCAT

6-inch
GU24 lamp



CEZ4125E26WBCAT

4-inch, shallow
E26 lamp



CEZ6126E26WBCAT

6-inch, shallow
E26 lamp



CEZ6125E26WBCAT

6-inch
E26 lamp



Scan Here to
Learn More!



Designer Lens Overlays (compatible with CEZ6 6" fixtures only)

Wet location rated lens, perfect for bathrooms and soffits



CEZ6125LTRMWHWB



CEZ6125LTRMWHBB



CEZ6125LTRMBKBB



CEZ6125LTRMSN



CEZ6125LTRMTBZ

Product Features

- Durable metal baffle trim with attached j-box
- No housing required for installation
- Compatible with LED GU10, GU24 or E26 lamps
- Maximum lamp wattage: 15W
- IC rated, for direct contact with insulation
- Spring clips firmly secure fixture in ceiling

Traditional Housing Features Minus the Housing

- Air-Tite** pre-installed gasket
- Quick Connect** pre-installed push-in wiring connectors
- Slide-N-Side** pre-installed tool-less strain reliefs eliminate need for additional non-metallic cable connectors

