

Panels

Troffers

Good

Better

Best

Click on products to learn more



		Backlit CGT	Backlit CGTS ²	Edgelit FP	Edgelit FPS	Backlit CGTX	Edgelit FPX	CGSB
APPLICABILITY	Education	★★★	★★★	★★★	★★★	★★★	★★★	★★★
	Office	★★	★★	★★	★★★	★★★	★★★	★★
	Healthcare	★	★★	★	★	★★	★★	★★★
	Retail	★★	★★	★★★	★★★	★★★	★★★	★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
	Im/W (Max)	115	159	136	120	137	130	140
	Lum (Max)	5,300	6,900	7,000	6,500	10,000	6,400	9,300
	Life (@60K)	L84	L86	L86	L87	L88	L87	L86
	Lens	Frost, Smooth	Frost, Smooth	Frost, Smooth	Frost, Smooth	Frost - Smooth, Prismatic	Frost, Smooth	Frost, Smooth
	Service from Below	No	No	No	No	No	No	Yes
	Emergency	Remote	Remote	Remote	Remote	Integrated	Integrated	Integrated
	CRI	80+	80+	80+ / 90+	80+	80+ / 90+	80+	80+ / 90
	Sensor Location	Tile Mount	Tile Mount	Tile Mount	Tile Mount	Integrated	Integrated	Integrated
	DLC	Standard	Standard	Standard	Standard	Premium	Premium	Standard
	Door	No - see CGSB Panel	No - see CGSB Panel	No - see CGSB Panel	No - see CGSB Panel	No - see CGSB Panel	No - see CGSB Panel	Yes
	Air Venting	No	No	No	No	No	No	No
	Lumen / CCT Select	No	Yes	No	Yes	No	No	No
VividTune™	No	No	No	No	No	No	No	
INTEGRATED CONTROLS	WaveLinX Lite					✓	✓	✓
	WaveLinX Pro					✓	✓	✓
	DLVP					✓	✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable. 2. CGTS-NUV also available (Canadian market only).

Click on products to learn more



		Center Basket CBRK	Flat Lens GR	Center Basket Achieva ARS	Center Basket Cruze CZS	Cruze ST	Cruze SB	RLN	Ovation	Accord	SkyRidge	Encounter
APPLICABILITY	Education	★★★	★★★	★★★	★★★	★★★	★★★	★★	★★	★	★	★★
	Office	★★	★★	★★	★★★	★★★	★★	★★★	★★★	★★★	★★★	★★★
	Healthcare	★	★★	★★	★★	★★	★★★	★★	★	★★	★★	★★★
	Retail	★	★★	★★	★★★	★★★	★★	★★	★★★	★★	★★	★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4, Metric
	Im/W (Max)	168	140	146	156	157	157	139	109	127	150	141
	Lumens (Max)	4,700	18,000	8,000	6,500	17,000	7,500	8,000	5,000	7,300	6,400	7,400
	Life (@60K)	L85	L89	L90	L90	L90	L84	L93	L89	L89	L89	L92
	Lens	Frost, Ribbed	Frost, Prismatic	Round, Ribbed	Round or Square, Frost - Ribbed or Smooth, Perf Inlays	Round or Square, Frost - Ribbed or Smooth, Perf Inlays	Round, Frost - Ribbed or Smooth	Frosted Acrylic	Metal Perforated	Frosted Acrylic	Acrylic (WaveStream)	Acrylic (WaveStream)
	Service from Below	Yes	Yes	No	No	No	Yes	Yes	No	Yes	No	No
	Emergency	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80+	80+	80+	80+ / 90	80+ / 90	80+ / 90	80+	80+	80+	80+
	Sensor Location	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Tile Mount	Integrated	Integrated	Integrated
	DLC	Premium	Standard / Premium	Standard / Premium	Standard / Premium	Standard / Premium	Premium	Premium	Standard	Premium	Premium	Premium
	Door	No	Yes	No - see Cruze SB	No - see Cruze SB	No - see Cruze SB	Yes	No	No	No	No	No
	Air Venting	Yes	No	No	Yes	Yes	No	No	Yes	Yes	Yes	Yes
	Lumen / CCT Select	Yes	Yes	Yes	Yes	Yes	No	Yes	No	No	No	Yes
VividTune™	No	Tunable White	No	No	Tunable White	Tunable White	Tunable White	No	No	No	Tunable White	
INTEGRATED CONTROLS	WaveLinX Lite	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	WaveLinX Pro	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	DLVP	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable