



	HU11	HU30M
Lumens/ft	380	300
CRI/CCT	90 CRI, 3-Color SeleCCTable (2700K, 3000K, 4000K)	90 CRI, 5-Color SeleCCTable (2700K, 3000K, 3500K, 4000K, 5000K)
Dim-To-Warm(@ 120V)	No	Yes (D2W 2700K-1800K)
Dimmable (@ 120V)	ELV down to 5%	ELV down to 5%
Thickness	0.9"	0.75"
Available Lengths	9", 18", 24", 36", 48"	9", 18", 24", 36", 48"
Linkable	Yes	Yes
Direct Wire	Yes	Yes
Plug-In Cord Available	Yes	Yes
Finishes	Matte Black, White	Matte Black, White
Dry/Wet/Damp Rating	Damp	Damp
Energy Compliance	ENERGY STAR®, T24(JA8)	ENERGY STAR®, T24(JA8)
Voltage	120V	120V - 277V (UNV)
Motion Sensor/USB accessory	No	Yes
Compatible with existing Connectors	Yes	Yes
Specialized low glare optics	No	Yes