

Note: HC6 and PD6 ARE NOT Interchangeable

PD6 Series Stock / Popular	NEW HC6 Series Equivalent Cross		
PD6 Catalog No.	HC6 Catalog No.	HC6 Description	Notes
61VC	61NDC / 61MDC / 61WDC	6" Narrow / Medium / Wide Reflector Specular Clear	HC6 - Narrow/ Medium / Wide beam options
61VCWF	61NDCWF / 61MDCWF / 61WDCWF	6" Narrow / Medium / Wide Reflector Specular Clear, White Flange	HC6 - Narrow/ Medium / Wide beam options
61VEMC	61NDCIEM / 61MDCIEM / 61WDCIEM	6" Narrow / Medium / Wide Reflector Specular Clear IEM	HC6 - Narrow/ Medium / Wide beam options
61VEMCWF	61NDCWFIEM / 61MDCWFIEM / 61WDCWFIEM	6" Narrow / Medium / Wide Reflector Specular Clear, White Flange IEM	HC6 - Narrow/ Medium / Wide beam options
61VEMH	61NDHIEM / 61MDHIEM / 61WDHIEM	6" Narrow / Medium / Wide Reflector Semi Specular IEM	HC6 - Narrow/ Medium / Wide beam options
61VEMHWF	61NDHWFIEM / 61MDHWFIEM / 61WDHWFIEM	6" Narrow / Medium / Wide Reflector Semi Specular, White Flange IEM	HC6 - Narrow/ Medium / Wide beam options
61VEMW	61NDWIEM / 61MDWIEM / 61WDWIEM	6" Narrow / Medium / Wide Reflector Matte White IEM	HC6 - Narrow/ Medium / Wide beam options
61VEMWB	61WDWBIEM	6" Wide Reflector White Baffle IEM	HC6 - Baffle is wide beam
61VH	61NDH / 61MDH / 61WDH	6" Narrow / Medium / Wide Reflector Semi Specular	HC6 - Narrow/ Medium / Wide beam options
61VHWF	61NDHWF / 61MDHWF / 61WDHWF	6" Narrow / Medium / Wide Reflector Semi Specular, White Flange	HC6 - Narrow/ Medium / Wide beam options
61VW	61NDW / 61MDW / 61WDW	6" Narrow / Medium / Wide Reflector Matte White	HC6 - Narrow/ Medium / Wide beam options
61VWB	61WDWB	6" Wide Reflector White Baffle	HC6 - Baffle is wide beam
61VEMBB	61WDDBIEM	6" Wide Reflector Black Baffle IEM	HC6 - Baffle is wide beam
61VBB	61WDDB	6" Wide Reflector Black Baffle	HC6 - Baffle is wide beam
61WWC	61RWWC	6" Lens Wall Wash Reflector Specular Clear	HC6 - Rotatable Lensed Wall Wash
61WWCWF	61RWWCWF	6" Lens Wall Wash Reflector Specular Clear, White Flange	HC6 - Rotatable Lensed Wall Wash
61WWH	61RWWH	6" Lens Wall Wash Reflector Semi Specular	HC6 - Rotatable Lensed Wall Wash
61WWHWF	61RWWHWF	6" Lens Wall Wash Reflector Semi Specular, White Flange	HC6 - Rotatable Lensed Wall Wash
61WWW	61RWWW	6" Lens Wall Wash Reflector Matte White	HC6 - Rotatable Lensed Wall Wash
PD56R10D010B	HC56R10D010	HC56 Retrofit Housing 1000lm, UNV, 0-10V	
PD56R10ED010	HC56R10D010*	HC56 Retrofit Housing 1000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD56R15D010B	HC56R15D010	HC56 Retrofit Housing 1500lm, UNV, 0-10V	

PD6 Series Stock / Popular	NEW HC6 Series Equivalent Cross		
PD6 Catalog No.	HC6 Catalog No.	HC6 Description	Notes
PD56R20D010B	HC56R20D010	HC56 Retrofit Housing 2000lm, UNV, 0-10V	
PD56R20ED010	HC56R20D010*	HC56 Retrofit Housing 2000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD56R30D010	HC56R30D010	HC56 Retrofit Housing 3000lm, UNV, 0-10V	
PD610D010B	HC610D010	6" 1000lm, UNV, 0-10V	
PD610ED010	HC610D010*	6" 1000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD615D010B	HC615D010	6" 1500lm, UNV, 0-10V	
PD615ED010	HC615D010*	6" 1500lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD618ED010	HC620D010*	6" 2000lm, UNV, 0-10V	*Use 2000lm for PD6 1800lm
PD620D010B	HC620D010	6" 2000lm, UNV, 0-10V	
PD620ED010	HC620D010*	6" 2000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD630D010B	HC630D010	6" 3000lm, UNV, 0-10V	
PD630D010	HC630D010*	6" 3000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD6R10D010B	HC6R10D010	HC6 Retrofit Housing 1000lm, UNV, 0-10V	
PD6R10ED010	HC6R10D010*	HC6 Retrofit Housing 1000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD6R15D010B	HC6R15D010	HC6 Retrofit Housing 1500lm, UNV, 0-10V	
PD6R15ED010	HC6R15D010*	HC6 Retrofit Housing 1500lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD6R20D010B	HC6R20D010	HC6 Retrofit Housing 2000lm, UNV, 0-10V	
PD6R20ED010	HC6R20D010*	HC6 Retrofit Housing 2000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD6R30D010B	HC6R30D010	HC6 Retrofit Housing 3000lm, UNV, 0-10V	
PD6R30D010	HC6R30D010*	HC6 Retrofit Housing 3000lm, UNV, 0-10V	*HC6 cross PD6 Gen-A for 0-10V dimming only
PD6RX10D010B	HC6R10D010*	HC6 Retrofit Housing 1000lm, UNV, 0-10V	* use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide
PD6RX15D010B	HC6R15D010*	HC6 Retrofit Housing 1500lm, UNV, 0-10V	* use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide
PD6RX20D010B	HC6R20D010*	HC6 Retrofit Housing 2000lm, UNV, 0-10V	* use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide
PD6RX30D010B	HC6R30D010*	HC6 Retrofit Housing 3000lm, UNV, 0-10V	* use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide

HALO Commercial

New HC6 / PD6 Equivalent Crossover

PD6 Series Stock / Popular	NEW HC6 Series Equivalent Cross		
PD6 Catalog No.	HC6 Catalog No.	HC6 Description	Notes
PDM6A827	HM612827 / HM634827	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 2700K	HC6 -LED module - determined by housing lumens
PDM6A830	HM612830 / HM634830	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3000K	HC6 -LED module - determined by housing lumens
PDM6A835	HM612835 / HM634835	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3500K	HC6 -LED module - determined by housing lumens
PDM6A840	HM612840 / HM634840	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 4000K	HC6 -LED module - determined by housing lumens
PDM6A927	HM612927 / HM634927	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 2700K	HC6 -LED module - determined by housing lumens
PDM6A930	HM612930 / HM634930	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3000K	HC6 -LED module - determined by housing lumens
PDM6930	HM612930 / HM634930	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3000K	HC6 -LED module - determined by housing lumens
PDM6935	HM612935 / HM634935	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3500K	HC6 -LED module - determined by housing lumens
PDM6A935	HM612935 / HM634935	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3500K	HC6 -LED module - determined by housing lumens
PDM6A940	HM612940 / HM634940	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 4000K	HC6 -LED module - determined by housing lumens
PDM6B827	HM612827 / HM634827	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 2700K	HC6 -LED module - determined by housing lumens
PDM6B830	HM612830 / HM634830	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3000K	HC6 -LED module - determined by housing lumens
PDM6B835	HM612835 / HM634835	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3500K	HC6 -LED module - determined by housing lumens
PDM6B840	HM612840 / HM634840	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 4000K	HC6 -LED module - determined by housing lumens
PDM6B927	HM612927 / HM634927	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 2700K	HC6 -LED module - determined by housing lumens
PDM6B930	HM612930 / HM634930	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3000K	HC6 -LED module - determined by housing lumens
PDM6B935	HM612935 / HM634935	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3500K	HC6 -LED module - determined by housing lumens
PDM6B940	HM612940 / HM634940	6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 4000K	HC6 -LED module - determined by housing lumens
64VC - shallow trim	N/A		HC6 - use 1000-1500-2000lm module for shallow applications
64VCWF - shallow trim	N/A		HC6 - use 1000-1500-2000lm module for shallow applications
64VDFW - shallow trim	N/A		HC6 - use 1000-1500-2000lm module for shallow applications
64VH - shallow trim	N/A		HC6 - use 1000-1500-2000lm module for shallow applications
64VHWF - shallow trim	N/A		HC6 - use 1000-1500-2000lm module for shallow applications
64VW - shallow trim	N/A		HC6 - use 1000-1500-2000lm module for shallow applications