



Cruze ST and Cruze CZS Selectable are specification center basket LED troffer series that deliver architectural features with unmatched value. These high quality luminaires deliver superior aesthetics, optical distribution, and energy efficiency. This center basket series delivers the features needed for use in premier office spaces, primary and secondary schools, and retail merchandising. The Cruze ST is perfect for specification applications where varying light levels and foot-candle requirements drive the need for a variety high and low lumen packages and where color is specified. The CZS offers design flexibility with selectable lumen output and color temperature with simple, easy to access toggle switches to enable worksite adaptability and reduction of rack space for distributors by taking 9 skus into 1 sku.

Quick install

Aesthetic appeal


















Selectable Lumens and CCT

Room side access

Click on products to learn more











		CBRK	Cruze ST	CZS Cruze Selectable	Cruze SB
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
	lm/W (Max)	162	157	156	157
	Lum (Max)	4700	17000	6500	7500
	Life (@60K)	L84	L90	L94	L84
	Lens	Frost, Ribbed	Round or Square, Frost - Ribbed or Smooth, Perf Inlays	Round or Square, Frost - Ribbed or Smooth, Perf Inlays	Round, Frost, Ribbed or Smooth
	CRI	80+	80+ / 90	80+	80+ / 90
	Depth	Standard 2.95"	Standard 3.25"	Standard 3.25"	Standard 3.25"
	Driver access	Room-Side	Plenum	Plenum	Room-Side
	Type	Retrofit Kit, Driver Access	Fixture, Standard	Fixture, Standard	Fixture, Driver Access
	Air Venting	Yes	Yes	Yes	None

Features	Benefits
Latchless design with no visible hinges	Improved aesthetic to delight specifiers
Standard matte white paint from corner to corner	Improved aesthetic to delight specifiers
<p>Multiple lens options</p> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Ribbed Frosted Acrylic Lens</p>  <p>Standard</p> </div> <div style="text-align: center;"> <p>Smooth Frosted Acrylic Lens</p>  </div> <div style="text-align: center;"> <p>Round Pattern Insert</p>  </div> <div style="text-align: center;"> <p>Ribbed Square Acrylic Lens</p>  </div> </div>	Various aesthetic options available to delight specifiers
<p>Large J Box with standard access plate and trade size knockouts</p> 	Easier wiring access to delight contractors
Hemmed side flanges	Easier handling during installation to delight contractors
Linear disconnect included	Easier installation to delight contractors
Multiple sizes available (2x2, 2x4 in standard 3.25" depth and 1x4 in shallow 2.25" depth)	Enables fixture matching in spaces
Grid lock feature included in the endplate with available "earthquake clip" accessory	Helps meet building codes
<p>Connected lighting options available (see options)</p> 	<p>Sensing and communication</p> <p>Energy savings</p> <p>Asset tracking</p> <p>Space utilization</p>
<p>Tunable white options available</p> 	<p>Improve productivity, focus, mood</p>
<p>Compliance and approvals</p>          	

# Cruze CZS

## Center Basket LED luminaire with Selectable lumens + CCT

# Metalux

Features	Benefits
Latchless design with no visible hinges	Improved aesthetic to delight specifiers
<b>Multiple lens options</b> Ribbed Frosted Acrylic Lens      Smooth Frosted Acrylic Lens  Standard  Round Pattern Insert  Ribbed Square Acrylic Lens	Various aesthetic options available to delight specifiers Round Pattern Insert      Ribbed Square Acrylic Lens
Large J Box with standard access plate and trade size knockouts 	Easier wiring access to delight contractors Easy to access toggle switches for lumen and color temperature control
Hemmed side flanges	Easier handling during installation to delight contractors
Linear disconnect included	Easier installation to delight contractors
Multiple sizes available (2x2, 2x4 in standard 3.25" depth and 1x4 in shallow 2.25" depth)	Enables fixture matching in spaces
Grid lock feature included in the endplate with available "earthquake clip" accessory	Helps meet building codes
Connected lighting options available (see options) 	Sensing and communication Energy savings Asset tracking Space utilization
<b>Selectable lumens and CCT</b>  <p>Easy to access toggle switches</p>	<b>Flexibility - Multiple light choices, one fixture</b>  <p><b>SELECTABLE COLORS (CCT)</b> Choose from a wide range of color temperatures to set the ideal lighting scene.</p>  <p><b>SELECTABLE LUMENS</b> Select between the preset lumen outputs to create your optimal lighting experience.</p>
<b>Compliance and approvals</b> 