

Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO

CEZ4125

4" Canless EZ-Trim
Lamp-based direct mount
15W Maximum

Typical Applications

- Residential • Light Commercial

Interactive Menu

- Order Information page 2
- Product Specifications page 2
- Product Warranty

Product Certification




Product Features



Top Product Features

- Baffle trim
- Direct mount – does not require recessed housing or junction box
- Option for GU10 or E26 lamp base, use with compatible LED lamps (sold by others)
- Air-tite, for use in insulated and non-insulated ceilings
- Suitable for 2x6 residential framing or shallow plenum commercial construction

Dimensional and Mounting Details



Order Information

SAMPLE ORDER NUMBER: **CEZ4125GU10WBICAT**

A complete luminaire consists of a Canless EZ-Trim lamp-based direct mount and a compatible lamp (sold by others).

Model	Lamp Base	Trim Type	Certifications	Accessories (sold separate)
CEZ4125 = 4-inch Canless EZ-Trim	E26 = E26 base GU10 = GU10 base	WB = White flange, white baffle trim	ICAT = IC rated, air-tite	HL4RSMF = 4" new construction round/square mounting frame
Notes	Notes	Notes	Notes	Notes

Compatible LED Lamps

- MR16 LED, E26 base
- PAR16 LED, E26 base
- MR16 LED, GU10 base
- PAR16 LED, GU10 base
- MR11 LED, GU10 base



Product Specifications

Trim

- Durable metal baffle trim

Lamp Compatibility

- For use with maximum 15W LED lamps
- Option for GU10 or E26 lamp base
- Compatible with MR16, PAR16, MR11 LED lamps

Installation

- Can be installed in 1/2" to 1-1/4" thick ceilings
- Suitable for 2x6 residential framing or shallow plenum commercial construction
- Heat treated springs hold fixture fitting securely in the ceiling eliminating light leaks
- Can be removed from below the ceiling for service or replacement
- Can be used with Halo new construction mounting frames

Junction Box

- Compact galvanized steel junction box
- Listed for (10) #12 AWG 90° C splice conductors
- Hinged door is retained and provides easy access to field wiring
- (2) 1/2" conduit pry-outs positioned to allow straight conduit runs
- (2) Slide-N-Side™ non-metallic (NM) wire traps allow wiring outside the box
- Accepts 14-2, 14-3, 12-2, 12-3 U.S. and 14-2, 14-3, 12-2 Canadian NM cable
- (3) 4-port push wire nuts with clear caps for quick and reliable mains voltage connections

Compliance

- Type IC thermally protected, suitable for direct contact to air permeable insulation and cULus listed for damp locations
- Not for use in direct contact with spray foam insulation, consult NEMA LSD57-2013
- Air-tite per ASTM-E283
- Can be used for State of California Title 24 high efficacy luminaire compliance with CA JA8-2016-E or JA8-2019-E labeled lamps
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- Contains no mercury or lead and RoHS compliant

Warranty

- One-year limited warranty, consult website for details. www.cooperlighting.com/legal