

# OUTDOOR LED LIGHTING SOLUTIONS

STOCK CATALOG

LUMARK

LUMARK AP



# BUILD BRIGHTER



We make endless possibilities work by providing you with a comprehensive portfolio of outdoor lighting solutions for commercial and industrial spaces. Our products are designed to simplify and personalize lighting for consumers' unique needs. Whether you're planning a retrofit or new construction project, we've got you covered.

To find this catalog online visit [cooperlighting.com/global/outdoor](https://cooperlighting.com/global/outdoor)

## Lumark

Combines value-engineered specification-grade lighting features with market-leading retrofit solutions to enable contractors to get on and off the job quickly and deliver superior illumination coverage.

## Lumark AP

High-value outdoor lighting products that are always in stock and supported with decades of experience and expertise in the industry. Simple. Outdoor. Lighting.

## Product Features & Technologies

Cooper Lighting Solutions is the source for superior quality lighting products in all markets, bringing creativity, insight, and knowledge together to provide the best and the brightest lighting solutions. Below you will find descriptions that detail some of the features and technology icons listed throughout this catalog.

For more information, contact your representative or visit [cooperlighting.com/global](https://cooperlighting.com/global)



### RoHS

All products in this catalog are RoHS Compliant. This Restriction of Hazardous Substances directive ensures there is no use of specific hazardous materials found in electrical and electronic products.



### Warranty

All products in this catalog are covered by a standard 5-year limited warranty (exceptions noted by product). Warranty details can be found on [cooperlighting.com/legal](https://cooperlighting.com/legal).



### UL Certified

All products listed in this catalog have been evaluated, tested, and listed by Underwriters Laboratories for product safety certification in US and Canada.



### IP66 Rated

The products with this notation are tested to be water resistant and also protected against dust, dirt, sand and debris, all while maintaining long luminaire life.



### DLC

These families have SKUs that are DesignLights Consortium® Qualified. Refer to [designlights.org](https://designlights.org) Qualified Products List under Family Models for details.



### DLC Premium

These families have SKUs that are DesignLights Consortium® Premium Qualified. Refer to [designlights.org](https://designlights.org) Qualified Products List under Family Models for details.

Controls Key	
-	No additional integrated controls. Fixture only manually switched ON/OFF
D2D	Dusk-to-dawn operation by way of an integrated (or button-type) photocontrol
3P	Integrated 3-PIN NEMA twistlock photocontrol receptacle (photocontrol sold separately)
3P-PC	Integrated 3-PIN NEMA twistlock photocontrol receptacle (photocontrol included)
M	Motion detection for ON/OFF operation (degrees of detection)
SENS	Integrated, programmable motion and occupancy detection for ON/Dim operation with integrated dusk-to-dawn capability

Product specifications subject to change without notice. Visit [cooperlighting.com/global](https://cooperlighting.com/global) to find the most up to date information.

**Floodlighting**  
4-9

**Wall Mount**  
10-15

**Area / Site**  
16-19

**Parking Garage / Canopy**  
20-23

# Floodlighting

Lumark and Lumark AP provide a variety of outdoor floodlighting for solutions ranging from commercial industrial to residential and light commercial applications, and include features such as precise aiming, rugged construction and long life.



**Lumark**  
Night Harrier



**Lumark**  
Night Falcon



**Lumark**  
Tracer Floodlight



**Lumark AP**  
LSF Selectable  
Flood Series

## Lumark Night Harrier

- Cutting-edge innovated design offering years of maintenance-free service
- 3-color selectable CCT: 3000K, 4000K, 5000K
- Lumen packages ranging from 5,500-22,000 lumens
- Slipfitter and trunnion mounting types
- Ideal for area lighting such as facade, wall washing, building and sign lighting



Large  
NHR100

Medium  
NHR50

**0-10V**  
DIMMING



Model	HID Equivalent	Lumens	Watts	Voltage	Mounting	Controls	UPC
<b>Night Harrier Medium</b>							
NHRS50UT	70W - 500W	5,500 - 22,000	40 - 155W	120 - 277V	Trunnion	-	080083283903
NHRS50US	70W - 500W	5,500 - 22,000	40 - 155W	120 - 277V	Slipfitter	-	080083283910
NHRS50HT	70W - 500W	5,500 - 22,000	40 - 155W	347 - 480V	Trunnion	-	080083283927
NHRS50HS	70W - 500W	5,500 - 22,000	40 - 155W	347 - 480V	Slipfitter	-	080083283934
NHRS50UT-BPC	70W - 500W	5,500 - 22,000	40 - 155W	120 - 277V	Trunnion	D2D	080083283941
NHRS50US-BPC	70W - 500W	5,500 - 22,000	40 - 155W	120 - 277V	Slipfitter	D2D	080083283958
<b>Night Harrier Large</b>							
NHRS100UT	500W - 1000W	23,000 - 43,000	40 - 155W	120 - 277V	Trunnion	-	080083296965
NHRS100US	500W - 1000W	23,000 - 43,000	40 - 155W	120 - 277V	Slipfitter	-	080083296972
NHRS100HT	500W - 1000W	23,000 - 43,000	40 - 155W	347 - 480V	Trunnion	-	080083296989
NHRS100HS	500W - 1000W	23,000 - 43,000	40 - 155W	347 - 480V	Slipfitter	-	080083296996
NHRS100UT-PR	500W - 1000W	23,000 - 43,000	40 - 155W	120 - 277V	Trunnion	-	080083297009
NHRS100US-PR	500W - 1000W	23,000 - 43,000	40 - 155W	120 - 277V	Slipfitter	-	080083297016

## Lumark Night Falcon

- Cost-effective LED floodlight available in 3 sizes
- Precision engineered and high-efficiency optics delivers superior uniformity
- Compact, robust die-cast aluminum housing, driver compartment and door
- 6H x 6V wide distribution and 3H x 3V spot distribution
- Ideal for area lighting for security, building facade and signage



Model	HID Equivalent	Lumens	Watts	Voltage	Mounting	Controls	UPC
<b>Night Falcon Small</b>							
NFFLD-S-C70-KNC-UNV	70W	2,682	20	120-277V	Knuckle	-	080083760282
NFFLD-S-C70-KNC-UNV-PC1	70W	2,682	20	120V	Knuckle	D2D	080083760350
NFFLD-S-C70-KNC-UNV-PC2	70W	2,682	20	207-277V	Knuckle	D2D	080083788194
NFFLD-S-C70-KNC-347	70W	2,682	20	347V	Knuckle	-	080083760367
NFFLD-S-C70-T-UNV	70W	2,682	20	120-277V	Trunnion	-	080083760299
NFFLD-S-C70-T-UNV-PC1	70W	2,682	20	120V	Trunnion	D2D	080083760343
NFFLD-S-C70-T-UNV-PC2	70W	2,682	20	207-277V	Trunnion	D2D	080083788187
NFFLD-S-C70-T-347	70W	2,682	20	347V	Trunnion	-	080083760374
NFFLD-S-C15-KNC-UNV	150W	5,797	51	120-277V	Knuckle	-	080083760268
NFFLD-S-C15-KNC-UNV-PC1	150W	5,797	51	120V	Knuckle	D2D	080083760329
NFFLD-S-C15-KNC-UNV-PC2	150W	5,797	51	207-277V	Knuckle	D2D	080083788170
<b>Night Falcon</b>							
NFFLD-C25-S	250W	10,530	85	120-277V	Slipfitter	-	080083801244
NFFLD-C25-E-UNV-66-S-CB-PER	250W	10,530	85	120-277V	Slipfitter	3P	080083147106
NFFLD-C25-T	250W	10,530	85	120-277V	Trunnion	-	080083801220
NFFLD-C40-S	400W	16,932	128	120-277V	Slipfitter	-	080083801206
NFFLD-C40-E-UNV-66-S-CB-PER	400W	16,932	128	120-277V	Slipfitter	3P	080083813391
NFFLD-C40-T	400W	16,932	128	120-277V	Trunnion	-	080083801183
NFFLD-C40-E-UNV-66-T-CB-PER	400W	16,932	128	120-277V	Trunnion	3P	080083813407
<b>Night Falcon Large</b>							
NFFLD-L-C75-S	750W	25,942	179	120-277V	Slipfitter	-	080083800964
NFFLD-L-C75-T	750W	25,942	179	120-277V	Trunnion	-	080083800988
NFFLD-L-C100-S	1,000W	33,941	252	120-277V	Slipfitter	-	080083800889
NFFLD-L-C100-S-347	1,000W	33,941	252	347V	Slipfitter	-	080083800926
NFFLD-L-C100-T	1,000W	33,941	252	120-277V	Trunnion	-	080083800902
NFFLD-L-C100-T-347	1,000W	33,941	252	347V	Trunnion	-	080083800940
<b>Night Falcon Accessories</b>							
TS2/NFFLD-CB	Top and Side Visor (Medium)						080083736270
VS/NFFLD	Vandal Shield (Medium)						080083747993
WG/NFFLD	Wire Guard (Medium)						080083748006

## Lumark Tracer Floodlight

- Value and Performance in a unique, patent-pending durable design
- The rugged, die-cast housing is IP66 rated for exceptional durability and long-term reliability.
- Adjustable 1/2" NPS knuckle mount
- Delivers superior uniformity and excellent illumination to the targeted application.
- Ideal for applications such as landscape, accent, facade, or sign lighting.



Catalog Number	Non-LED Equivalent	Lumens	Watts	Voltage	Distribution	UPC
<b>Tracer Small</b>						
TCRS5S	50W Halogen	550	5	120-277V	Spot	080083884438
TCRS5M	50W Halogen	550	5	120-277V	Medium	080083884834
TCRS5W	50W Halogen	550	5	120-277V	Wide	080083884933
TCRS8S	70W Halogen	850	8	120-277V	Spot	080083884452
TCRS8M	70W Halogen	850	8	120-277V	Medium	080083884858
TCRS8W	70W Halogen	850	8	120-277V	Wide	080083884957
<b>Tracer Large</b>						
TCRL15S	100W Halogen	1,600	15	120-277V	Spot	080083884773
TCRL15M	100W Halogen	1,600	15	120-277V	Medium	080083884872
TCRL15W	100W Halogen	1,600	15	120-277V	Wide	080083884971
TCRL20S	120W Halogen	2,200	20	120-277V	Spot	080083884797
TCRL20M	120W Halogen	2,200	20	120-277V	Medium	080083884896
TCRL20W	120W Halogen	2,200	20	120-277V	Wide	080083884995
TCRL26S	150W Halogen	2,900	26	120-277V	Spot	080083884810
TCRL26M	150W Halogen	2,900	26	120-277V	Medium	080083884919
TCRL26W	150W Halogen	2,900	26	120-277V	Wide	080083885015



## Lumark AP LSF Selectable Flood Series

- Simple outdoor solution for various floodlight applications
- Selectable CCT & selectable lumens
- 3 housing sizes and multiple lumen packages
- Slipfitter and trunnion mounting types
- Ideal for signs, facades, parking lots, and more



Model	HID Equivalent	Lumens	Watts	Voltage	Mounting	Controls	UPC
LSF25-KN-PC	155W HID	1,700-4,000	11-25W	120-347V	Knuckle	-	080083267705
LSF65-KN-PC	375W HID	5,000-10,000	25-65W	120-347V	Knuckle	-	080083267729
LSF120-SF-PC	450W HID	9,000-20,000	50-120W	120-347V	Slipfitter	-	080083267743
LSF25-YK-PC	155W HID	1,700-4,000	11-25W	120-347V	Yoke	-	080083267767
LSF65-YK-PC	375W HID	5,000-10,000	25-65W	120-347V	Yoke	-	080083267781
LSF120-TR-PC	450W HID	9,000-20,000	50-120W	120-347V	Trunnion	-	080083267804



# Wall Mount

Lumark and Lumark AP wall mounted luminaires can provide unique architectural styling to a building while illuminating the adjacent areas for increased pedestrian safety. These LED products offer a mix of mounting heights, optical distributions, and control options for a variety of lighting applications.



**Lumark Axcent**



**Lumark Crosstour**



**Lumark WP Wal-Pak Glass**



**Lumark Square Glass Wall Packs**



**Lumark AP Traditional Glass Wall Packs**



**Lumark AP ASWP Adjustable Slim Wall Pack**

## Lumark Axcent

- Full cutoff and refractive LED lens models available in small or large
- Hook-N-Lock mechanism for quick, easy installation
- Die-cast aluminum construction with energy-efficient illumination
- Gasketed housing and sealed optical compartment making impervious to contaminants
- Ideal for pathway illumination and floodlighting applications



Refractive lens

Full cutoff

**0-10V**  
DIMMING



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Lens Type	UPC
<b>Axcent Small</b>						
AXCS1A	70W	1,806	14	120-277V	Full Cutoff	080083887965
AXCS1ARL	70W	1,915	14	120-277V	Refractive Lens	080083887972
AXCS2A	100W	2,561	21	120-277V	Full Cutoff	080083887989
AXCS2ARL	100W	2,716	21	120-277V	Refractive Lens	080083887996
AXCS3A	150W	3,537	27	120-277V	Full Cutoff	080083888009
AXCS3ARL	150W	3,704	27	120-277V	Refractive Lens	080083888016
AXCS4A	250W	5,520	44	120-277V	Full Cutoff	080083888023
AXCS4ARL	250W	5,858	44	120-277V	Refractive Lens	080083888030
AXCS5A	320W	6,300	52	120-277V	Full Cutoff	080083888047
AXCS5ARL	320W	6,699	52	120-277V	Refractive Lens	080083888054
<b>Axcent Large</b>						
AXCL6A	320W	7,594	56	120-277V	Full Cutoff	080083811564
AXCL6ARL	320W	7,809	56	120-277V	Refractive Lens	080083811649
AXCL8A	400W	9,696	72	120-277V	Full Cutoff	080083811588
AXCL8ARL	400W	9,970	72	120-277V	Refractive Lens	080083811663
AXCL10A	400W	13,283	102	120-277V	Full Cutoff	080083811601
AXCL10ARL	400W	13,641	102	120-277V	Refractive Lens	080083811687
AXCL12A	450W	16,823	123	120-277V	Full Cutoff	080083811625
AXCL12ARL	450W	17,346	123	120-277V	Refractive Lens	080083811700

## Lumark Crosstour

- Architectural style with super bright, energy-efficient LEDs
- Low-profile, rugged die-cast aluminum construction and stainless steel hardware
- Universal back box with sealed and gasketed optical compartment
- Wall, surface, post, bollard, low-level, inverted, floodlight mounting
- Ideal for multi-use facilities, pathway illumination and building entrances



XTOR / XTOR Maxx



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Finish	Lens Type	UPC
XTOR1B	70W	1,418	12	120-277V	Carbon Bronze	Full Cutoff	080083777969
XTOR2B	100W	2,135	18	120-277V	Carbon Bronze	Full Cutoff	080083778225
XTOR3B	150W	2,751	26	120-277V	Carbon Bronze	Full Cutoff	080083778041
XTOR4B	250W	4,269	38	120-277V	Carbon Bronze	Full Cutoff	080083778003
XTORFLD-KNC	Floodlight Knuckle Accessory Kit				Carbon Bronze	--	080083619115
XTORFLD-TRN	Floodlight Trunnion Accessory Kit				Carbon Bronze	--	080083619153
XTOR6B	320W	6,129	58	120-277V	Carbon Bronze	Full Cutoff	080083774807
XTOR6B-WT	320W	6,129	58	120-277V	Summit White	Full Cutoff	080083775132
XTOR6BRL	320W	6,225	58	120-277V	Carbon Bronze	Refractive Lens	080083774821
XTOR6BRL-WT	320W	6,225	58	120-277V	Summit White	Refractive Lens	080083775194
XTOR8B	400W	8,502	81	120-277V	Carbon Bronze	Full Cutoff	080083774814
XTOR8B-WT	400W	8,502	81	120-277V	Summit White	Full Cutoff	080083789160
XTOR8BRL	400W	8,635	81	120-277V	Carbon Bronze	Refractive Lens	080083774852
XTOR8BRL-WT	400W	8,635	81	120-277V	Summit White	Refractive Lens	080083775668
XTOR12B	450W	12,728	102	120-277V	Carbon Bronze	Full Cutoff	080083779574
XTOR12BRL	450W	13,458	102	120-277V	Carbon Bronze	Refractive Lens	080083779581



## Lumark WP Wal-Pak Glass

- Traditional architectural style with high performance energy efficient illumination
- Rugged die-cast aluminum housing and door in bronze powder-coat paint
- Impact resistant borosilicate prismatic glass hinged, removable door
- Ballast/LED driver are secured to housing for optimal heat sinking
- Ideal for building entrances, vehicle ramps, schools, tunnels, stairways and loading docks



WP Wal-Pak Glass



Catalog Number	Non-LED Equivalent	Lumens	Watts	CCT	Voltage	Controls	UPC
WPL4B	70W	4,199	32	5000K	120-277V	--	080083751365
WPL6B	100W	5,883	46	5000K	120-277V	--	080083751402

## Lumark Square Glass Wall Packs

- Traditional square style with high performance and energy efficient illumination
- Rugged die-cast aluminum housing for enhanced durability
- Removable door offers ease of maintenance
- Optional button photocontrol to enable dusk-to-dawn control
- Ideal for building entrances, vehicle ramps, schools, tunnels, stairways and loading docks



WPSQLED



Catalog Number	Non-LED Equivalent	Lumens	Watts	CCT	Voltage	Controls	UPC
WPSQLED-100-UNV-PC	320-450W	11,043	101	4000K	120-277V	D2D	080083805945
WPSQLED-65-UNV-7050	175W	7,441	64	5000K	120-277V	--	080083805723
WPSQLED-75-UNV	250W	7,706	74	4000K	120-277V	--	080083805686
WPSQLED-75-UNV-PC	250W	7,706	74	4000K	120-277V	D2D	080083805921

## Lumark AP Traditional Glass Wall Packs

- LED wall pack available with selectable configurations
- Die-cast aluminum housing with hinged, removable die-cast aluminum door
- Heat and impact resistant borosilicate glass lens
- Selectable CCT & selectable lumens
- Ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks



WPMLED



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Color Temperature	Controls	UPC
WPMLED07B	70W	3,500	28	120-277V	4000K	--	080083175901
WPMLED10B	100W	4,800	40	120-277V	4000K	--	080083175925
WPMLED15B	150W	7,100	60	120-277V	4000K	--	080083175949
WPMLED20B	200W	9,800	80	120-277V	4000K	--	080083175963
WPMLED25B	250W	12,000	100	120-277V	4000K	--	080083175987
WPMLED15S	150W	4,000-7,800	30/40/60	120-347V	3000/4000/5000K	D2D	080083176144
WPMLED25S	250W	9,800-13,400	70/80/90/100	120-347V	3000/4000/5000K	D2D	080083176168

## Lumark AP ASWP Adjustable Slim Wall Pack

- Adjustable slim wall pack available in small and medium sizes
- 3-color selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages range from 2,100-10,200 lumens
- Internal toggle switches to easily adjust luminaire CCT and lumens
- Integrated button type photocontrol for dusk-to-dawn operation



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Color Temperature	Controls	UPC
ASWPLED1S	155W	2,000 - 4,000	15 - 30W	120-347V	3000K - 5000K	--	080083265169
ASWPLED2S	375W	5,000 - 10,000	40 - 75W	120-347V	3000K - 5000K	--	080083265183





# Area/Site Lighting

Lumark and Lumark AP area and site solutions provide a uniform lighting experience for improved safety by illuminating walking paths, potential obstacles as well as providing substantial energy savings over traditional sources. These patented designs offer a mix of mounting heights, optical designs, and control options for a variety of applications.



**Lumark**  
Prevail | Prevail XL



**Lumark**  
Caretaker



**Lumark AP**  
LAS Area/Site Luminaire

## Lumark Prevail | Prevail XL

- Provides a new level of performance, versatility and value
- Low-profile, architectural design with a die-cast aluminum housing
- Versatile mount arm includes multiple drill patterns, round and square poles
- Simple retrofit installation; Reduces installation time and provides labor savings
- Ideal for general area lighting such as parking lots, walkways, roadways and building areas



Area/Site

LUMARK

Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Distribution	Controls	UPC
<b>Prevail</b>							
PRVS-C15-UNV-T3	150W	7,111	52	120-277V	T3	-	080083897261
PRVS-C15-UNV-T4	150W	7,088	52	120-277V	T4	-	080083897285
PRVS-C25-UNV-T3	250W	13,183	96	120-277V	T3	-	080083897308
PRVS-C25-UNV-T4	250W	13,140	96	120-277V	T4	-	080083897322
PRVS-C40-UNV-T3	400W	17,144	131	120-277V	T3	-	080083897346
PRVS-C40-UNV-T4	400W	17,087	131	120-277V	T4	-	080083897360
PRVS-C60-UNV-T3	450W	20,050	153	120-277V	T3	-	080083897384
PRVS-C60-UNV-T4	450W	19,984	153	120-277V	T4	-	080083897421
PRVS-C15-347-T3	150W	7,111	52	347V	T3	-	080083897445
PRVS-C15-347-T4	150W	7,088	52	347V	T4	-	080083897452
PRVS-C25-347-T3	250W	13,183	96	347V	T3	-	080083897469
PRVS-C25-347-T4	250W	13,140	96	347V	T4	-	080083897476
PRVS-C40-347-T3	400W	17,144	131	347V	T3	-	080083897483
PRVS-C40-347-T4	400W	17,087	131	347V	T4	-	080083897490
PRVS-C60-347-T3	450W	20,050	153	347V	T3	-	080083897506
PRVS-C60-347-T4	450W	19,984	153	347V	T4	-	080083897513
<b>Prevail XL</b>							
PRVS-XL-C75-UNV-T3	750W	26,120	176	120-277V	T3	-	080083906499
PRVS-XL-C75-UNV-T4	750W	26,098	176	120-277V	T4	-	080083906512
PRVS-XL-C100-UNV-T3	1,000W	31,061	217	120-277V	T3	-	080083906536
PRVS-XL-C100-UNV-T4	1,000W	31,035	217	120-277V	T4	-	080083906550
PRVS-XL-C125-UNV-T3	1,000W+	36,304	264	120-277V	T3	-	080083906574
PRVS-XL-C125-UNV-T4	1,000W+	36,274	264	120-277V	T4	-	080083906598
PRVS-XL-C150-UNV-T3	1,500W	41,124	285	120-277V	T3	-	080083906611
PRVS-XL-C150-UNV-T4	1,500W	41,089	285	120-277V	T4	-	080083906635
PRVS-XL-C175-UNV-T3	1,500W+	48,610	346	120-277V	T3	-	080083906659
PRVS-XL-C175-UNV-T4	1,500W+	48,569	346	120-277V	T4	-	080083906673

## Lumark Caretaker

- Combines high performance, low maintenance, and easy installation for years of worry-free operation
- Rugged die-cast housing for durability in security applications
- Versatile universal mounting plate allows quick and easy installation
- Uniform distribution with excellent vertical illumination for maximum light coverage
- Ideal for residential street lighting, perimeter area lighting, parking areas, loading platforms, boat docks, access drives or pathways



SR-CARETAKER

0-10V  
DIMMING



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Area of Coverage	Controls	UPC
CTKR1B	100-150W	4,515	29	120-277V	56'	3P-PC	080083865390
CTKR2B	175W	7,110	50	120-277V	72'	3P-PC	080083865406
CTKR3B	250W	9,741	71	120-277V	90'	3P-PC	080083865413
SR-CARETAKER	Small Refractive Lens Accessory						080083699087



## Lumark AP LAS Area/Site Luminaire

- High-efficiency LED luminaire delivers maximum energy savings while lowering overall maintenance costs
- 10-position, Field-Selectable lumens across 2 die-cast aluminum housing sizes
- Pole mount arm or adjustable slipfitter mounting arm included for versatility in use and simple installation
- Energy and maintenance savings up to 79% versus HID solutions up to 79%
- Ideal parking lots, walkways, building areas and other outdoor areas



0-10V  
DIMMING



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Mounting	Distribution	Controls	UPC
LAS45P-T3	450W	4,800-20,000	30-150	120-277V	Slipfitter	T3	--	080083248360
LAS45P-T3-HV	450W	4,800-20,000	30-150	347-480V	Slipfitter	T3	--	080083248728
LAS45P-T4	450W	4,800-20,000	30-150	120-277V	Slipfitter	T4	--	080083248384
LAS45P-T4-HV	450W	4,800-20,000	30-150	347-480V	Slipfitter	T4	--	080083248742
LAS45P-T5	450W	4,800-20,000	30-150	120-277V	Slipfitter	T5	--	080083248704
LAS45P-T5-HV	450W	4,800-20,000	30-150	347-480V	Slipfitter	T5	--	080083248766
LAS45S-T3	450W	4,800-20,000	30-150	120-277V	Slipfitter	T3	--	080083155804
LAS45S-T3-HV	450W	4,800-20,000	30-150	347-480V	Slipfitter	T3	--	080083155927
LAS45S-T4	450W	4,800-20,000	30-150	120-277V	Slipfitter	T4	--	080083155828
LAS45S-T4-HV	450W	4,800-20,000	30-150	347-480V	Slipfitter	T4	--	080083155941
LAS45S-T5	450W	4,800-20,000	30-150	120-277V	Slipfitter	T5	--	080083155842
LAS45S-T5-HV	450W	4,800-20,000	30-150	347-480V	Slipfitter	T5	--	080083155965
<b>LAS100</b>								
LAS100P-T3	1000W	8,100-34,000	48-250	120-277V	Slipfitter	T3	--	080083248780
LAS100P-T3-HV	1000W	8,100-34,000	48-250	347-480V	Slipfitter	T3	--	080083248841
LAS100P-T4	1000W	8,100-34,000	48-250	120-277V	Slipfitter	T4	--	080083248803
LAS100P-T4-HV	1000W	8,100-34,000	48-250	347-480V	Slipfitter	T4	--	080083248865
LAS100P-T5	1000W	8,100-34,000	48-250	120-277V	Slipfitter	T5	--	080083248827
LAS100P-T5-HV	1000W	8,100-34,000	48-250	347-480V	Slipfitter	T5	--	080083248889
LAS100S-T3	1000W	8,100-34,000	48-250	120-277V	Slipfitter	T3	--	080083155866
LAS100S-T3-HV	1000W	8,100-34,000	48-250	347-480V	Slipfitter	T3	--	080083155989
LAS100S-T4	1000W	8,100-34,000	48-250	120-277V	Slipfitter	T4	--	080083155880
LAS100S-T4-HV	1000W	8,100-34,000	48-250	347-480V	Slipfitter	T4	--	080083156009
LAS100S-T5	1000W	8,100-34,000	48-250	120-277V	Slipfitter	T5	--	080083155903
LAS100S-T5-HV	1000W	8,100-34,000	48-250	347-480V	Slipfitter	T5	--	080083156023

# Parking Garage/Canopy

Lumark and Lumark AP parking garage and canopy luminaires provide durable, wet-location rated lighting solutions for any outdoor, under-cover application. With a variety of mounting configurations, output adjustability and controls, these products offer the ideal solutions for new or retrofit applications.



**Lumark**  
RPGC Round  
Parking Garage and Canopy



**Lumark AP**  
CLCS Canopy

## Lumark RPGC Round Parking Garage and Canopy

- Innovative, energy-efficient LED fixture designed to replace traditional HID on a 1-to-1 basis.
- Low profile, rugged construction in a die-cast aluminum housing
- Junction box, surface, or pendant mounting available
- Selectable lumen allows for seamless integration where high security illumination and energy savings are needed
- Ideal for parking garages, canopy, stairwells, and low-bay retail installations



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Controls	UPC
RPGC25S	150 - 250W	3,690 - 7,811	31 - 63	120-277V	-	080083885664
RPGC25S-347	150 - 250W	3,690 - 7,811	31 - 63	347V	-	080083885688
RPGC25-MS/DIM-L20	150 - 250W	3,690 - 7,811	31 - 63	120-277V	SENS	080083885725
RPGC25-347-ZD-WOBWH	150 - 250W	3,690 - 7,811	31 - 63	347V	SENS	080083249282



## Lumark AP CLCS Canopy

- Slim, low-profile, traditional design with high performance energy efficient illumination
- Rugged die-cast aluminum construction and gasketed housing
- LED canopy available with fixed output or selectable configurations
- 3-color selectable CCT: 3000K, 4000K, 5000K
- Ideal for new or existing spaces including bank, retail, drive-thru, covered sidewalks and hospital entryways



Catalog Number	HID Equivalent	Lumens	Watts	Voltage	Color Temperature	Controls	UPC
CLCS15	150W	5,500	40	120-277V	4000K	--	080083161003
CLCS17	175W	8,000	60	120-277V	4000K	--	080083161041
CLCS17S	175W	5,500-8,000	40-60	120-277V	3000/4000/5000K	--	080083160006
CLCS17S-PC	175W	5,500-8,000	40-60	120-277V	3000/4000/5000K	D2D	080083159727
CLCS40S	400W	13,600-17,600	90-120	120-277V	3000/4000/5000K	--	080083160020
CLCSLED-55-SM-UNV	175W	7,230	56	120-277V	4000K	--	080083776085





### Lighting Product Lines

Ametrix  
AtLite  
Corelite  
Ephesus  
Fail-Safe  
HALO  
HALO Commercial  
Invue  
iO  
Iris  
Lumark  
Lumark AP  
Lumière  
McGraw-Edison  
Metalux  
MWS  
Neo-Ray  
Portfolio  
Prentlux - 3D Printed Lighting  
RSA  
Shaper  
Streetworks  
Sure-Lites

### Controls Product Lines

Greengate  
Fifth Light  
Intelligent Lighting Controls

### Connected Lighting Systems and Smart Spaces Platform

WaveLinx  
Trellix Infrastructure



Cooper Lighting Solutions  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.cooperlighting.com

Canada Sales  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2024 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. CA51418324EN  
September 30, 2024 4:11 PM

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.