

Good

Better

Best

Click on products to learn more



		LHBS	SPHB	VHB	UHBS	CZL	Steeler	OHB(L)	Benchmark
APPLICABILITY <sup>1</sup>	Big Box Retail	★	★★★	★	★★	★★★	★★	★★★	★
	Sports / Recreation	★★	★★	★★	★★	★	★★★	★★★	★★
	Warehouses	★★★	★★★	★★★	★★	★★	★★★	★★★	★★★
	Manufacturing	★★	★★	★★	★★	★	★★★	★★★	★★★
	Cold Storage	★	★★	★★★	★	★	★	★★★	★★
	Large Indoor		★	★			★★	★★★	★★
	Complex Environments			★	★★		★		★★★
FEATURES / PERFORMANCE	Lumen Range	12,000 - 36,000	9,000 - 60,000	9,000 - 48,000	12,000 - 36,000	5,000 - 32,000	9,000 - 30,000	9,000 - 100,000	12,000 - 70,000
	Selectable	Lumens/CCT	Lumens/CCT	Lumens	Lumens/CCT				
	Efficacy (Max)	160 lm/W	172 lm/W	164 lm/W	165 lm/W	176 lm/W	152 lm/W	205 lm/W	181 lm/W
	CRI	80	70, 80, 90	70, 80, 90	80	80, 90	80	70, 80, 90	70, 80
	Distribution	M	N, M, W	N, W	M	Multiple	N, M, W	N, M, W	N, M, W
	Sizes	13", 14.2", 19.7"	18", 26", 42"	< 2'	13"/15" Dia	4', 8'	17" Dia	Scalable	17", 25" Dia
	Housing <sup>2</sup>	CRS / Diecast	CRS	CRS / Extruded	Diecast	CRS	CRS / Diecast	CRS	Diecast
	Lensing	Acrylic	Polycarbonate	Polycarbonate	Polycarbonate	Multiple	Polycarbonate	Acrylic	Acrylic
	Uplight	None	Optional	None	None	Optional	Up to 10%	None	None
	Life (@ 60K hrs)	L85	L88	L83	L91	L89	L88	L96	L92
	Ambient Range	-20C to 50C	-40C to 55C	-40C to 55C	-40C to 50C	-40C to 65C	-40C to 55C	-40C to 55C	-40C to 65C
	Emergency	Rapid Response	Integrated	Remote	✓	Integrated	Remote	Integrated	Remote
	Ratings	Damp	Damp	Damp	IP65	Damp	IP65 Optics	Damp	IP66
DLC	Premium	Premium	Standard, Premium	Premium	Premium	Premium	Premium	Premium	
INTEGRATED CONTROLS	Basic Occupancy	Rapid Response		✓		✓	✓	✓	✓
	Stand Alone Daylight / Occupancy	✓	✓	✓	✓	✓	✓	✓	✓
	WaveLinx	✓	✓	✓		✓	✓	✓	✓
	Enlighted <sup>3</sup>		✓	✓		✓	✓	✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable  
 2. CRS=Cold-rolled Steel, Extruded=Extruded Aluminum, Diecast=Diecast Aluminum.  
 3. Location data for asset tracking.