

Shaper

DESCRIPTION

605-W and 605-WP Luminous Wall Sconce features 6 standard finishes, 3 decorative trim bar options and ADA compliant.

- Wall Luminous Vanity Luminaire
- Painted solid aluminum w/ extruded white acrylic panel
- Universal circular strap for a standard 4" J-box or plaster ring
- UL and CUL approved for interior and damp locations

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Material
Painted solid aluminum with a 1/8" matte white extruded acrylic panel and solid aluminum end caps closed end.

Finishes
ALP (Aluminum Paint)
MW (Matte White)
MB (Matte Black)
GRM (Graphite Metallic)
DP (Dark Platinum)
BM (Bronze Metallic)
CC (Custom Color – Specify)

For Custom Color contact factory for quotation.

LED
25" L3:2000 (nominal lumens at max) 20W

37" L4:3000 (nominal lumens at max) 29W
49" L5:4000 (nominal lumens at max) 38W

Driver
Standard integral class 2 driver 38W max., 0-10V dimming. LED system coupled with electrical driver to deliver optimal performance. Electronic drivers are available for 120-277V applications. A 0-10V dimming control is standard on all models.

Installation
Supplied with a universal circle strap for a standard 4" J-box or round or octagonal plaster ring. Horizontal or vertical mount. Shaper 605-W luminaires are

designed for interior installations only. Shaper 605-WP are listed for wet location. Battery must be remote mounted in an interior location at a 5ft max distance.


Compliance
For W mounting, U.L. and C.U.L approved for indoor and damp location. For WP mounting, U.L. and C.U.L. listed for wet location, ADA compliant, except with proud trim options. Options to meet Buy American Act requirements.

Warranty
5 year limited warranty on LED components.



605-W Series 605-WP Series

DIMENSIONS



25"
- Lumen Output Source Lumens:
L3:2000 nominal lumens at max
- Wattage: 20W
- Color Rendering: CRI 83+
- Correlated Color Temperature:
4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

37"
- Lumen Output Source Lumens:
L4:3000 nominal lumens at max
- Wattage: 29W
- Color Rendering: CRI 83+
- Correlated Color Temperature:
4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

49"
- Lumen Output Source Lumens:
L5:4000 nominal lumens at max
- Wattage: 38W
- Color Rendering: CRI 83+
- Correlated Color Temperature:
4000K, 3500K, 3000K, 2700K
- Rated Life of L amp
- Dimming: 0-10V



ORDERING INFORMATION

Sample Number: 605-37-W-L4/827-UNV-ALP-2VTB

Domestic Preferences ⁽¹⁾	Series	Size	Mounting Type	LED Lamp	LED Voltage	Finish	Options
[Blank] = Standard BAA = Buy American Act	605 = Luminous Sconce	25 = 25" 37 = 37" 49 = 49"	W = Interior Wall WP = Exterior Wall	25" L3/827 L3/830 L3/835 L3/840 37" L4/827 L4/830 L4/835 L4/840 49" L5/827 L5/830 L5/835 L5/840	UNV = (120-277V)	ALP=Aluminum Paint MW=Matte White MB =Matte Black DP = Dark Platinum GRM=Graphite Metallic BM=Bronze Metallic CC =Custom Color - Contact factory for quotation	2VTB=Two Vertical Trim Bars 2HTB=Two Horizontal Trim Bars 2VTB/2HTB=Two Vertical Trim Bars/ Two Horizontal Trim Bars 2HTB/PC=Two Horizontal Trim Bars with Perforated Center RBP =Remote Battery Pack

Notes (1) Only product configurations with this designated prefix are built to be compliant with the Buy American Act of 1933 (BAA). Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.



Cooper Lighting Solutions
18001 East Colfax Avenue
Aurora, CO 80011
P: 303-393-1522
www.cooperlighting.com

Specifications and dimensions subject to change without notice.

605 SERIES WALL LUMINAIRE

PS525083EN

05-23-19

1 of 1