

# Indoor Vandal Resistant LED

## Selection Guide


# Fail-Safe

Good

Better

Best

Click on products to learn more



		FLD4B	FLD6B	UCLV	GRV	FSP	FCZ	ENV	FSN	SGI
<b>APPLICABILITY<sup>1</sup></b>	<b>Behavioral Health</b>	★★★	★★★	★★	★★	★★★	★★★	★★★	★★★	★★★
	<b>Indoor Vandal Resistant</b>	★★★	★★★	★★★	★★★	★★★	★★★	★★★	★★★	★★★
	<b>Indoor High Abuse</b>	★★★	★★★	★	★★★	★★★	★★★	★	★★★	★
	<b>Multifamily homes</b>	★★★	★★★	★	★★	★★	★★	★★	★	★★
<b>FEATURES</b>	<b>Size</b>	4" Round	6" Round	1', 2', 3', 4'	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4	Fixed 2', 4', 8'	1x4, 2x2, 2x4
	<b>Mounting</b>	Recessed	Recessed	Undercabinet	Recessed	Recessed	Recessed	Recessed	Recessed or Surface/Suspension	Recessed
	<b>Maximum Lumen Output</b>	4,000	7,000	2,400	17,000	6,400	7,500	6,200	4,121 (4ft)	11,500
	<b>Maximum Lens Thickness</b>	0.187"	0.500"	0.187"	0.187"	0.375"	0.250"	0.375"	0.250"	0.375"
	<b>Emergency</b>	Optional	Optional	N/A	Optional	Optional	Optional	Optional	Optional	Optional
	<b>Occupancy</b>	N/A	N/A	Optional	N/A	N/A	N/A	N/A	N/A	N/A
<b>CERTIFICATIONS</b>	<b>IP</b>	IP66	IP66	IP63	N/A	IP65/IP66	IP65	IP66	IP66	IP65
	<b>Wet Location</b>	Standard	Standard	N/A	N/A	Standard	Standard	Standard	Standard	Optional
	<b>NSF</b>	Standard	Standard	N/A	N/A	Standard	Standard	Standard	Standard	Optional

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable



**Cooper Lighting Solutions**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.cooperlighting.com

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2020 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. SA519061EN-web  
November 2, 2021 2:08 PM

Cooper Lighting Solutions is a registered trademark.  
All other trademarks are property of their respective owners.  
Product availability, specifications, and compliances are subject to change without notice.