



# HALO Downlighting


## LED Product Selection Guide

August 2023



# HALO®

For over 65 years, **HALO** has been the industry-leader in high-quality recessed downlighting. For new construction, renovation or retrofits, **HALO** offers a full range of LED luminaires from 2" apertures all the way to 14" apertures. Our innovative surface mount downlights can be retrofitted into existing recessed housings, installed into most junction boxes or direct mounted to the ceiling with mains connections to an integrated junction box. Our LED lamp-based housing and trim solutions are available in 3", 4", 5", and 6" apertures for line and low voltage MR16/PAR16 lamps and 3", 4", 5", and 6" apertures for medium screw base (E26) lamps.



## Table of Contents

- 2 Surface / Junction Box Mount
- 3 Canless
- 5 LED Recessed Trims
- 6 Integrated

The LED selection guide is a simple yet powerful tool to help assist with product comparisons and selection based on features, performance and value.



# Surface / Junction Box Mount

## LED Selection Guide

HALO

**M**arket focus portfolio with products designed for broad applications

**V**alue and quality industry leading leadership

**P**erformance for any application and feature offerings for residential and commercial applications

Good Better Best



		HLCE	HLS	BLD	CLD	SMD	SLD
<b>APPLICATION</b>	<b>Lens / Wet Location</b>		✓	✓	✓	✓	✓
	<b>Lens / Damp Location</b>	✓					
	<b>Accent Adjustable</b>						
	<b>Wall Wash</b>						
	<b>Open / Deep Baffle</b>						
<b>FEATURES / PERFORMANCE</b>	<b>Size / Shape</b>	4" & 6" Round	4" / 6" / 9" Round	4" & 6" Round	7" Round	4"/6"/12"/14" Round & Square	4" & 6" Round
	<b>Lumens (Max)</b>	960	1200	812	810	1264	1215
	<b>Lite (L70B50)</b>	50K hours	50K hours	50K hours	50K hours	50K hours	50K hours
	<b>CRI</b>	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)
	<b>CCT (K)</b>	30	30/40/50	27/30/35/40/50	30/40/50	27/30/35/40/50	27/30/35/40
	<b>Distribution / S.C.</b>	1.4	1.4	1.4	1.4	1.4	1.4
	<b>Input Voltage</b>	120	120	120	120	120/120-277	120/120-277
<b>CONTROL</b>	<b>Field Select (5) CCT</b>			✓	✓ (3)	✓	✓
	<b>LE/TE Phase Cut</b>	✓	✓	✓	✓	✓	✓
	<b>0-10V Analog</b>					✓	✓
	<b>Smart (Zigbee)</b>						
	<b>Smart (Wi-Fi® + Bluetooth)</b>			✓			



## Junction Box Installation (SMD)



Good

Better



		HLB Lite	LT-DM	CJB	HLBPH	RL-DM	RA-DM	HLA	HLB	
APPLICATION	Lens	smooth	smooth	smooth	smooth	smooth	smooth	smooth	prismatic	
	Wet Location	✓	✓	✓	✓	✓	✓	✓	✓	
	Direct Mount Type	slim	regressed	slim w/driver attached	slim	regressed	regressed adjustable	smooth adjustable	slim	
	Wall Wash									
FEATURES / PERFORMANCE	Size / Shape	4" & 6" Round	3"/4"/6" Round	4" & 6" Round	4" & 6" Round	4" & 6" Round	4" & 6" Round	3" & 4" Round & Square	3"/4"/6" Round & Square 8" & 12" Round	
	Lumens (Max)	1000	800	600 or 900	1100	1200	600	600	2400	
	Lite (L70B50)	30K hours	35K hours	35K hours	50K hours	70K hours	70K hours	50K hours	50K hours	
	CRI	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	
	CCT (K)	27/30/35/40/50/60	27/30/35 & 30/40/50	27/30/35/40/50	27/30/35/40/50	27/30/35/40/50/ D2W	27/30/35/40/50	27/30/35/40/50	27/30/35/40/50	27/30/35/40/50
	Distribution / S.C.	1.4	1.2	1.4	1.4	1.2	1.2	1.4	1.4	
	Input Voltage	120	120	120	120	120	120	120	120/120-277	
CONTROL	Field Select CCT	✓ (3) CCT	✓ (3) CCT	✓ (5) CCT	✓ (5) CCT	✓ (5) CCT (2) D2W	✓ (5) CCT	✓ (5) CCT	✓ (5) CCT	
	Field Select Lumens					✓				
	LE/TE Phase Cut	✓	✓	✓	✓	✓	✓	✓	✓	
	0-10V Analog								✓	
	Smart (Zigbee)									
	Smart (Wi-Fi® + Bluetooth)								✓	

Canless  
Installation





Best

		HLBC	RL-DM Night Light	RLS-DM Slope	LCR	ML4-DM	QuickLink Slim		QuickLink Regressed	
							Phase Cut	0-10V	Phase Cut	0-10V
APPLICATION	Lens	prismatic	smooth	prismatic	smooth	lensed or open	prismatic	prismatic	smooth	smooth
	Wet Location	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Direct Mount Type	slim	regressed	regressed / slope ceiling	regressed	flush or regressed	slim (HLB)	slim (HLB)	regressed (LT-DM)	regressed (RL-DM)
	Wall Wash				✓	✓				
FEATURES / PERFORMANCE	Size / Shape	4" & 6" Round	4" & 6" Round	4" & 6" Round	2"/4"/6"/8" Round	4" Round/Square	4" & 6" Round	4" & 6" Round	4" & 6" Round	4" & 6" Round
	Lumens (Max)	1100	1000	1500	8000	1000	1000	1000	600	600
	Lite (L70B50)	50K hours	50K hours	50K hours	50K hours	50K hours	50K hours	50K hours	50K hours	50K hours
	CRI	90 (min)	90 (min)	90 (min)	90 (min)	90 & 95	90 (min)	90 (min)	90 (min)	90 (min)
	CCT (K)	27/30/35/40/50/D2W	27/30/35/40/50/D2W	27/30/35/40/50	27/30/35/40/50/65	27/30/35/40/50/D2W	27/30/35/40/50	27/30/35/40/50	27/30/35/40/50	27/30/35/40/50
	Distribution / S.C.	1.2	1.2	1.2	1.2	NFL, FL, WFL, AWW	1.4	1.4	1.2	1.2
	Input Voltage	120/120-277	120	120	120-277	120-277	120	120-277	120	120-277
CONTROL	Field Select CCT	✓ (5) CCT (2) D2W	✓ (5) CCT	✓ (5) CCT	✓ (5) CCT	✓ (5) CCT (2) D2W	✓ (5) CCT	✓ (5) CCT	✓ (5) CCT	✓ (5) CCT
	Field Select Lumens	✓								
	LE/TE Phase Cut	✓	✓	✓	✓	✓	✓		✓	
	0-10V Analog				✓	✓		✓		✓
	Smart (Zigbee)									
	Smart (Wi-Fi® + Bluetooth)									

**QuickLink**  
Low Voltage System



**1 POWER SUPPLY & MULTIPLE FIXTURES**



With QuickLink Twist Connectors, each fixture attaches to the low voltage cable in seconds. The flexibility of the system allows the user to mix and match the compatible HALO QuickLink canless fixtures onto the same low voltage cable.



Good

Better

Best



		LT	LA	HLBC	RL	RL Night Light	RLD	RA	RSQ	ML4	ML56	
APPLICATION	Lens / Wet Location	✓		✓	✓	✓			✓	✓	✓	
	Accent Adjustable		✓					✓			✓	
	Wall Wash									✓	✓	
	Open / Deep Baffle						✓			✓	✓	
FEATURES / PERFORMANCE	Size / Shape	4" & 5/6"	4" & 5/6"	4" & 6" Round	3" / 4" & 5/6"	4" & 5/6"	4" & 6"	3" / 4" & 5/6"	4, 5 & 6"	4"	5" & 6"	
	Lumens (Max)	1200	600	1100	1200	1000	600	600	800	1100	1200	
	Lite (L70B50)	50K hours	50K hours	50K hours	70K hours	50K hours	70K hours	70K hours	50K hours	50K hours	50K hours	
	CRI	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 (min)	90 or 95	90 (min)
	CCT (K)	27/30/35/40/50	27/30	27/30/35/40/50/ D2W	27/30/35/40/50/ D2W	27/30/35/40/50/ D2W	30	27/30/35/40/50	27/30/35/40	27/30/35/40/50/ D2W	27/30/35/40/50/ D2W	
	Distribution / S.C.	1.3	VWFL	1.2	1.2	1.2	1.4	NFL/VWFL	1.2	NFL/FL/WFL	NFL/FL/WFL	
	Input Voltage	120	120	120/120-277	120	120	120	120	120	120-277	120-277	
CONTROL	Field Select CCT	✓ (5) CCT		✓ (5) CCT (2) D2W	✓ (5) CCT (2) D2W	✓ (5) CCT (2) D2W		✓ (5) CCT	✓ (5) CCT	✓ (5) CCT (2) D2W	✓ (5) CCT (2) D2W	
	Field Select Lumens			✓	✓					✓	✓	
	LE/TE Phase Cut	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	
	0-10V Analog									✓	✓	
	Smart (Zigbee)				✓							
	Smart (Wi-Fi® + Bluetooth)				✓							

## Recessed Installation



**M**arket focus portfolio with products designed for broad applications

**V**alue and quality industry leading leadership

**P**erformance for any application and feature offerings for residential and commercial applications



**Better** **Best**



		HL6	H4LED	HL36AR/ HL36SAR	HL3R/HL3S
<b>APPLICATION</b>	<b>Lens / Wet Location</b>	✓	✓	✓	✓
	<b>Accent Adjustable</b>	slope ceiling	✓	✓	✓
	<b>Wall Wash</b>		✓	✓	✓
	<b>Open / Deep Baffle</b>	✓	✓	✓	✓
<b>FEATURES / PERFORMANCE</b>	<b>Size / Shape</b>	6"	4" Round and Square	3" Round & Square	3" Round & Square
	<b>Lumens (Max)</b>	1800	700	1500	1800
	<b>Lite (L70B50)</b>	50K hours	50K hours	50K hours	50K hours
	<b>CRI</b>	90 (min)	90 (min)	90 (min)	90 (min)
	<b>CCT (K)</b>	27/30/35/40	27/30/35/40	27/30/35/40	27/30/35/40
	<b>Distribution / S.C.</b>	NFL/FL/WFL	NFL/FL/WFL & 1.2	SP/NFL/FL/WFL	SP/NFL/FL/WFL
	<b>Input Voltage</b>	120-277	120-277	120/120-277	120/120-277
<b>CONTROL</b>	<b>Field Select (5) CCT</b>				
	<b>LE/TE Phase Cut</b>	✓	✓	✓	✓
	<b>0-10V Analog</b>	✓	✓	✓	✓
	<b>Smart (Zigbee)</b>				
	<b>Smart (Wi-Fi® + Bluetooth)</b>				

## Lighting Brands

Ametrix  
AtLite  
Corelite  
Ephesus  
Fail-Safe  
HALO  
HALO Commercial  
Invue  
iO  
Iris  
Lumark  
Lumière  
McGraw-Edison  
Metalux  
MWS  
Neo-Ray  
Portfolio  
PrentaLux - 3D Printed Lighting  
RSA  
Shaper  
Streetworks  
Sure-Lites  
Telensa

## Controls Brands

Greengate  
Fifth Light  
Intelligent Lighting Controls

## Connected Lighting Systems and Smart Spaces Platform

WaveLinx



**Cooper Lighting Solutions**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.cooperlighting.com](http://www.cooperlighting.com)

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2023 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. SA518100EN  
August 16, 2023 9:25 AM

All other trademarks are property  
of their respective owners.

Product availability, specifications,  
and compliances are subject to  
change without notice.