

Fail-Safe



FLR/FLR2

Fully Luminous
Recessed

High abuse, medical/cleanroom,
and wet location
applications



Scan for more.



Construction

IK10 rated luminaire with
medical/cleanroom, wet
location, and high abuse
constructions available



Customizable

Highly configurable
with up to 10,000
lumens



Connected Controls


WaveLinx PRO and
LITE enabled




Low glare

90 CRI and
selectable CCT for
uniform lighting
available

Healthcare • Public Spaces • Locker Rooms • Behavioral Health • Wet Locations • Cleanrooms • Labs • Canopies
• Pharmacies • Research Centers • High Tech Manufacturing • Food Processing • Food Service



Standard Configurable Dimensional and Mounting Details



Features		Benefits
Construction	2-1/4" depth	Excellent choice for shallow plenum environments
	Medical/cleanroom, Wet Location, and High Abuse options available	Three applications; one solution
	Custom lumen packages available. Standard up to 10,000 lumens	Fully configurable for a plethora of locations
Performance	Available in 3000K, 3500K, 4000K, and 5000K CCT, 80 and 90 CRI	Uniform light source with visual comfort
	0-10V dimming to 10% standard, 1% dimming available	Full dimming controls to meet any standards
	WaveLinx enabled	Key for adaptability and potential energy savings
	Ligature Resistant, IK10, IP65, and ISO 5-8 rated	Code compliant to meet all complex environment standards

