

**AtLite**



Approved for  
New York City

**Rival Series**  
Emergency Lighting

**COOPER** Lighting

The AtLite Rival Series is a complete family of exit and emergency lighting fixtures that have been designed to offer both performance and value. All products listed in this brochure are UL listed and approved for use in New York City.

When placing your next order, look no further than AtLite, the brand with the largest product offering and most reliable name for exit and emergency lighting in New York!



**The Rival Series -  
A quality line of NYC Approved emergency lighting.**

# Rival Series - Edge-Lit Exits


## Features:

- Anodized Aluminum Housing/Faceplate
- Clear Acrylic Panel<sup>1</sup>
- Dual Voltage Input  
120/277 VAC, 60 Hz
- Long-Life, Energy Efficient LEDs
- Sealed Nickel Cadmium Batteries with 15 Year Life Expectancy<sup>2</sup>
- UL Damp Location Listed (Indoor)
- Universal, Field Installed Chevrons
- Ceiling, Wall or End Mounting<sup>3</sup>




## Dimensions<sup>4</sup>

### Surface REUS Series




### Recessed REUR Series



## Ordering Information

Sample Number: REURNR



## Energy Data:

Input Power:  
120V = 3W  
277V = 3W

Input Current (Max.):  
120V = .025A  
277V = .011A

<sup>1</sup> Single face = clear background; Double face = mirrored background.

<sup>2</sup> Nickel Cadmium batteries include a 15 year pro-rata warranty.

<sup>3</sup> Surface Version (Recessed Edge-Lit only available for accessible ceiling mounting).

<sup>4</sup> Dimensions for 8" letter sign.

# Rival Series - Die Cast Exits


## Features:

- Die Cast Aluminum Housing with Canopy
- Brushed Aluminum Face
- Dual Voltage Input 120/277 VAC, 60 Hz
- Long Life, Energy Efficient LEDs
- Premium Sealed Nickel Cadmium Batteries with 15 Year Life Expectancy<sup>1</sup>
- UL Damp Location Listed (Indoor)
- Universal, Field Selectable Chevrons
- Ceiling, Wall, End Mounting



## Dimensions

### Ceiling




### End



## Ordering Information

Sample Number: RXDN8R1



## Energy Data:

Input Power:

120V = 2.3W

277V = 2.7W

Input Current (Max.):

120V = .025A

277V = .012A

<sup>1</sup> Nickel Cadmium batteries include a 15 year pro-rata warranty.

# Rival Series - Steel Exit Signs


## Features:

- Heavy Duty 20 Gauge Steel Housing with Canopy
- White Powder Coat Finish
- Dual Voltage Input  
120/277 VAC, 60 Hz
- Long-Life, Energy Efficient LEDs
- Sealed Nickel Cadmium Batteries with 15 Year Life Expectancy<sup>1</sup>
- UL Damp Location Listed (Indoor)
- Universal, Field Selectable Chevrons
- Ceiling, Wall, End Mounting




## Dimensions

### Ceiling




### End



## Ordering Information

Sample Number: RXSN8RU



## Energy Data:

Input Power:

120V = 5W

277V = 5W

Input Current (Max.):

120V = .041A

277V = .018A

<sup>1</sup> Nickel Cadmium batteries include a 15 year pro-rata warranty.

# Rival Series - Steel Combo (Exit Sign & Emergency Light)




## Features:

- Heavy Duty 20 Gauge Steel Housing
- White Powder Coat Finish
- Dual Voltage Input  
120/277 VAC, 60 Hz
- Long Life, Energy Efficient LEDs (Exit)
- Three Powerful 12W Incandescent Lamps (Emergency Heads)
- 36W Sealed Lead Calcium Batteries with Available Remote Capacity<sup>1</sup>
- UL Damp Location Listed (Indoor)
- Universal, Field Selectable Chevrons



## Dimensions



## Ordering Information

Sample Number: RCS8R-3

<b>RCS</b>	<b>8</b>	<b>R</b>	<b>3</b>
Series RCS=Rival Steel Combo	Letter Size 8=8"	Letter Color R=Red Letters	Number of Heads 3=Three Heads

## Energy Data:

Input Power:

120V = 12.7W

277V = 14.3W

Input Current (Max.):

120V = .115A

277V = .056A

<sup>1</sup> Lead Calcium batteries include 5 year pro-rata warranty, 12W remote capacity available with (2) 12W lamps attached to fixture.

# Rival Series - Steel Emergency Lights


## Features:

- Heavy Duty 20 Gauge Steel Housing
- White Powder Coat Finish
- Dual Voltage Input  
120/277 VAC, 60 Hz
- Available in both 6V and  
12V Models
- Powerful Incandescent  
Lamping
  - 6REL18 includes (2) 9W Heads
  - 6REL27 includes (2) 12W Heads
  - 12REL50-3 includes (3) 12W Heads
- Dependable Sealed Lead  
Calcium Batteries<sup>1</sup>
- UL Damp Location Listed  
(Indoor)




## Dimensions

### 6REL18 / 6REL27



### 12REL50-3



## Energy Data:

### 6REL18:

Input Power:

120V = 7.1W  
277V = 8.0W

Input Current (Max.):

120V = .066A  
277V = .031A

### 6REL27:

Input Power:

120V = 7.1W  
277V = 8.0W

Input Current (Max.):

120V = .066A  
277V = .033A

### 12REL50-3:

Input Power:


120V = 7.0W  
277V = 8.4W

Input Current (Max.):

120V = .165A  
277V = .072A

## Ordering Information

Sample Number: 6REL18



<sup>1</sup> Lead Calcium Battery(s) include a 5 year pro-rata warranty.

**AtLite**

100 Andrews Road  
Hicksville, NY 11801-1704  
P: 800-209-6357  
F: 800-382-1391

**Cooper Lighting**

Customer First Center  
1121 Highway 74 South  
Peachtree City, GA 30269

P: 770-486-4800  
F: 770-486-4801

[www.cooperlighting.com](http://www.cooperlighting.com)

**International Sales, USA**

Cooper Lighting  
1121 Highway 74 South  
Peachtree City, GA 30269

P: 770-486-4800  
F: 770-486-4801

**Canada**

Cooper Lighting  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8

P: 905-507-4000  
F: 905-568-7049

**The Cooper Lighting Family**

Halo  
Metalux  
Lumark  
Sure-Lites  
Neo-Ray  
Corelite  
Portfolio  
Iris  
Shaper  
io  
Lumière  
Invue  
McGraw-Edison  
Streetworks  
Fail-Safe  
Atlite  
MWS  
DLS  
RSA  
Ametrix

**Domestic Facilities**

Cranbury, New Jersey  
Elk Grove Village, Illinois  
Irving, Texas  
Ontario, California  
Peachtree City, Georgia

**Canadian Facility**

Calgary, Alberta T2E 7V9

Cooper Lighting and AtLite are valuable trademarks of Cooper Industries in the United States and other countries.  
You are not permitted to use the Cooper Trademarks without the prior written consent of Cooper Industries.

**Cooper Industries, Ltd.**  
600 Travis, Ste. 5800  
Houston, TX 77002-1001  
P: 713-209-8400  
[www.cooperindustries.com](http://www.cooperindustries.com)