


# HALO<sup>®</sup>

808E Essential  
LED Track Luminaire


808E Essential



The HALO 808E Track Head is the perfect lighting solution for general, accent, and display applications.

Our state-of-the-art LED technology delivers up to 2500 lumens and 120 lumens per watt, making it one of the most efficient options on the market. Whether you're lighting a retail, hospitality, or mixed-use project, the HALO 808E is the sleek and energy-efficient choice you've been looking for.

The 3-inch flat back cylindrical design is beautifully crafted with low glare and interchangeable optics, making it a versatile choice for any space.



## Applications

The 808E was designed to deliver powerful, efficient, low-glare solutions in a myriad of applications



Hospitality



Offices



Restaurants



Retail




Lobbies

## Product specifications

- 3" Yolk-mounted Round Flatback Cylinder Track Head
- Die-cast Aluminum Finishes: Matte White, Matte Black, Aluminum Haze
- Tool-less adjustment: +/- 90° vertically; +/- 350° horizontally
- Lumens/Watts:
  - 1500 lm/12W
  - 1900 lm/15W
  - 2500 lm/20W
- Field-interchangeable Optics:
  - 24° Narrow Flood (pre-installed)
    - 17° Spot
    - 32° Flood
    - 3000K; 90+ CRI
- Compatible with HALO Power-trac and Lazer track
- Dims to 5% (phase cut LE/TE) with compatible dimmers; 120V input
- L70 at 50,000 hours (70% lumen maintenance at 50,000 hours)
- 5-year warranty



## Dimensional details



808E Essential



## Order Information

SAMPLE ORDER NUMBER: **L808E19NF930MB**

Track	Series	Output	Optic	CRI & CCT	Finish	Voltage
L=HALO Power Trac & Lazer Track	808E	15=1500 lm 19=1900 lm 25=2500 lm	NF=24° Narrow Flood Optic (pre-installed)	930=00K CCT; 90+ CRI	P=Matte White MB=Matte Black AH=Aluminum Haze	Blank=120V
<b>Notes</b>	<b>Notes</b>	<b>Notes</b>	<b>Notes</b>	<b>Notes</b>	<b>Notes</b>	<b>Notes</b>
Can be used in 1 & 2 circuit HALO Power-trac, and Lazer track system						

Accessories
<p><b>Interchangeable reflector optics</b></p> <p>808ECPKFL= 808E 32° Flood Optic 808ECPKSP= 808E 17° Spot Optic</p>
<p><b>Notes</b></p> <p>Fixtures ship with the 24° Narrow Flood optic pre-installed. Accessory optics are field-interchangeable. See installation instructions for details.</p>



### Lighting Brands

Ametrix  
AtLite  
Corelite  
Ephesus  
Fail-Safe  
HALO  
HALO Commercial  
Invue  
iO  
Iris  
Lumark  
LumarkAP  
Lumière  
McGraw-Edison  
Metalux  
MWS  
NeoRay  
Portfolio  
PrentaLux - 3D Printed Lighting  
RSA  
Shaper  
Streetworks  
Sure-Lites

### Controls Brands

Greengate  
Fifth Light  
Intelligent Lighting Controls

### Connected Lighting Systems and Smart Spaces Platform

WaveLinx  
Trellix Infrastructure



**Cooper Lighting Solutions**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.cooperlighting.com](http://www.cooperlighting.com)

Canada Sales  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2024 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. BR51802224EN  
August 22, 2024 5:48 PM

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.