

Lumark LAS Area / Site Luminaire


Features and Benefits

The Lumark LAS Area and Site luminaire provides automatic dusk-to-dawn area lighting for parking lots, walkways, and other outdoor areas. This high-efficiency LED luminaire delivers maximum energy savings while also lowering overall maintenance costs. The adjustable slipfitter arm mounts horizontally or vertically allowing for versatility in use and a simple installation.

PRODUCT FEATURES

- Heavy-duty, die-cast aluminum housing provides durability and reliability
- Efficacies up to 135 lumens per watt at maximum output
- Energy and maintenance savings up to 79% versus HID solutions

DESIGN FEATURES



Selectable lumen switch

10-position field-adjustable lumen output switch accessible via hinged luminaire door



Dusk-to-Dawn

Twistlock photocontrol provides automatic dusk-to-dawn operation for maximum energy savings



Pole Mount Arm

Pole mount directly to round or square poles



Slipfitter Arm

Vertical or horizontal pipe installation with adjustable tilt



LAS45



LAS100

QUICK FACTS

- Lumens packages ranging from 4,900 - 34,000 lumens
- 2 housing sizes
- 4000K CCT / 70 CRI minimum
- >126,000 hour lifetime



Lumark

LAS Area / Site Luminaire

Features and Benefits

STOCK ORDERING INFORMATION

Catalog Number	Catalog Number	HID Equivalent	Input Watts	Lumens	Efficacy (LPW)	Distribution	Voltage	UPC Code
Pole Mount	LAS45P-T3	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T3	UNV	080083248360
Pole Mount	LAS45P-T4	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T4	UNV	080083248384
Pole Mount	LAS45P-T5	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T5	UNV	080083248704
Pole Mount	LAS45P-T3-HV	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T3	347 / 480V	080083248728
Pole Mount	LAS45P-T4-HV	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T4	347 / 480V	080083248742
Pole Mount	LAS45P-T5-HV	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T5	347 / 480V	080083248766
Pole Mount	LAS100P-T3	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T3	UNV	080083248780
Pole Mount	LAS100P-T4	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T4	UNV	080083248803
Pole Mount	LAS100P-T5	450-1,000W	50 - 250W	8,200 - 34,000	135 - 173	T5	UNV	080083248827
Pole Mount	LAS100P-T3-HV	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T3	347 / 480V	080083248841
Pole Mount	LAS100P-T4-HV	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T4	347 / 480V	080083248865
Pole Mount	LAS100P-T5-HV	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T5	347 / 480V	080083248889
Slipfitter	LAS45S-T3	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T3	UNV	080083155804
Slipfitter	LAS45S-T4	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T4	UNV	080083155835
Slipfitter	LAS45S-T5	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T5	UNV	080083155842
Slipfitter	LAS45S-T3-HV	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T3	347 / 480V	080083155866
Slipfitter	LAS45S-T4-HV	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T4	347 / 480V	080083155941
Slipfitter	LAS45S-T5-HV	100 - 450W	30 - 150W	4,900 - 20,000	130 - 167	T5	347 / 480V	080083155965
Slipfitter	LAS100S-T3	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T3	UNV	080083155927
Slipfitter	LAS100S-T4	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T4	UNV	080083155880
Slipfitter	LAS100S-T5	450-1,000W	50 - 250W	8,200 - 34,000	135 - 173	T5	UNV	080083155903
Slipfitter	LAS100S-T3-HV	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T3	347 / 480V	080083155989
Slipfitter	LAS100S-T4-HV	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T4	347 / 480V	080083156009
Slipfitter	LAS100S-T5-HV	450 - 1,000W	50 - 250W	8,200 - 34,000	135 - 173	T5	347 / 480V	080083156023

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

© 2022 Cooper Lighting Solutions
All Rights Reserved
Publication No. SA514101EN
January 31, 2022 4:36 PM