

**FEATURES**

- Heavy-duty, 20-gauge steel housing
- White powder coat finish
- Dual voltage input 120/277 VAC, 60Hz
- Available in both 6 volt and 12 volt models
- Powerful incandescent lamping
- Dependable sealed lead calcium batteries

**ENERGY DATA**

See Specification Sheet for Energy Data

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

**COMPLIANCES:** UL924 Listed; Damp Location, NYC Code Compliant

## REL - STEEL EMERGENCY LIGHT

**ORDERING INFORMATION**

SAMPLE NUMBER: 6REL18


Voltage	Family	Capacity
6=6 Volt	REL=Rival Emergency Light	18=18 Watts (with (2) 9 Watt Heads) 27=27 Watts (with (2) 12 Watt Heads)

**ORDERING INFORMATION**

SAMPLE NUMBER: 12REL503

Voltage	Family	Capacity	Number of Heads
12=12 Volt	REL=Rival Emergency Light	50=50 Watts	3=(3) 12 Watt Heads

6REL18 / 6REL27



12REL50-3

