

E44 4" Trim Series

The E44 trims are offered in open, lens and lens wall wash in both round and square apertures. They are adjustable and feature 360° rotation, 35° tilt and when combined with various distribution lamps provide a broad range of optical distributions providing accent, task, wall washing / grazing and general area illumination.

Catalog #		Type
Project		
Comments		Date
Prepared by		

WAFER THIN TRIMS



The E44 wafer thin trims are used with the new construction housings. The 1.0 mm thin profile provides minimal ceiling presence.

Directional Open

- 1430** Conical Reflector
- 1431** Conical Baffle
- 1434** Round Pinhole
- 1435** Round Pinhole w/Oculus
- 1464** Square Pinhole
- 1465** Square Pinhole w/Oculus

Lens Wall Wash

- 1432** Angle Cut Conical Reflector
- 1436** Round Pinhole
- 1466** Square Pinhole

Directional Lens

- 1433** Conical Reflector
- 1437** Round Pinhole
- 1467** Square Pinhole

DIRECTIONAL OPEN



1430
Conical Reflector,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1430MWWF

Trim	Finish
1430 = 4" conical reflector, open, 35° tilt	BN =Brushed Nickel GB =German Bronze H =Haze HWF =Haze, White Flange MWWF =Matte White, White Flange



1431
Conical Baffle,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1431MBWF

Trim	Finish
1431 = 4" conical baffle, open, 35° tilt	BBWF =Black Baffle, White Flange BN =Brushed Nickel GB =German Bronze MBWF =White Baffle, White Flange



1434
Round Pinhole,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1434MW

Trim	Finish
1434 = 4" round pinhole, open, 35° tilt	BN =Brushed Nickel GB =German Bronze MW =Matte White



1435
Round Pinhole with Oculus,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1435MWWB

Trim	Finish
1435 = 4" round pinhole w/oculus, open, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle

DIRECTIONAL OPEN

1464
Square Pinhole,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1464MW

Trim	Finish
1464 = 4" square pinhole, open, 35° tilt	BN =Brushed Nickel GB =German Bronze MW =Matte White



1465
Square Pinhole w/Oculus,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1465MWWB

Trim	Finish
1465 = 4" square pinhole w/oculus, open, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle

LENS WALL WASH

1432
Angle Cut Conical Reflector,
Lens Wall Wash

ORDERING INFORMATION

SAMPLE NUMBER: 1432MWWF

Trim	Finish
1432 = 4" angle cut conical reflector, lens wall wash	H =Haze HWF =Haze, White Flange MWWF =Matte White, White Flange



1436
Round Pinhole,
Lens Wall Wash

ORDERING INFORMATION

SAMPLE NUMBER: 1436MWWB

Trim	Finish
1436 = 4" round pinhole, lens wall wash	MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle



1466
Square Pinhole,
Lens Wall Wash

ORDERING INFORMATION

SAMPLE NUMBER: 1466MWWB

Trim	Finish
1466 = 4" square pinhole, lens wall wash	MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle

DIRECTIONAL LENS



1433
Conical Reflector,
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1433MWWF

Trim	Finish
1433 = 4" conical reflector, diffuse lens, 35° tilt	H =Haze HWF =Haze, White Flange MWWF =Matte White, White Flange



1437
Round Pinhole,
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1437MWWB

Trim	Finish
1437 = 4" round pinhole, diffuse lens, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle



1467
Square Pinhole,
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1467MWWB

Trim	Finish
1467 = 4" square pinhole, diffuse lens, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle