

## E44 4" Trim Series

The E44 trims are offered in open, lens and lens wall wash in both round and square apertures. They are adjustable and feature 360° rotation, 35° tilt and when combined with various distribution lamps provide a broad range of optical distributions providing accent, task, wall washing / grazing and general area illumination. E26 medium base to GU10 adapter provided, useful in retrofitting H99 or compatible incandescent housings.

|             |  |      |
|-------------|--|------|
| Catalog #   |  | Type |
| Project     |  |      |
| Comments    |  | Date |
| Prepared by |  |      |

### FULL OVERLAP TRIMS



The E44 full overlap trims are used with both new construction and remodeler housings. The full overlap flange style trims match the ML4 trim series.

**Directional Open**  
**1440** Conical Reflector  
**1441** Conical Baffle  
**1444** Round Pinhole  
**1445** Round Pinhole w/Oculus  
**1484** Square Pinhole  
**1485** Square Pinhole w/Oculus

**Lens Wall Wash**  
**1442** Angle Cut Conical Reflector  
**1446** Round Pinhole  
**1486** Square Pinhole

**Directional Lens**  
**1443** Conical Reflector  
**1447** Round Pinhole  
**1449** Round All Acrylic-Glass  
**1487** Square Pinhole  
**1489** Square All Acrylic-Glass

### DIRECTIONAL OPEN



**1440**  
 Conical Reflector,  
 Open, 35° tilt

#### ORDERING INFORMATION

SAMPLE NUMBER: 1440MWWF

| Trim   | Finish  |
|--|---|
| <b>1440</b> = 4" conical reflector, open, 35° tilt | <b>BN</b> =Brushed Nickel<br><b>GB</b> =German Bronze<br><b>H</b> =Haze<br><b>HWF</b> =Haze, White Flange<br><b>MWWF</b> =Matte White, White Flange |



**1441**  
 Conical Baffle,  
 Open, 35° tilt

#### ORDERING INFORMATION

SAMPLE NUMBER: 1441MBWF

| Trim  | Finish  |
|---|---|
| <b>1441</b> = 4" conical baffle, open, 35° tilt | <b>BBWF</b> =Black Baffle, White Flange<br><b>BN</b> =Brushed Nickel<br><b>GB</b> =German Bronze<br><b>WBWF</b> =White Baffle, White Flange |



**1444**  
 Round Pinhole,  
 Open, 35° tilt

#### ORDERING INFORMATION

SAMPLE NUMBER: 1444MW

| Trim   | Finish  |
|--|---|
| <b>1444</b> = 4" round pinhole, open, 35° tilt | <b>BN</b> =Brushed Nickel<br><b>GB</b> =German Bronze<br><b>MW</b> =Matte White |




**1445**  
 Round Pinhole with Oculus,  
 Open, 35° tilt

#### ORDERING INFORMATION

SAMPLE NUMBER: 1445MWWB

| Trim  | Finish  |
|---|---|
| <b>1445</b> = 4" round pinhole w/oculus, open, 35° tilt | <b>BNBB</b> =Brushed Nickel, Black Baffle<br><b>GBBB</b> =German Bronze, Black Baffle<br><b>MWBB</b> =Matte White, Black Baffle<br><b>MWWB</b> =Matte White, White Baffle |

## DIRECTIONAL OPEN



**1484**  
Square Pinhole,  
Open, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1484MW

| Trim  | Finish  |
|---|---|
| <b>1484</b> = 4" square pinhole, open, 35° tilt | <b>BN</b> =Brushed Nickel<br><b>GB</b> =German Bronze<br><b>MW</b> =Matte White |



**1485**  
Square Pinhole w/Oculus,  
Open, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1485MWWB

| Trim   | Finish  |
|--|---|
| <b>1485</b> = 4" square pinhole w/oculus, open, 35° tilt | <b>BNBB</b> =Brushed Nickel, Black Baffle<br><b>GBBB</b> =German Bronze, Black Baffle<br><b>MWBB</b> =Matte White, Black Baffle<br><b>MWWB</b> =Matte White, White Baffle |

## LENS WALL WASH



**1442**  
Angle Cut Conical Reflector,  
Lens Wall Wash

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1442MWWF

| Trim  | Finish   |
|---|--|
| <b>1442</b> = 4" angle cut conical reflector,<br>lens wall wash | <b>H</b> =Haze<br><b>HWF</b> =Haze, White Flange<br><b>MWWF</b> =Matte White, White Flange |



**1446**  
Round Pinhole,  
Lens Wall Wash

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1446MWWB

| Trim   | Finish   |
|--|--|
| <b>1446</b> = 4" round pinhole, lens wall wash | <b>MWBB</b> =Matte White, Black Baffle<br><b>MWWB</b> =Matte White, White Baffle |



**1486**  
Square Pinhole,  
Lens Wall Wash

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1486MWWB

| Trim  | Finish   |
|---|--|
| <b>1486</b> = 4" square pinhole, lens wall wash | <b>MWBB</b> =Matte White, Black Baffle<br><b>MWWB</b> =Matte White, White Baffle |

## DIRECTIONAL LENS



**1443**  
Conical Reflector,  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1443MWWF

| Trim   | Finish   |
|--|--|
| <b>1443</b> = 4" conical reflector, diffuse lens, 35° tilt | <b>H</b> =Haze<br><b>HWF</b> =Haze, White Flange<br><b>MWWF</b> =Matte White, White Flange |



**1447**  
Round Pinhole,  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1447MWWB

| Trim   | Finish  |
|--|---|
| <b>1447</b> = 4" round pinhole, diffuse lens, 35° tilt | <b>BNBB</b> =Brushed Nickel, Black Baffle<br><b>GBBB</b> =German Bronze, Black Baffle<br><b>MWBB</b> =Matte White, Black Baffle<br><b>MWWB</b> =Matte White, White Baffle |



**1449**  
Round "All Acrylic-Glass",  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1449AAG

| Trim   | Finish                        |
|--|-------------------------------|
| <b>1449</b> = 4" round "all acrylic-glass", diffuse lens, 35° tilt | <b>AAG</b> =All Acrylic Glass |



**1487**  
Square Pinhole,  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1487MWWB

| Trim  | Finish  |
|---|---|
| <b>1487</b> = 4" square pinhole, diffuse lens, 35° tilt | <b>BNBB</b> =Brushed Nickel, Black Baffle<br><b>GBBB</b> =German Bronze, Black Baffle<br><b>MWBB</b> =Matte White, Black Baffle<br><b>MWWB</b> =Matte White, White Baffle |



**1489**  
Square "All Acrylic-Glass",  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1489AAG

| Trim  | Finish                        |
|---|-------------------------------|
| <b>1489</b> = 4" square "all acrylic-glass", diffuse lens, 35° tilt | <b>AAG</b> =All Acrylic Glass |