



Clean aesthetic
| No ceiling disruption

EXIT



SELMTG


The SELMTG60R5SD is an Architectural grade, recessed, T-Grid mounted emergency light. The 300 lumen LED source will cover up to 60 feet resulting in less total fixtures required. Also, the adjustable recessed heads eliminate the traditional unsightly emergency fixture look. The SELMTG60R5SD series has 5 watts of remote capacity which can create an additional 50 feet of emergency egress coverage. This product is UL924 listed and meets both City of Chicago and NYC construction requirements.

Feature	Benefit	Result
Recessed heads	No ceiling disruption; clean aesthetic	Peace of mind
LED source with nickel cadmium battery	No maintenance	Save money
Self-diagnostics	Reduced labor for NFPA and OSHA required testing	Save time
Up to 60 feet of emergency egress coverage	Less total fixtures required	Save money
Steel housing, 300 lumen/head LED output	UL924, New York and Chicago approved	Peace of mind
5 year fixture; 7 year prorated battery warranty	Certified and guaranteed performance	Peace of mind
5 watts of remote capacity	Up to 50 feet of additional coverage	Save money

Ordering Information

SAMPLE NUMBER:

Series	Housing	Spacing	Remote Capacity	Color	Self-diagnostics	Catalog Logic
SELM = Sure-Lites emergency, metal housing	TG = grid ceiling	60 = 60 Feet	R5 = 5 watts of remote capacity	_ = white BK = black	SD = self-diagnostics (standard)	SELMTG60R5SD SELMTG60R5BKSD



SELMTG

replaces



GC

Say "NO" to ugly emergency lighting.



T20 Certified to California
Title 20 Appliance Database