

**Note: HC6 and PD6 ARE NOT Interchangeable**

| PD6 Series Stock / Popular | NEW HC6 Series Equivalent Cross      |  |   |
|----------------------------|--------------------------------------|--|---|
| PD6 Catalog No.            | HC6 Catalog No.                      | HC6 Description  | Notes                                       |
| 61VC                       | 61NDC / 61MDC / 61WDC                | 6" Narrow / Medium / Wide Reflector Specular Clear                   | HC6 - Narrow/ Medium / Wide beam options    |
| 61VCWF                     | 61NDCWF / 61MDCWF / 61WDCWF          | 6" Narrow / Medium / Wide Reflector Specular Clear, White Flange     | HC6 - Narrow/ Medium / Wide beam options    |
| 61VEMC                     | 61NDCIEM / 61MDCIEM / 61WDCIEM       | 6" Narrow / Medium / Wide Reflector Specular Clear IEM               | HC6 - Narrow/ Medium / Wide beam options    |
| 61VEMCWF                   | 61NDCWFIEM / 61MDCWFIEM / 61WDCWFIEM | 6" Narrow / Medium / Wide Reflector Specular Clear, White Flange IEM | HC6 - Narrow/ Medium / Wide beam options    |
| 61VEMH                     | 61NDHIEM / 61MDHIEM / 61WDHIEM       | 6" Narrow / Medium / Wide Reflector Semi Specular IEM                | HC6 - Narrow/ Medium / Wide beam options    |
| 61VEMHWF                   | 61NDHWFIEM / 61MDHWFIEM / 61WDHWFIEM | 6" Narrow / Medium / Wide Reflector Semi Specular, White Flange IEM  | HC6 - Narrow/ Medium / Wide beam options    |
| 61VEMW                     | 61NDWIEM / 61MDWIEM / 61WDWIEM       | 6" Narrow / Medium / Wide Reflector Matte White IEM                  | HC6 - Narrow/ Medium / Wide beam options    |
| 61VEMWB                    | 61WDWBIEM                            | 6" Wide Reflector White Baffle IEM                                   | HC6 - Baffle is wide beam                   |
| 61VH                       | 61NDH / 61MDH / 61WDH                | 6" Narrow / Medium / Wide Reflector Semi Specular                    | HC6 - Narrow/ Medium / Wide beam options    |
| 61VHWF                     | 61NDHWF / 61MDHWF / 61WDHWF          | 6" Narrow / Medium / Wide Reflector Semi Specular, White Flange      | HC6 - Narrow/ Medium / Wide beam options    |
| 61VW                       | 61NDW / 61MDW / 61WDW                | 6" Narrow / Medium / Wide Reflector Matte White                      | HC6 - Narrow/ Medium / Wide beam options    |
| 61VWB                      | 61WDWB                               | 6" Wide Reflector White Baffle                                       | HC6 - Baffle is wide beam                   |
| 61VEMBB                    | 61WDDBIEM                            | 6" Wide Reflector Black Baffle IEM                                   | HC6 - Baffle is wide beam                   |
| 61VBB                      | 61WDDB                               | 6" Wide Reflector Black Baffle                                       | HC6 - Baffle is wide beam                   |
| 61WWC                      | 61RWWC                               | 6" Lens Wall Wash Reflector Specular Clear                           | HC6 - Rotatable Lensed Wall Wash            |
| 61WWCWF                    | 61RWWCWF                             | 6" Lens Wall Wash Reflector Specular Clear, White Flange             | HC6 - Rotatable Lensed Wall Wash            |
| 61WWH                      | 61RWWH                               | 6" Lens Wall Wash Reflector Semi Specular                            | HC6 - Rotatable Lensed Wall Wash            |
| 61WWHWF                    | 61RWWHWF                             | 6" Lens Wall Wash Reflector Semi Specular, White Flange              | HC6 - Rotatable Lensed Wall Wash            |
| 61WWW                      | 61RWWW                               | 6" Lens Wall Wash Reflector Matte White                              | HC6 - Rotatable Lensed Wall Wash            |
| PD56R10D010B               | HC56R10D010                          | HC56 Retrofit Housing 1000lm, UNV, 0-10V                             |   |
| PD56R10ED010               | HC56R10D010*                         | HC56 Retrofit Housing 1000lm, UNV, 0-10V                             | *HC6 cross PD6 Gen-A for 0-10V dimming only |
| PD56R15D010B               | HC56R15D010                          | HC56 Retrofit Housing 1500lm, UNV, 0-10V                             |   |

# HALO Commercial

New HC6 / PD6 Equivalent Crossover

| PD6 Series<br>Stock / Popular | NEW HC6 Series<br>Equivalent Cross |  |  |
|-------------------------------|------------------------------------|--|--|
| PD6 Catalog No.               | HC6 Catalog No.                    | HC6 Description                          | Notes  |
| PD56R20D010B                  | HC56R20D010                        | HC56 Retrofit Housing 2000lm, UNV, 0-10V |  |
| PD56R20ED010                  | HC56R20D010*                       | HC56 Retrofit Housing 2000lm, UNV, 0-10V | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD56R30D010                   | HC56R30D010                        | HC56 Retrofit Housing 3000lm, UNV, 0-10V |  |
| PD610D010B                    | HC610D010                          | 6" 1000lm, UNV, 0-10V                    |  |
| PD610ED010                    | HC610D010*                         | 6" 1000lm, UNV, 0-10V                    | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD615D010B                    | HC615D010                          | 6" 1500lm, UNV, 0-10V                    |  |
| PD615ED010                    | HC615D010*                         | 6" 1500lm, UNV, 0-10V                    | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD618ED010                    | HC620D010*                         | 6" 2000lm, UNV, 0-10V                    | *Use 2000lm for PD6 1800lm   |
| PD620D010B                    | HC620D010                          | 6" 2000lm, UNV, 0-10V                    |  |
| PD620ED010                    | HC620D010*                         | 6" 2000lm, UNV, 0-10V                    | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD630D010B                    | HC630D010                          | 6" 3000lm, UNV, 0-10V                    |  |
| PD630D010                     | HC630D010*                         | 6" 3000lm, UNV, 0-10V                    | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD6R10D010B                   | HC6R10D010                         | HC6 Retrofit Housing 1000lm, UNV, 0-10V  |  |
| PD6R10ED010                   | HC6R10D010*                        | HC6 Retrofit Housing 1000lm, UNV, 0-10V  | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD6R15D010B                   | HC6R15D010                         | HC6 Retrofit Housing 1500lm, UNV, 0-10V  |  |
| PD6R15ED010                   | HC6R15D010*                        | HC6 Retrofit Housing 1500lm, UNV, 0-10V  | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD6R20D010B                   | HC6R20D010                         | HC6 Retrofit Housing 2000lm, UNV, 0-10V  |  |
| PD6R20ED010                   | HC6R20D010*                        | HC6 Retrofit Housing 2000lm, UNV, 0-10V  | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD6R30D010B                   | HC6R30D010                         | HC6 Retrofit Housing 3000lm, UNV, 0-10V  |  |
| PD6R30D010                    | HC6R30D010*                        | HC6 Retrofit Housing 3000lm, UNV, 0-10V  | *HC6 cross PD6 Gen-A for 0-10V dimming only                          |
| PD6RX10D010B                  | HC6R10D010*                        | HC6 Retrofit Housing 1000lm, UNV, 0-10V  | * use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide |
| PD6RX15D010B                  | HC6R15D010*                        | HC6 Retrofit Housing 1500lm, UNV, 0-10V  | * use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide |
| PD6RX20D010B                  | HC6R20D010*                        | HC6 Retrofit Housing 2000lm, UNV, 0-10V  | * use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide |
| PD6RX30D010B                  | HC6R30D010*                        | HC6 Retrofit Housing 3000lm, UNV, 0-10V  | * use HC6R for retrofit of earlier PD6H/PD6V CFL or PD6 Metal Halide |

# HALO Commercial

New HC6 / PD6 Equivalent Crossover

| PD6 Series Stock / Popular | NEW HC6 Series Equivalent Cross |  |  |
|----------------------------|---------------------------------|--|--|
| PD6 Catalog No.            | HC6 Catalog No.                 | HC6 Description  | Notes  |
| PDM6A827                   | HM612827 / HM634827             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 2700K | HC6 -LED module - determined by housing lumens             |
| PDM6A830                   | HM612830 / HM634830             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3000K | HC6 -LED module - determined by housing lumens             |
| PDM6A835                   | HM612835 / HM634835             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3500K | HC6 -LED module - determined by housing lumens             |
| PDM6A840                   | HM612840 / HM634840             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 4000K | HC6 -LED module - determined by housing lumens             |
| PDM6A927                   | HM612927 / HM634927             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 2700K | HC6 -LED module - determined by housing lumens             |
| PDM6A930                   | HM612930 / HM634930             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3000K | HC6 -LED module - determined by housing lumens             |
| PDM6930                    | HM612930 / HM634930             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3000K | HC6 -LED module - determined by housing lumens             |
| PDM6935                    | HM612935 / HM634935             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3500K | HC6 -LED module - determined by housing lumens             |
| PDM6A935                   | HM612935 / HM634935             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3500K | HC6 -LED module - determined by housing lumens             |
| PDM6A940                   | HM612940 / HM634940             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 4000K | HC6 -LED module - determined by housing lumens             |
| PDM6B827                   | HM612827 / HM634827             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 2700K | HC6 -LED module - determined by housing lumens             |
| PDM6B830                   | HM612830 / HM634830             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3000K | HC6 -LED module - determined by housing lumens             |
| PDM6B835                   | HM612835 / HM634835             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 3500K | HC6 -LED module - determined by housing lumens             |
| PDM6B840                   | HM612840 / HM634840             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 80CRI 4000K | HC6 -LED module - determined by housing lumens             |
| PDM6B927                   | HM612927 / HM634927             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 2700K | HC6 -LED module - determined by housing lumens             |
| PDM6B930                   | HM612930 / HM634930             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3000K | HC6 -LED module - determined by housing lumens             |
| PDM6B935                   | HM612935 / HM634935             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 3500K | HC6 -LED module - determined by housing lumens             |
| PDM6B940                   | HM612940 / HM634940             | 6" Module 12 = 1000-1500-2000lm / 34 = 3000-4000lm 90CRI 4000K | HC6 -LED module - determined by housing lumens             |
| 64VC - shallow trim        | N/A                             |  | HC6 - use 1000-1500-2000lm module for shallow applications |
| 64VCWF - shallow trim      | N/A                             |  | HC6 - use 1000-1500-2000lm module for shallow applications |
| 64VDFW - shallow trim      | N/A                             |  | HC6 - use 1000-1500-2000lm module for shallow applications |
| 64VH - shallow trim        | N/A                             |  | HC6 - use 1000-1500-2000lm module for shallow applications |
| 64VHWF - shallow trim      | N/A                             |  | HC6 - use 1000-1500-2000lm module for shallow applications |
| 64VW - shallow trim        | N/A                             |  | HC6 - use 1000-1500-2000lm module for shallow applications |