

Project		Catalog #		Type	
Prepared by		Notes		Date	



Ephesus

Slip Fitter

Tenon Mounting for Round Pole

Typical Applications

- Professional Indoor Stadiums & Arenas
- University/Collegiate Indoor Stadiums & Arenas
- Public Assembly & Convention Centers
- Gymnasiums & Field Houses

Product Certification



SLIP FITTER (SLPFTR) SHOWN WITH LUMASPORT 8 - INTEGRAL LUMINAIRE ATTACHED
LUMINAIRE SOLD SEPARATELY

Interactive Menu

- [Ordering Information](#) page 2
- [Dimensional Details](#) page 3

Compatible Ephesus Luminaires

- LUMASPORT 8 - INTEGRAL
- LUMASPORT 8 - REMOTE
- LUMASPORT 8 PRISM - LOCAL
- LUMASPORT 8 PRISM - REMOTE
- LUMAVISION



Ordering Information for Accessories

NOTE: A complete accessory order requires a selection entry for **Brand, Accessory, Mounting Type, & Coating**.

SAMPLE ORDER NUMBER: **EPH-SLPFTR-025-B**


Brand	Accessory	Mounting Type	Coating	Intended Use
EPH = Ephesus, Standard TAA =Trade Agreements Act ¹	SLPFTR = Slip Fitter	025 = .25in Bracket ² 075 = .75in Bracket ³	B = Black Powder Coating	Slip Fitter Bracket is intended to be used to mount luminaires to a tenon / pole mount with 2 3/8in, 3in or 3 1/2in outer diameters. Designed to attach the LUMASPORT 8 - INTEGRAL , LUMASPORT 8 - LOCAL , LUMASPORT 8 - REMOTE , LUMASPORT 8 PRISM - LOCAL , LUMASPORT 8 PRISM - REMOTE , & LUMAVISION luminaires only to a round pole top.
Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.		Notes: (2) The LUMASPORT 8 - Local and LUMASPORT 8 PRISM - Local luminaires utilize the .75in (075) mounting type. (3) When installing with an Ephesus pendant or remote mounting brackets utilize the .25in (025) mounting type.		

Slip Fitter Dimensional Details



Configuration Physical Dimensions¹


CONFIGURATION	WEIGHT (lbs)
Slip Fitter	4.68
Notes: (1) Weights +/-2lbs	



Slip Fitter Parts¹

ITEM NO.	DESCRIPTION	QUANTITY
1	SLIP FITTER CASTING ² ³	1
2	1/2-13 x 1.75in, SS, CUP POINT SET	8
3	1/2in-13, SS, THIN HEX NYLON-INSERT NUT	8
4	3/8in-16 X 5-1/2in, SS, HEX HEAD SCREW	1
5	3/8in-16, SS, NYLON INSERT LOCKNUT	1
6	3/8in SS, WASHER	4
7	3/8in-16 X 1-1/8in OR 1-5/8in, SS, HEX HEAD SCREW WITH PATCH	4

MOUNTING BOLT TYPES



¹Parts Listed for the EPH-SLPFTR-075-B configuration

²The LUMASPORT 8 and PRISM RGBA luminaires utilize the .75in (075) mounting type.

³When installing with an Ephesus pendant or remote mounting brackets utilize the .25in (025) mounting type.