

Architectural Linear LED


Lines of Light

Metalux | Corelite | Neo-Ray

Market focused portfolio with products designed for broad applications

Value - competitive prices with industry leading DLC listings

Performance - market leading performance with connected sensors options delivering value beyond lumens per watt



Whether lighting contemporary architectural spaces or general area lighting, **Cooper Lighting Solutions' architectural linear LED** products offer a complete family of innovative, affordable, and energy saving LED solutions for your next project.

		Good	Better	Best		
		Click on products to learn more				
APPLICABILITY*	Office	★★	★★	★★	★★★	★★★
	Secondary Education	★★	★★	★★	★★★	★★
	Primary Education	★★★	★★★	★★★	★★	★
	Healthcare	★★	★	★	★★	★★★
	Tenant Improvement	★★★	★★★	★★★	★★	★
	FEATURES / PERFORMANCE					
	Apertures	4"	3"	2", 4"	1.5", 2", 3", 4", 5"	1.5", 2", 3", 4", 5"
	Sizes	Fixed 2', 4', 8'	4', 8'	4', 8' + Continuous Runs	2'-12' + Continuous Runs	2'-12' + Continuous Runs
	Length Resolution	Fixed	Fixed	4' Increments	1" Increments	1" Increments
	Installation Type	Ceiling, Wall	Ceiling	Ceiling	Ceiling, Wall, Perimeter	Ceiling, Wall, Perimeter
	Configuration Geometry	Straight	Straight	Straight	Straight, Corners, Intersection	Straight, Corners, Intersection
	Compatible Family Fixtures	Surface/Susp & Drywall Kits	N/A	N/A	Suspended, Surface, Wall	Suspended, Surface, Wall
	lm/W (Max)	115	121	124	127	141
	Lms/ft (Max)	1,000	1,000	1,200	1,400	1,500
	Standard Lumen Levels	3	4	5	5 + Custom	5 + Custom
	Lens	Flush Frosted	Flush Frosted, Asymmetric	Flush Frosted, Asymmetric	Flush & Drop Frosted, Asymmetric, Louver	Flush & Drop Frosted, Asymmetric, Louver
	Emergency	Integrated, Remote Switch	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80 Standard, 90 Optional	80 Standard, 90 Optional	80 Standard, 90 Optional	80 Standard, 90 Optional
	Ceiling Integration / Flange Type	Standard T-Grid, Gypsum	Standard T-Grid, Gypsum	6 Common Architectural Systems	>12 Architectural Ceiling Systems	>12 Architectural Ceiling Systems
	DLC	Standard	Standard	Standard	Standard & Premium	Standard & Premium
	VividTune™	No	No	No	No	Tunable White
INTEGRATED CONTROLS	WaveLinx, Enlighted, DLVP, Stand Alone	Integrated or Tile Mount	Integrated	Integrated	Integrated or Tile Mount	Integrated or Tile Mount
	Integral Downlights	N/A	N/A	N/A	Optional Fixed or Adjustable	Optional Fixed or Adjustable

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2021 Cooper Lighting Solutions
All Rights Reserved
Publication No. SA519058EN-web
November 2, 2021 11:52 AM

Cooper Lighting Solutions is a registered trademark.
All other trademarks are property of their respective owners.
Product availability, specifications, and compliances are subject to change without notice.