

## E26 6" Trim Series


### DESCRIPTION

Open wet location, shallow reflector trim with self-flange in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- Open wet location shallow showerlight for PAR30S and PAR38 outdoor rated lamps ONLY
- Torsion spring retention
- Socket supporting cone
- Self-flanged trim ring sized to hide gaps caused by construction tolerances



Lamp Gasket (included)



#### Dimensions:


- A: 5-3/8" [136mm]
- D: 7/8 [22mm]
- H: 4-7/8" [123mm]
- OD: 7-3/4" [197mm]

Housings	Max Lamp Compatibility
H7ICT H7ICAT	
H7RICT H7RICAT	75W PAR30S, 75W PAR30L, 80W PAR38
E7ICAT E7RICAT	
H7UICAT	75W PAR30S, 75W PAR30L, 90W PAR38
H7ICTNB H7ICATNB E7ICATNB	75W PAR30S, 75W PAR30L, 80W PAR38
H27ICAT H27RICAT	E27ICAT E27RICAT 75W PAR30S, 75W PAR30L, 80W PAR38
H7T H7TCP H7RT	E7TAT E7RTAT 75W PAR30S, 75W PAR30L, 150W PAR38
H7TNB	E7TATNB 75W PAR30S, 75W PAR30L, 150W PAR38
H27T	E27TAT 150W PAR38, 75W PAR30S, 75W PAR30L
H27RT	E27RTAT 90W PAR38, 75W PAR30S, 75W PAR30L


Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.



**6145WH**  
White Shallow Reflector



**6145SN**  
Satin Nickel Shallow Reflector



**6145TBZ**  
Tuscan Bronze Shallow Reflector

## 6145

6-Inch Open Wet Location, Shallow Reflector, Self-flange



### ORDERING INFORMATION

SAMPLE NUMBER: 6145WH

Trim	Finish
6145= 6" Open Wet Location, Shallow Reflector, Self-flange	WH=White trim SN=Satin nickel trim TBZ=Tuscan bronze trim

### HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
6145	Open Showerlight	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		•	•	•	•	•	•		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
•	•	•	•	•	•	•	•		
		H27RT	E27TAT	E27RTAT					
•	•	•							

For use in select other's housings, refer to U.L. classification list at [www.cooperlighting.com](http://www.cooperlighting.com).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.