

Metalux

Surround

Selectable
Drop Lens LED

Another **winning innovation** from Metalux.



Scan for more.



5-4-3-2-1...GO!

5

Sizes

- 1' x 2'
- 1' x 4'
- 1' x 8'
- 2' x 2'
- 2' x 4'

4

Selectable CCT

- 3000K
- 3500K
- 4000K
- 5000K

3

Selectable Lumens

- Low
- Medium
- High

2

Applications

- Recessed
- Suspended

1


Remote Mounted Driver

- 0-10V dimming to 5%

Commercial Office Spaces • Education • Healthcare • Retail • Hospitality



Sizes



Features		Benefits
Construction	Thoughtful wire management	ACT tiles do not need to be cut to fit on top. Wire preset to the edge and fits between the tile and the grid.
	Two piece installation	Install driver on grid and simply plug into the luminaire. No luminaire assembly required.
	Recessed and Suspended	One solution, two applications offering a unique look for your space
	5 form factors available	Mix and match shapes, enabling design freedom in education, office and retail spaces
Performance	80+ CRI w/ 4 Color Temperatures	Designed with confidence - 3000K, 3500K, 4000K and 5000K CCT meet 94% of commercial CCT specifications
	Linear lens prisms	Lens prisms increase light on surrounding surfaces to reduce glare
	Up to 149 LPW	Energy savings vs. traditional and other LED sources as well as DLC Premium rebates
	3 selectable lumen levels	Designed with confidence and delivers the foot candles required

Stock is available in the following catalog numbers:

Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
12SFS-L3C4-UNV	1x2 Surround	(2) T8 17W	3000/3500 4000/5000	120-277	1500-3600	12-28	080083293100	S-MST08Y
14SFS-L3C4-UNV	1x4 Surround	(2) T8 17W	3000/3500 4000/5000	120-277	1900-4600	15-36	080083293162	S-L3V6F0
18SFS-L3C4-UNV	1x8 Surround	(4) T8 32W	3000/3500 4000/5000	120-277	4400-8500	31-60	080083293186	S-V8WFF7
22SFS-L3C4-UNV	2x2 Surround	(2) T8 32W U-Lamp	3000/3500 4000/5000	120-277	1900-4600	15-36	080083293124	S-KD7QF8
24SFS-L3C4-UNV	2x4 Surround	(3) T8 32W	3000/3500 4000/5000	120-277	3000-6100	23-47	080083293148	S-S46X0S

