

Project		Catalog #		Type	
Prepared by		Notes		Date	



# HALO

## HL36A | TL3

### 3" Shallow Directional New Construction LED Housing and Trims

#### Typical Applications

Residential, Light Commercial

#### Interactive Menu

- Order Information page 2
- Product Specifications page 4
- Photometric Data page 5
- Energy & Performance Data page 3
- Dimming Guide
- Product Warranty

#### Top Product Features

- Broad range of trims, distribution can easily be changed in the field
- Optional adapter allows rimless installation
- Interchangeable 15°, 25°, 40° and 55° LED optics provide focus
- Flicker-free dimming down to 1%, available with LE/TE phase cut and 0-10V analog control
- Locking 365° rotation and 45° tilt holds any aiming position
- Options to meet Trade Agreements Act requirements

#### Product Certification





Refer to ENERGY STAR® Certified Products List.  
Can be used to comply with California Title 24 High Efficacy requirements.  
Certified to California Appliance Efficiency Database under JAB.

#### Product Features



#### Dimensional and Mounting Details










Note: For use in shallow ceilings with 2" x 6" joist construction.

## Order Information







SAMPLE ORDER NUMBER: **HL36A20927ED010ICAT, TIR45SP15, TL3RMW**

A complete luminaire consists of a housing, TIR optic, and trim.




Domestic Preferences	Models	Wattage	Distribution	Light Engine	Input/Control	Housing Type	Accessories
Domestic Preferences <sup>(1)</sup>	Models	Wattage	Distribution <sup>(2)</sup>	Light Engine	Input/Control	Housing Type	Accessories <sup>(4)</sup>
<b>[Blank]</b> =Standard <b>TAA</b> =Trade Agreements Act	<b>HL36A</b> = 3" shallow new construction directional housing	<b>10</b> = 10W (nominal) <b>15</b> = 15W (nominal) <b>20</b> = 20W (nominal)	<b>[blank]</b> = Purchase optic separately	<b>927</b> = 90 CRI, 2700K <b>930</b> = 90 CRI, 3000K <b>935</b> = 90 CRI, 3500K <b>940</b> = 90 CRI, 4000K <b>D2W</b> = 90 CRI, 3000K CCT, dim to warm <sup>(3)</sup>	<b>ED010</b> = UNV 120-277V 50/60Hz leading or trailing edge phase cut 1% dimming at 120V only and UNV 120-277V 50/60Hz 0-10V 1% dimming <b>TELTE</b> = Lutron® Hi-Lume Forward Phase Dimming, 1% to 100%, 120V Only <b>DE010</b> = 0-10V Dimming, 0% to 100%, 120V-277V	<b>ICAT</b> = insulation contact and airtight	<b>RA3R</b> = rimless adapter for HL36A housings and trims <b>CE3R</b> = collar extender for HL36A housings, adjusts from 7/8" to 1-1/4" thick ceilings <b>OTL3MW</b> = oversized trim ring for TL3 trims  <b>Optics</b> <b>TIR45SP15</b> = 15° beam <b>TIR45NFL25</b> = 25° beam <b>TIR45FL40</b> = 40° beam <b>TIR45WFL55</b> = 55° beam <b>TIR45MH12PK</b> = replacement media holder, package of 12 <b>L100 Series</b> = 2.0" lens and filters, see spec sheet
<b>Notes</b> <small>(1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to <a href="#">DOMESTIC PREFERENCES</a> website for more information. Components shipped separately may be separately analyzed under domestic preference requirements...</small>	<b>Notes</b>	<b>Notes</b>	<b>Notes</b> <small>(2) Add necessary optic as an accessory.</small>	<b>Notes</b> <small>(3) Only available in 10W and 15W</small>	<b>Notes</b>	<b>Notes</b>	<b>Notes</b> <small>(4) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.</small>

Trim	Shielding	Finishes	Flange
 <b>TL3PIN</b> = 2.00" aperture pinhole w/oculus, open, self-flanged	<b>[blank]</b> = open	<b>Electroplated Finishes</b> <b>BNBB</b> = brushed nickel flange, black oculus <b>ORBBB</b> = oil rubbed bronze flange, black oculus  <b>Painted Finishes</b> <b>MWWB</b> = matte white flange, white oculus <b>MWBB</b> = matte white flange, black oculus <b>MBBB</b> = matte black flange, black oculus	<b>[blank]</b> = full overlap self-flanged
 <b>TL3PIN</b> = 2.00" aperture pinhole w/oculus, open, rimless	<b>[blank]</b> = open	<b>Painted Finishes</b> <b>MWWB</b> = matte white flange, white oculus	<b>RL</b> = rimless, must be used with rimless adapter ordered separately
 <b>TL3PIN</b> = 2.00" aperture pinhole w/oculus, lens, self-flanged	<b>2G</b> = micro-prismatic lens	<b>Electroplated Finishes</b> <b>BNBB</b> = brushed nickel flange, black oculus <b>ORBBB</b> = oil rubbed bronze flange, black oculus  <b>Painted Finishes</b> <b>MWWB</b> = matte white flange, white oculus <b>MWBB</b> = matte white flange, black oculus <b>MBBB</b> = matte black flange, black oculus	<b>[blank]</b> = full overlap self-flanged
 <b>TL3PIN</b> = 2.00" aperture pinhole w/oculus, lens, rimless	<b>2G</b> = micro-prismatic lens	<b>Painted Finishes</b> <b>MWWB</b> = matte white flange, white oculus	<b>RL</b> = rimless, must be used with rimless adapter ordered separately
 <b>TL3R</b> = 3.25" aperture conical reflector, open, self-flanged	<b>[blank]</b> = open	<b>Anodized Finishes</b> <b>H</b> = semi-specular clear reflector and flange <b>HWF</b> = semi-specular clear reflector and matte white flange  <b>Electroplated Finishes</b> <b>BN</b> = brushed nickel reflector and flange <b>ORB</b> = oil rubbed bronze reflector and flange  <b>Painted Finishes</b> <b>MW</b> = matte white reflector and flange <b>MB</b> = matte black reflector and flange	<b>[blank]</b> = full overlap self-flanged
 <b>TL3R</b> = 3.25" aperture conical reflector, open, rimless	<b>[blank]</b> = open	<b>Painted Finishes</b> <b>MW</b> = matte white reflector and flange	<b>RL</b> = rimless, must be used with rimless adapter ordered separately
 <b>TL3R</b> = 3.25" aperture conical reflector, open, self-flanged	<b>2G</b> = micro-prismatic lens	<b>Anodized Finishes</b> <b>H</b> = semi-specular clear reflector and flange <b>HWF</b> = semi-specular clear reflector and matte white flange  <b>Electroplated Finishes</b> <b>BN</b> = brushed nickel reflector and flange <b>ORB</b> = oil rubbed bronze reflector and flange  <b>Painted Finishes</b> <b>MW</b> = matte white reflector and flange <b>MB</b> = matte black reflector and flange	<b>[blank]</b> = full overlap self-flanged

## Order Information

	Trim	Shielding	Finishes	Flange
	<b>TL3R</b> = 3.25" aperture conical reflector, open, rimless	<b>2G</b> = micro-prismatic lens	<u>Painted Finishes</u> <b>MW</b> = matte white reflector and flange	<b>RL</b> = rimless, must be used with rimless adapter ordered separately
	<b>TL3R</b> = 3.25" aperture conical baffle, open, self-flanged	<b>[blank]</b> = open	<u>Painted Finishes</u> <b>BBWF</b> = matte black baffle, matte white flange <b>WBWF</b> = matte white baffle, matte white flange	<b>[blank]</b> = full overlap self-flanged
	<b>TL3R</b> = 3.25" aperture conical baffle, open, self-flanged	<b>2G</b> = micro-prismatic lens	<u>Painted Finishes</u> <b>BBWF</b> = matte black baffle, matte white flange <b>WBWF</b> = matte white baffle, matte white flange	<b>[blank]</b> = full overlap self-flanged
	<b>TL3PR</b> = 3.25" aperture conical polymer reflector, lens, self-flanged	<b>2G</b> = micro-prismatic lens	<u>Painted Finishes</u> <b>MW</b> = matte white reflector and flange	<b>[blank]</b> = full overlap self-flanged
	<b>TL3LWW</b> = 3.25" aperture conical lens wall wash, self-flanged	<b>6G</b> = linear spread lens	<u>Anodized Finishes</u> <b>H</b> = semi-specular clear reflector and flange <b>HWF</b> = semi-specular clear reflector and matte white flange <u>Painted Finishes</u> <b>MW</b> = matte white reflector and flange	<b>[blank]</b> = full overlap self-flanged
	<b>TL3LWW</b> = 3.25" aperture conical lens wall wash, rimless	<b>6G</b> = linear spread lens	<u>Painted Finishes</u> <b>MW</b> = matte white reflector and flange	<b>RL</b> = rimless

Lens trims are wet location listed, covered ceilings only and IP44 rated.

Accessory				
	<b>RA3R</b> = Rimless adapter for HL3xR housings and trims			
	<b>CE3R</b> = Collar extender for HL3xR housings, adjusts from 7/8" to 1-1/4" thick ceilings			
	<b>OTL3MW</b> = 3" Oversized trim ring, matte white			

## Energy Data

### ED010 Driver

Input Voltage	120V	277V
Input Current	0.17 (A)	0.08 (A)
Input Power	19.5 (W)	19.4 (W)
Inrush (A)	6.2 (A)	13.8 (A)
THD	≤ 20%	≤ 20%
PF	≥ 0.90	≥ 0.90
T Ambient	-40 - +40°C	-40 - +40°C
Sound Rating	≤ 22dba	≤ 22dba

### 1ELTE Driver

Input Voltage	120V
Input Current	0.19 (A)
Input Power	21.8 (W)
Inrush (A)	1.15 (A)
THD	≤ 20%
PF	≥ 0.90
T Ambient	-40 - +40°C
Sound Rating	≤ 22dba

### DE010 Driver

Input Voltage	120V	277V
Input Current	0.17 (A)	0.09 (A)
Input Power	19.8 (W)	20.6 (W)
Inrush (A)	1.1 (A)	2.5 (A)
THD	≤ 20%	≤ 20%
PF	≥ 0.90	≥ 0.90
T Ambient	-40 - +40°C	-40 - +40°C
Sound Rating	≤ 22dba	≤ 22dba

## Product Specifications

### Frame

- Galvanized steel plaster frame with integral bar hanger receivers
- Setscrew provide positive horizontal locking
- Collar adjusts vertically to accommodate 1/2" to 7/8" thick ceilings and locks in position with (4) screws
- Use optional collar extender for 7/8" to 1-1/4" thick ceilings
- Integral gun sights facilitate the use of guide strings or laser lines
- Shipped with overspray protector installed

### Housing

- Steel housing painted matte black for a visually dark interior
- Removable top allows service from above

### Bar Hangers

- GOT NAIL! Gen 3 bar hangers adjust from 10-1/2" to 24" wide
- Captive nail penetrates standard and engineered lumber
- Mounting flange levels platform with ceiling
- Integral clip attaches directly to tee-bar

### Gaskets

- Gaskets achieve restrictive airflow requirements without additional caulking

### Adjustment Mechanism

- Rotates 365°, tilts 45° and locks in position maintaining any aiming angle
- Angle markings assist in repeatable settings
- Translating center beam optics aligns axis of primary reflector with aperture from nadir to 45°

### Trim Retention

- Attached by (8) rare earth Neodymium magnets, holds trim securely to the ceiling
- Tether secures trim to housing during service or adjustment

### LED Module

- LED array is field replaceable
- Proximity phosphors over chip on board LEDs provide a uniform source with high efficiency and no pixilation
- Color accuracy within 3 SDCM and 90 CRI minimum
- Passive cooling achieves L70 at 50,000 hours

### Primary Optic

- Precision molded TIR optics deliver highly efficient and uniform patterns
- Various patterns are available and can be interchanged without tools

### Media

- Integral media holder accepts up to (2) 2" diameter 3.0mm thick color filters or lens
- Order color filters and lens separately

### Trims

- Die cast aluminum trims are available in open, lens and lens wall wash styles
- Polymer non-conductive trim meets many local code requirements for 'dead front'
- Physical and optical cutoff provides visual comfort
- Light trap eliminates spill light with flange
- Multiple finishes to match many décors
- Available in self-flanged or rimless styles with optional rimless adapter

### Shielding

- Micro-prismatic lens standard with lens trims
- Hinged to allow rimless trim removal

### Driver

- Field replaceable constant current driver provides noise free operation
- UNV 120-277VAC 50/60Hz input
- Continuous, flicker-free 1% dimming, available with LE and TE phase cut (at 120V only) and 0-10V analog control

### Junction Box

- Galvanized steel junction box with 18in3 internal volume
- Listed for (12) #12 AWG 90° C splice conductors
- (7) 1/2" conduit pry-outs positioned to allow straight conduit runs
- (3) Slide-N-Side™ non-metallic (NM) wire traps
- Accepts 14-2, 14-3, 12-2, 12-3 U.S. and 14-2, 14-3, 12-2 Canadian NM cable
- (3) 4-port push wire nuts mains voltage connections

### Compliance

- Type IC inherently protected, suitable for direct contact to air permeable insulation and cULus listed for damp locations
- Not for use in direct contact with spray foam insulation, consult NEMA LSD57-2013
- Wet location listed in covered ceilings. Housing is IP20 certified and when installed with a lens trim IP55 certified below the ceiling in covered ceiling applications only
- Airtight per ASTM-E283-04
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy LED compliance under JA8, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2016 JA8 High Efficacy Lighting
- ENERGY STAR® certified, reference certified light fixtures database

### Warranty

- Five year limited warranty, consult website for details. [www.cooperlighting.com](http://www.cooperlighting.com)

## Photometric Data - Multiplier Tables

### Wattage Multipliers

Wattage	10W	15W	20W
Multiplier	0.520883275	0.736897133	1.00000

Multipliers for relative lumen values with other wattage options.

### CCT Multipliers

CCT	D2W	2700K	3000K	3500K	4000K
Multiplier	0.49733	0.93842	1.00000	1.05535	1.07038

Multipliers for relative lumen values with other color temperatures.

### Driver Multipliers

Driver	ED010	DE010	1ELTE
Multiplier	1.00000	1.00000	1.02108

Multipliers for relative lumen values with other driver options.

### Color Finish Multipliers when tilted at 30°

Trim	TL3R			TL3LWW & TL3PIN
	BN	ORB, MB, BBWF	H, HWF, MW, WBWF	N/A
Multiplier	0.95800	0.97000	1.00000	Trim is not exposed to direct light

Multipliers for relative lumen values with other color finish options.

### Optic Details



Optic	BEAM	FIELD	LUMENS	LPW	CBCP
SP	16.8	30.5	1644	84	15266
NFL	26.1	43.4	1765	91	8046
FL	38.9	57.8	1754	90	4177
WFL	53.9	79.3	1609	83	2065

Photometric performance for TL3RWBWF 3000K CCT

## Photometric Data - Spot



View IES files

SUMMARY TABLE	
Filename	HL36A20SP930ED010TL3RMW.ies
Test No.	P284171
Lumcat	HL36A20SP930ED010TL3RMW
Lumens	1644 Lm
Watts	19.5 W
LPW	84.3 Lm/W
CCT	3000K
SC (0/90/45)	0.29 / 0.29 / 0.28





CONE OF LIGHT													
0 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Vertical Illuminance on Wall					
MH	FC	L	W	MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	753.9	1.2	1.2	4.5'	463.7	1.6	1.4	2.6	3'	241.2	2.5	1.6	5.2
5.5'	504.7	1.4	1.4	5.5'	310.4	1.9	1.8	3.2	4'	135.7	3.4	2	6.9
6.5'	361.3	1.8	1.8	6.5'	222.3	2.4	2.2	3.8	6'	60.3	5.1	3.2	10.4
8'	238.5	2.2	2.2	8'	146.7	2.9	2.6	4.6	8'	33.9	6.8	4.2	13.9
10'	152.7	2.8	2.8	10'	93.9	3.7	3.4	5.8	10'	21.7	8.5	5.4	17.3
12'	106	3.4	3.4	12'	65.2	4.5	4	6.9	12'	15.1	10.3	6.4	20.8

SUMMARY TABLE	
Filename	HL36A20SP930ED010TL3R2GMW.ies
Test No.	P284170
Lumcat	HL36A20SP930ED010TL3R2GMW
Lumens	1553 Lm
Watts	19.5 W
LPW	79.6 Lm/W
CCT	3000K
SC (0/90/45)	0.31 / 0.31 / 0.31





CONE OF LIGHT													
0 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Vertical Illuminance on Wall					
MH	FC	L	W	MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	588.9	1.2	1.2	4.5'	314.6	1.8	1.6	2.6	3'	163.8	2.9	1.6	5.2
5.5'	394.2	1.6	1.6	5.5'	210.6	2.2	2	3.2	4'	92.1	4	2.2	6.9
6.5'	282.2	2	2	6.5'	150.8	2.6	2.2	3.8	6'	41	5.9	3.4	10.4
8'	186.3	2.4	2.4	8'	99.5	3.2	2.8	4.6	8'	23	8	4.6	13.9
10'	119.2	3	3	10'	63.7	4	3.6	5.8	10'	14.7	10	5.8	17.3
12'	82.8	3.6	3.6	12'	44.2	4.7	4.2	6.9	12'	10.2	12	7	20.8

SUMMARY TABLE	
Filename	HL36A20SP930ED010TL3PINMWWB.ies
Test No.	P284169
Lumcat	HL36A20SP930ED010TL3PINMWWB
Lumens	1539 Lm
Watts	19.5 W
LPW	78.9 Lm/W
CCT	3000K
SC (0/90/45)	0.29 / 0.29 / 0.28



CONE OF LIGHT													
0 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Vertical Illuminance on Wall					
MH	FC	L	W	MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	754	1.2	1.2	4.5'	450.6	1.5	1.4	2.6	3'	243.8	2.4	1.4	5.2
5.5'	504.8	1.4	1.4	5.5'	301.6	1.9	1.8	3.2	4'	137.1	3.2	2	6.9
6.5'	361.4	1.8	1.8	6.5'	216	2.2	2	3.8	6'	60.9	4.8	3	10.4
8'	238.6	2.2	2.2	8'	142.6	2.8	2.6	4.6	8'	34.3	6.5	4	13.9
10'	152.7	2.8	2.8	10'	91.2	3.5	3.2	5.8	10'	21.9	8.1	5	17.3
12'	106	3.4	3.4	12'	63.4	4.2	3.8	6.9	12'	15.2	9.7	6.2	20.8

SUMMARY TABLE	
Filename	HL36A20SP930ED010TL3PIN2GMWWB.ies
Test No.	P284168
Lumcat	HL36A20SP930ED010TL3PIN2GMWWB
Lumens	1413 Lm
Watts	19.5 W
LPW	72.5 Lm/W
CCT	3000K
SC (0/90/45)	0.31 / 0.31 / 0.31





CONE OF LIGHT													
0 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Horizontal Illuminance on Floor				30 deg Aiming Angle Vertical Illuminance on Wall					
MH	FC	L	W	MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	570.9	1.2	1.2	4.5'	321.4	1.6	1.6	2.6	3'	160.2	2.7	1.6	5.2
5.5'	382.2	1.6	1.6	5.5'	215.2	1.9	1.8	3.2	4'	90.1	3.6	2.2	6.9
6.5'	273.6	1.8	1.8	6.5'	154.1	2.4	2.2	3.8	6'	40.1	5.5	3.4	10.4
8'	180.6	2.4	2.4	8'	101.7	2.9	2.8	4.6	8'	22.5	7.4	4.6	13.9
10'	115.6	3	3	10'	65.1	3.7	3.6	5.8	10'	14.4	9.3	5.8	17.3
12'	80.3	3.6	3.6	12'	45.2	4.4	4.2	6.9	12'	10	11.2	7	20.8

View Multipliers

## Photometric Data - Narrow Flood



View IES files

SUMMARY TABLE	
Filename	HL36A20NFL930ED010TL3RMW.ies
Test No.	P284155
Lumcat	HL36A20NFL930ED010TL3RMW
Lumens	1765 Lm
Watts	19.5 W
LPW	90.5 Lm/W
CCT	3000K
SC (0/90/45)	0.44 / 0.44 / 0.42





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	397.4	1.8	1.8		4.5'	260.8	2.3	2.2	2.6	3'	160.2	2.8	2	5.2
5.5'	266	2.4	2.4		5.5'	174.6	2.8	2.8	3.2	4'	90.1	3.8	2.8	6.9
6.5'	190.5	2.8	2.8		6.5'	125	3.3	3.2	3.8	6'	40.1	5.7	4.2	10.4
8'	125.7	3.4	3.4		8'	82.5	4.1	4	4.6	8'	22.5	7.7	5.6	13.9
10'	80.5	4.4	4.4		10'	52.8	5.2	5	5.8	10'	14.4	9.7	7	17.3
12'	55.9	5.2	5.2		12'	36.7	6.3	6.2	6.9	12'	10	11.6	8.4	20.8

SUMMARY TABLE	
Filename	HL36A20NFL930ED010TL3R2GMW.ies
Test No.	P284154
Lumcat	HL36A20NFL930ED010TL3R2GMW
Lumens	1655 Lm
Watts	19.5 W
LPW	84.9 Lm/W
CCT	3000K
SC (0/90/45)	0.45 / 0.45 / 0.44





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	328.2	2	2		4.5'	204.6	2.3	2.2	2.6	3'	109.6	3.3	2.2	5.2
5.5'	219.7	2.4	2.4		5.5'	137	2.8	2.6	3.2	4'	61.6	4.5	2.8	6.9
6.5'	157.3	2.8	2.8		6.5'	98.1	3.3	3.2	3.8	6'	27.4	6.7	4.4	10.4
8'	103.8	3.4	3.4		8'	64.7	4.1	4	4.6	8'	15.4	9	5.8	13.9
10'	66.5	4.4	4.4		10'	41.4	5.1	5	5.8	10'	9.9	11.3	7.4	17.3
12'	46.1	5.2	5.2		12'	28.8	6.2	6	6.9	12'	6.8	13.5	8.8	20.8

SUMMARY TABLE	
Filename	HL36A20NFL930ED010TL3PINMWWB.ies
Test No.	P284153
Lumcat	HL36A20NFL930ED010TL3PINMWWB
Lumens	1670 Lm
Watts	19.5 W
LPW	85.6 Lm/W
CCT	3000K
SC (0/90/45)	0.44 / 0.44 / 0.41



CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	398.7	1.8	1.8		4.5'	255.2	2.2	2	2.6	3'	162.4	2.7	2	5.2
5.5'	266.9	2.4	2.4		5.5'	170.9	2.7	2.6	3.2	4'	91.4	3.6	2.6	6.9
6.5'	191.1	2.8	2.8		6.5'	122.3	3.2	3	3.8	6'	40.6	5.5	4	10.4
8'	126.2	3.4	3.4		8'	80.8	4.1	3.8	4.6	8'	22.8	7.3	5.2	13.9
10'	80.7	4.4	4.4		10'	51.7	5.1	4.8	5.8	10'	14.6	9.1	6.6	17.3
12'	56.1	5.2	5.2		12'	35.9	6.1	5.6	6.9	12'	10.2	11	8	20.8

SUMMARY TABLE	
Filename	HL36A20NFL930ED010TL3PIN2GMWWB.ies
Test No.	P284152
Lumcat	HL36A20NFL930ED010TL3PIN2GMWWB
Lumens	1563 Lm
Watts	19.5 W
LPW	80.2 Lm/W
CCT	3000K
SC (0/90/45)	0.44 / 0.44 / 0.43





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	347.1	1.8	1.8		4.5'	211.7	2.2	2	2.6	3'	123.7	3	2	5.2
5.5'	232.3	2.4	2.4		5.5'	141.7	2.7	2.6	3.2	4'	69.6	3.9	2.6	6.9
6.5'	166.3	2.8	2.8		6.5'	101.5	3.2	3	3.8	6'	30.9	6	4	10.4
8'	109.8	3.4	3.4		8'	67	3.9	3.8	4.6	8'	17.4	8	5.4	13.9
10'	70.3	4.4	4.4		10'	42.9	5	4.8	5.8	10'	11.1	10.1	6.8	17.3
12'	48.8	5.2	5.2		12'	29.8	6	5.8	6.9	12'	7.7	12.1	8.2	20.8

View Multipliers

## Photometric Data - Flood



[View IES files](#)

SUMMARY TABLE	
Filename	HL36A20FL930ED010TL3RMW.ies
Test No.	P284139
Lumcat	HL36A20FL930ED010TL3RMW
Lumens	1754 Lm
Watts	19.5 W
LPW	90 Lm/W
CCT	3000K
SC (0/90/45)	0.65 / 0.65 / 0.59





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	206.3	2.8	2.8		4.5'	145.2	3	2.8	2.6	3'	113.4	2.6	2.6	5.2
5.5'	138.1	3.4	3.4		5.5'	97.2	3.7	3.6	3.2	4'	63.8	3.6	3.4	6.9
6.5'	98.9	4.2	4.2		6.5'	69.6	4.4	4.2	3.8	6'	28.4	5.4	5.2	10.4
8'	65.3	5	5		8'	45.9	5.4	5.2	4.6	8'	16	7.3	7	13.9
10'	41.8	6.4	6.4		10'	29.4	6.7	6.6	5.8	10'	10.2	9.2	8.8	17.3
12'	29	7.6	7.6		12'	20.4	8.2	7.8	6.9	12'	7.1	11	10.6	20.8

SUMMARY TABLE	
Filename	HL36A20FL930ED010TL3R2GMW.ies
Test No.	P284138
Lumcat	HL36A20FL930ED010TL3R2GMW
Lumens	1645 Lm
Watts	19.5 W
LPW	84.4 Lm/W
CCT	3000K
SC (0/90/45)	0.63 / 0.63 / 0.6





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	183.4	2.8	2.8		4.5'	120.2	2.9	2.8	2.6	3'	79.7	3.2	2.6	5.2
5.5'	122.8	3.4	3.4		5.5'	80.5	3.6	3.6	3.2	4'	44.8	4.3	3.6	6.9
6.5'	87.9	4	4		6.5'	57.6	4.3	4.2	3.8	6'	19.9	6.5	5.4	10.4
8'	58	5	5		8'	38	5.2	5.2	4.6	8'	11.2	8.8	7.4	13.9
10'	37.1	6.2	6.2		10'	24.3	6.6	6.4	5.8	10'	7.2	11	9.2	17.3
12'	25.8	7.4	7.4		12'	16.9	8	7.8	6.9	12'	5	13.2	11	20.8

SUMMARY TABLE	
Filename	HL36A20FL930ED010TL3PINMWWB.ies
Test No.	P284137
Lumcat	HL36A20FL930ED010TL3PINMWWB
Lumens	1644 Lm
Watts	19.5 W
LPW	84.3 Lm/W
CCT	3000K
SC (0/90/45)	0.64 / 0.64 / 0.58



CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	206.1	2.8	2.8		4.5'	143.4	2.8	2.8	2.6	3'	100.2	2.9	2.4	5.2
5.5'	137.9	3.4	3.4		5.5'	96	3.4	3.4	3.2	4'	56.4	3.9	3.4	6.9
6.5'	98.8	4	4		6.5'	68.7	4.1	4	3.8	6'	25.1	5.9	5	10.4
8'	65.2	5	5		8'	45.4	5.1	5	4.6	8'	14.1	8	6.8	13.9
10'	41.7	6.2	6.2		10'	29	6.4	6.4	5.8	10'	9	10	8.4	17.3
12'	29	7.6	7.6		12'	20.2	7.7	7.6	6.9	12'	6.3	11.9	10.2	20.8

SUMMARY TABLE	
Filename	HL36A20FL930ED010TL3PIN2GMWWB.ies
Test No.	P284136
Lumcat	HL36A20FL930ED010TL3PIN2GMWWB
Lumens	1544 Lm
Watts	19.5 W
LPW	79.2 Lm/W
CCT	3000K
SC (0/90/45)	0.63 / 0.63 / 0.59





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	187	2.8	2.8		4.5'	124.4	2.8	2.8	2.6	3'	82.3	3.1	2.4	5.2
5.5'	125.2	3.4	3.4		5.5'	83.3	3.5	3.4	3.2	4'	46.3	4.2	3.4	6.9
6.5'	89.6	4	4		6.5'	59.6	4.1	4	3.8	6'	20.6	6.3	5	10.4
8'	59.2	5	5		8'	39.4	5.1	5	4.6	8'	11.6	8.5	6.8	13.9
10'	37.9	6.2	6.2		10'	25.2	6.3	6.2	5.8	10'	7.4	10.6	8.6	17.3
12'	26.3	7.4	7.4		12'	17.5	7.6	7.4	6.9	12'	5.1	12.7	10.2	20.8

[View Multipliers](#)

## Photometric Data - Wide Flood



View IES files

SUMMARY TABLE	
Filename	HL36A20WFL930ED010TL3RMW.ies
Test No.	P284187
Lumcat	HL36A20WFL930ED010TL3RMW
Lumens	1609 Lm
Watts	19.5 W
LPW	82.5 Lm/W
CCT	3000K
SC (0/90/45)	0.86 / 0.86 / 0.82





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	100.9	3.8	3.8		4.5'	88.1	3.3	3.4	2.6	3'	61.7	3.1	3.2	5.2
5.5'	67.6	4.6	4.6		5.5'	58.9	4	4	3.2	4'	34.7	4.1	4.2	6.9
6.5'	48.4	5.6	5.6		6.5'	42.2	4.8	4.8	3.8	6'	15.4	6.2	6.4	10.4
8'	31.9	6.8	6.8		8'	27.9	5.9	6	4.6	8'	8.7	8.3	8.6	13.9
10'	20.4	8.6	8.6		10'	17.8	7.3	7.4	5.8	10'	5.6	10.4	10.6	17.3
12'	14.2	10.2	10.2		12'	12.4	8.8	9	6.9	12'	3.9	12.6	12.8	20.8

SUMMARY TABLE	
Filename	HL36A20WFL930ED010TL3R2GMW.ies
Test No.	P284186
Lumcat	HL36A20WFL930ED010TL3R2GMW
Lumens	1491 Lm
Watts	19.5 W
LPW	76.5 Lm/W
CCT	3000K
SC (0/90/45)	0.84 / 0.84 / 0.8





CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	93.7	3.6	3.6		4.5'	73.4	3.3	3.6	2.6	3'	47.2	3.4	3.2	5.2
5.5'	62.8	4.4	4.4		5.5'	49.1	4.1	4.4	3.2	4'	26.6	4.5	4.2	6.9
6.5'	44.9	5.4	5.4		6.5'	35.2	4.8	5.2	3.8	6'	11.8	6.8	6.4	10.4
8'	29.7	6.6	6.6		8'	23.2	6	6.4	4.6	8'	6.6	9.1	8.6	13.9
10'	19	8.2	8.2		10'	14.9	7.5	8	5.8	10'	4.3	11.3	10.8	17.3
12'	13.2	10	10		12'	10.3	9.1	9.6	6.9	12'	3	13.7	13	20.8

SUMMARY TABLE	
Filename	HL36A20WFL930ED010TL3PINMWWB.ies
Test No.	P284185
Lumcat	HL36A20WFL930ED010TL3PINMWWB
Lumens	1490 Lm
Watts	19.5 W
LPW	76.4 Lm/W
CCT	3000K
SC (0/90/45)	0.85 / 0.85 / 0.79



CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	100.3	3.8	3.8		4.5'	83.7	3.3	3.2	2.6	3'	51.6	3.3	3	5.2
5.5'	67.1	4.6	4.6		5.5'	56.1	4.1	3.8	3.2	4'	29	4.4	4	6.9
6.5'	48.1	5.4	5.4		6.5'	40.1	4.8	4.6	3.8	6'	12.9	6.7	6	10.4
8'	31.7	6.6	6.6		8'	26.5	5.9	5.8	4.6	8'	7.3	8.9	8	13.9
10'	20.3	8.4	8.4		10'	17	7.4	7.2	5.8	10'	4.6	11.2	10	17.3
12'	14.1	10	10		12'	11.8	8.9	8.6	6.9	12'	3.2	13.5	12	20.8

SUMMARY TABLE	
Filename	HL36A20WFL930ED010TL3PIN2GMWWB.ies
Test No.	P284184
Lumcat	HL36A20WFL930ED010TL3PIN2GMWWB
Lumens	1393 Lm
Watts	19.5 W
LPW	71.4 Lm/W
CCT	3000K
SC (0/90/45)	0.82 / 0.82 / 0.78




CONE OF LIGHT														
0 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Horizontal Illuminance on Floor					30 deg Aiming Angle Vertical Illuminance on Wall				
MH	FC	L	W		MH	FC	L	W	CB	D	FC	L	W	CB
4.5'	93.6	3.6	3.6		4.5'	73.6	3.2	3.2	2.6	3'	42.1	3.6	3	5.2
5.5'	62.7	4.4	4.4		5.5'	49.3	4	4	3.2	4'	23.7	4.8	4.2	6.9
6.5'	44.9	5.2	5.2		6.5'	35.3	4.7	4.6	3.8	6'	10.5	7.2	6.2	10.4
8'	29.6	6.4	6.4		8'	23.3	5.7	5.8	4.6	8'	5.9	9.7	8.4	13.9
10'	19	8.2	8.2		10'	14.9	7.2	7.2	5.8	10'	3.8	12.1	10.4	17.3
12'	13.2	9.8	9.8		12'	10.4	8.7	8.6	6.9	12'	2.6	14.5	12.6	20.8

View Multipliers



## Notes and Formulas

- Illuminance values for multiple fixtures are based upon the center two units of a four unit array. Footcandle values are centerline of fixtures and centered between fixtures.
- Illuminance values are cosine corrected initial values with no contribution from inter reflections from other room surfaces. Total illumination may increase from contributions from other surfaces.
- DD=Distance Down from Ceiling.
- Changing fixture spacing will affect illuminance level.



$$\text{New Fc} = \frac{\text{Existing Spacing}}{\text{New Spacing}} \times \text{Average Table Fc Level}$$

For optimal wall washing, space fixtures equal to the distance from the wall.

SUMMARY TABLE	
Filename	HL36A20FL927ED010TL3LWWMW.ies
Test No.	P284435
Lumcat	HL36A20FL927ED010TL3LWWMW
Lumens	1037 Lm
Watts	19.5 W
LPW	53.2 Lm/W
CCT	2700K
SC (0/90/45)	1.09 / 1.01 / 1.15

Single Footcandles 3' from wall (distance from fixture along wall)								
DD	•	1'	2'	3'	4'	5'	6'	
2'	15.8	12.8	7.5	3.8	1.8	0.9	0.4	
3'	14.3	12.2	8	4.6	2.5	1.4	0.8	
4'	10.8	9.5	6.9	4.4	2.7	1.6	0.9	
5'	7.7	7	5.4	3.8	2.5	1.6	1	
6'	5.4	5	4.1	3.1	2.1	1.5	1	
8'	2.8	2.6	2.3	1.9	1.5	1.1	0.8	
10'	1.6	1.5	1.4	1.2	1	0.8	0.6	

Multiple Unit Footcandles 2' from wall (spacing between fixtures)								
•	- 2'-	•	•	- 3'-	•			
42.7	45.7	42.7		36.4	31.8	36.4		
29.8	32.6	29.8		25.1	25.2	25.1		
19	20.7	19		16.1	17.2	16.1		
12.2	13.1	12.2		10.5	11.4	10.5		
8	8.5	8		7.1	7.7	7.1		
3.9	4	3.9		3.5	3.8	3.5		
2.1	2.1	2.1		2	2.1	2		

Multiple Unit Footcandles 3' from wall (spacing between fixtures)								
•	- 2'-	•	•	- 3'-	•			
23.3	25.6	23.3		19.6	20.2	19.6		
22.4	24.3	22.4		19	20.3	19		
17.7	19	17.7		15.2	16.6	15.2		
13.1	13.9	13.1		11.4	12.5	11.4		
9.5	10	9.5		8.4	9.2	8.4		
5.1	5.3	5.1		4.7	5	4.7		
2.9	3	2.9		2.7	2.9	2.7		

SUMMARY TABLE	
Filename	HL36A20FL930ED010TL3LWWMW.ies
Test No.	P284436
Lumcat	HL36A20FL930ED010TL3LWWMW
Lumens	1105 Lm
Watts	19.5 W
LPW	56.7 Lm/W
CCT	3000K
SC (0/90/45)	1.09 / 1.01 / 1.15

Single Footcandles 3' from wall (distance from fixture along wall)								
DD	•	1'	2'	3'	4'	5'	6'	
2'	16.9	13.6	8	4	1.9	0.9	0.5	
3'	15.3	13	8.6	4.9	2.7	1.5	0.8	
4'	11.5	10.1	7.4	4.7	2.8	1.7	1	
5'	8.2	7.4	5.8	4	2.6	1.7	1.1	
6'	5.7	5.3	4.4	3.3	2.3	1.6	1	
8'	3	2.8	2.5	2	1.6	1.2	0.9	
10'	1.7	1.6	1.5	1.3	1.1	0.9	0.7	

Multiple Unit Footcandles 2' from wall (spacing between fixtures)								
•	- 2'-	•	•	- 3'-	•			
45.5	48.7	45.5		38.8	33.8	38.8		
31.8	34.7	31.8		26.8	26.8	26.8		
20.3	22	20.3		17.2	18.4	17.2		
13	13.9	13		11.2	12.2	11.2		
8.5	9.1	8.5		7.5	8.2	7.5		
4.1	4.3	4.1		3.7	4	3.7		
2.2	2.3	2.2		2.1	2.2	2.1		

Multiple Unit Footcandles 3' from wall (spacing between fixtures)								
•	- 2'-	•	•	- 3'-	•			
24.9	27.2	24.9		20.9	21.5	20.9		
23.8	25.9	23.8		20.2	21.7	20.2		
18.8	20.3	18.8		16.2	17.7	16.2		
13.9	14.8	13.9		12.2	13.3	12.2		
10.1	10.7	10.1		9	9.8	9		
5.4	5.6	5.4		5	5.3	5		
3.1	3.2	3.1		2.9	3.1	2.9		

[View Multipliers](#)

## Photometric Data - Wall Wash

 [View IES files](#)

 [View Multipliers](#)

SUMMARY TABLE	
Filename	HL36A20FL935ED010TL3LWVMMW.ies
Test No.	P284437
Lumcat	HL36A20FL935ED010TL3LWVMMW
Lumens	1166 Lm
Watts	19.5 W
LPW	59.8 Lm/W
CCT	3500K
SC (0/90/45)	1.09 / 1.01 / 1.15

Single Footcandles 3' from wall (distance from fixture along wall)								
DD	•	1'	2'	3'	4'	5'	6'	
2'	17.8	14.4	8.4	4.3	2	1	0.5	
3'	16.1	13.7	9	5.2	2.8	1.6	0.9	
4'	12.1	10.7	7.8	5	3	1.8	1.1	
5'	8.6	7.8	6.1	4.2	2.8	1.8	1.1	
6'	6.1	5.6	4.6	3.4	2.4	1.6	1.1	
8'	3.1	3	2.6	2.2	1.7	1.3	0.9	
10'	1.7	1.7	1.5	1.3	1.1	0.9	0.7	

Multiple Unit Footcandles 2' from wall (spacing between fixtures)								
•	- 2'-	•		•	- 3'-	•		
48	51.4	48		41	35.7	41		
33.5	36.6	33.5		28.2	28.3	28.2		
21.4	23.2	21.4		18.1	19.4	18.1		
13.7	14.7	13.7		11.8	12.9	11.8		
9	9.6	9		7.9	8.7	7.9		
4.3	4.5	4.3		4	4.2	4		
2.4	2.4	2.4		2.2	2.3	2.2		

Multiple Unit Footcandles 3' from wall (spacing between fixtures)								
•	- 2'-	•		•	- 3'-	•		
26.2	28.8	26.2		22.1	22.7	22.1		
25.2	27.4	25.2		21.3	22.9	21.3		
19.9	21.4	19.9		17.1	18.6	17.1		
14.7	15.7	14.7		12.9	14.1	12.9		
10.7	11.3	10.7		9.5	10.3	9.5		
5.7	5.9	5.7		5.3	5.6	5.3		
3.3	3.4	3.3		3.1	3.3	3.1		

SUMMARY TABLE	
Filename	HL36A20FL940ED010TL3LWVMMW.ies
Test No.	P284438
Lumcat	HL36A20FL940ED010TL3LWVMMW
Lumens	1183 Lm
Watts	19.5 W
LPW	60.7 Lm/W
CCT	4000K
SC (0/90/45)	1.09 / 1.01 / 1.15

Single Footcandles 3' from wall (distance from fixture along wall)								
DD	•	1'	2'	3'	4'	5'	6'	
18.1	14.6	8.6	4.3	2.1	1	0.5	0.5	
16.3	13.9	9.2	5.3	2.9	1.6	0.9	0.9	
12.3	10.9	7.9	5	3	1.8	1.1	1.1	
8.8	7.9	6.2	4.3	2.8	1.8	1.1	1.2	
6.1	5.7	4.7	3.5	2.4	1.7	1.1	1.2	
3.2	3	2.6	2.2	1.7	1.3	0.9	1	
1.8	1.7	1.6	1.4	1.1	0.9	0.7	0.8	



Multiple Unit Footcandles 2' from wall (spacing between fixtures)								
•	- 2'-	•		•	- 3'-	•		
48.7	52.2	48.7		41.6	36.2	41.6		
34	37.2	34		28.6	28.7	28.6		
21.7	23.6	21.7		18.4	19.7	18.4		
13.9	14.9	13.9		12	13.1	12		
9.1	9.7	9.1		8	8.8	8		
4.4	4.6	4.4		4	4.3	4		
2.4	2.4	2.4		2.2	2.4	2.2		

Multiple Unit Footcandles 3' from wall (spacing between fixtures)								
•	- 2'-	•		•	- 3'-	•		
26.6	29.2	26.6		22.4	23.1	22.4		
25.5	27.8	25.5		21.6	23.2	21.6		
20.2	21.7	20.2		17.3	18.9	17.3		
14.9	15.9	14.9		13.1	14.3	13.1		
10.8	11.4	10.8		9.6	10.5	9.6		
5.8	6	5.8		5.3	5.7	5.3		
3.3	3.4	3.3		3.1	3.3	3.1		


## Color Metric Summary

SUMMARY TABLE - 2700 K

TM-30-15	R <sub>f</sub> = 93.1
	R <sub>g</sub> = 98.5
CRI/ CIE	R <sub>a</sub> = 93.7
	R <sub>9</sub> = 56.2





CIE 1931 Chromaticity Diagram and 2015 ANSI 7-Step Quadrangles




SUMMARY TABLE - 3000 K

TM-30-15	R <sub>f</sub> = 92.5
	R <sub>g</sub> = 98.7
CRI/ CIE	R <sub>a</sub> = 93.6
	R <sub>9</sub> = 56.2





CIE 1931 Chromaticity Diagram and 2015 ANSI 7-Step Quadrangles




SUMMARY TABLE - 3500 K

TM-30-15	R <sub>f</sub> = 91.4
	R <sub>g</sub> = 98.8
CRI/ CIE	R <sub>a</sub> = 92.4
	R <sub>9</sub> = 54.8





CIE 1931 Chromaticity Diagram and 2015 ANSI 7-Step Quadrangles



SUMMARY TABLE - 4000 K

TM-30-15	R <sub>f</sub> = 91.1
	R <sub>g</sub> = 99.2
CRI/ CIE	R <sub>a</sub> = 93.5
	R <sub>9</sub> = 62.2



CIE 1931 Chromaticity Diagram and 2015 ANSI 7-Step Quadrangles

