| Project | Catalog # | Туре | |
|-------------|-----------|------|--|
| Prepared by | Notes | Date | |




ℳ Interactive Menu

- Order Information page 2
- Product Specifications page 3
- Photometric Data page 4
- Energy & Performance Data page 4
- Product Warranty

Top Product Features

- · 6" LED Direct Mount Night Light with Field Selectable CCT
- · Direct mount does not require recessed housing or junction box
- 6 selectable color temperature options
 - · 2700K, 3000K, 3500K, 4000K, 5000K
 - Dim-to-warm technology included: use your dimmer to warm color temperature from 3000K to 1800K
- · Night light provides soft glow at 2000K CCT
- Wet location listed for showers and protected ceilings
- · Dimmable to 5% with 120V dimmers

Dimensional and Mounting Details



HALO

RLNL6 Night Light Direct Mount

6" Night Light LED Canless Direct Mount w/ Remote Driver/Junction Box 1000 Lumen Series

Typical Applications

Residential

Product Certification













Product Features










Scale







Order Information

SAMPLE ORDER NUMBER: RLNL6109FSD2W1EWHDM

A complete luminaire consists of an LED module and remote driver/junction box.

| Notes | Notes | Notes | Notes | Notes | Notes |
|---------------------------|-----------------------------------|---|---|------------------|----------------------------------|
| Notes | Notes | Notes | Notes | Notes | Notes |
| RLNL6= 6" LED Night Light | 10 = 1000 lumens (nominal) | 9FSD2W = 90 CRI, selectable CCT with D2W option | 1E = 120V 60Hz, LE & TE phase cut 5% dimming | WH = Matte white | DM = Canless Direct Mount |
| Models | Lumens | CRI/CCT | Driver | Finish | Mounting |
| Models | Lumens | CRI/CCT | Driver | Finish | Mounting |
| | | | | | |

Accessories

| Accessories |
|---|
| Mounting Frame HL6RSMF = 6" round and square mounting frame |
| Extension Cable ECSPIN-6FT = 6ft. 5 pin extension cable ECSPIN-12FT = 12ft. 5 pin extension cable ECSPIN-20FT = 20ft. 5 pin extension cable |

Light Modes

Flip wall switch On/Off/On under 1.5 seconds to change light mode.

Downlight



Night Light





Product Specifications

Night Light System

Choose mode of light based on toggle of light switch

NIGHTLIGHT MODE:

- With wall switch in 'ON' position (downlight on), cycle wall switch 'OFF' and back to 'ON' within 0.2-1.5 seconds. Fixture should illuminate in nightlight mode.
- Fixture will default back to downlight mode when wall switch is cycled 'OFF' then 'ON.

DOWNLIGHT MODE:

- Cycle wall switch to 'ON' position to turn on downlight.
- Cycle wall switch to 'OFF' position to turn off downlight.

CCT Select System

- Use the CCT select switch to choose between D2W, 2700K, 3000K, 3500K, 4000K, and 5000K CCT
- D2W option starts at 3000K and warms to 1800K as fixture dims

Module - Trim

- Module construction includes LED Array, heat sink, reflector, lens, baffle/trim ring and ceiling ring
- Regressed baffle
- Heat sink designed to conduct heat away from the LED array

LED Array

- Mid power LED array provides a uniform source with high efficiency and no pixilation
- 90 CRI minimum, R9 greater than 50
- Color accuracy within 3 SDCM at the CCT endpoints and 4 SDCM in between endpoints, provide color accuracy and uniformity.
- Color Temperature (CCT) has an selectable range from 2700K to 5000K (factory default 3000K)

Optical Assembly

- Regressed lens
- Impact-resistant polycarbonate
- Convex form and lamp-like appearance
- Diffuse for even illumination

Remote Driver/ Junction Box

- Aluminum driver / junction box with captive hinged junction box cover
- Listed for (6) #12 AWG 90° C splice conductors, 2-in, 2-out plus (2) ground
- (2) 1/2" conduit pry-outs
- (2) Slide-N-Side[™] non-metallic (NM) wire traps all
- Accepts 14-2, 14-3, 12-2, 12-3 U.S and 14-2, 14-3, 12-2 Canadian NM cable
- (3) 4-port push wire nuts with clear caps for quick and reliable mains voltage connections
- Integral keyhole mounting slots facilitate direct mounting to building structure or new construction mounting frame

Driver

- Remote 120V 60 Hz constant current driver provides noise free operation
- · Continuous, flicker-free dimming from 100% to 5%.
- Plenum rated inline electrical quick connect provides low voltage connection to fixture fitting

Installation

- · Can be installed in 1/2" to 1-1/4" thick ceilings
- Cutout can utilize standard round hole saw sizes, cutout template provided
- Heat treated springs hold fixture fitting securely in the ceiling eliminating light leaks
- Can be removed from below the ceiling for service or replacement

Mounting / Retention

- The RL-DM requires no housing or third party junction box
- The remote enclosure may be used in direct contact with insulation
- Installer must cut template out of drywall and install into aperture with the clips compressed
- When released, the spring clips will rest on to the back side of the drywall
- · Not for installation in recessed cans


Compliance

- UL Certified for US and Canada, type IC suitable for direct contact with air permeable insulation
- Not for use in direct contact with spray foam insulation, reference NEMA LSD57-2013
- · Wet and Damp location listed
- · Airtight certified per ASTM-E283
- Suitable for use in closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- · Contains no mercury or lead and is RoHS compliant
- Photometric testing in accordance with IES I M-70-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Complies with State of California Title 24 JA8-2019-E as a high efficacy luminaire
- International Energy Conservation Code (IECC) and Washington State Energy Code compliant
- ENERGY STAR® listed, reference database for current listings

Warranty


 Five year limited warranty, consult website for details. <u>www.cooperlighting.com/warranty</u>

Dimensional and Mounting Details





Photometric Data



RLNL6109FSD2W1EWHDM-3000K

Spacing criterion:

(0-180) 1.24 | (90-270) 1.24 | (Diagonal) 1.34

Beam Angle: 104° Field Angle: 156° Lumens: 1020 Input Watts: 11.5 W Efficacy: 88.7 LPW

UGR: 25 Test Report: P645281

| Zonal Lumen | Lumens | % Lumens |
|-------------|--------|----------|
| 0-30 | 304 | 29.9 |
| 0-40 | 494 | 48.4 |
| 0-60 | 842 | 82.5 |
| 0-90 | 1020 | 100 |

| TM-30-15 | Rf = 91 | |
|------------|---------|--|
| 1101-30-15 | Rg = 98 | |
| CRI/CIE | Ra = 92 | |
| | R9 = 64 | |



Energy Data

| RLNL6109FSD2W1EWHDM | | | |
|---------------------|---------|--|--|
| Lumens | 1020 | | |
| Input Voltage | 120V | | |
| Input current | 0.1A | | |
| Input Power | 12W | | |
| Efficiency | 88.7% | | |
| Inrush(A) | 2.34A | | |
| THD | < 20% | | |
| PF | > 0.9 | | |
| Sound Rating | < 22dBA | | |

| RL4-DM | CCT | Lumens | Power (W) | LPW |
|-------------------------|-------|--------|-----------|------|
| Field Selectable CCT | 2700K | 995 | 11.5 | 86.5 |
| | 3000K | 1020 | 11.5 | 88.7 |
| | 3500K | 1055 | 11.5 | 91.7 |
| | 4000K | 1085 | 11.5 | 94.3 |
| | 5000K | 1110 | 11.5 | 96.5 |

Product Specifications

RLNL6109FSD2W1EWHDM

