

# CERTIFICATE OF COMPLIANCE

**Certificate Number** E328008  
**Report Reference** E328008-20160826  
**Issue Date** 2020-SEPTEMBER-22

**Issued to:** COOPER LIGHTING DIV OF COOPER INDUSTRIES INC  
1121 HIGHWAY 74 S  
PEACHTREE CITY, GA 30269-3019 USA

**This certificate confirms that  
representative samples of**

LIGHT-EMITTING-DIODE SURFACE-MOUNTED  
LUMINAIRES

See Addendum page for Models/Product

Have been investigated by UL in accordance with the  
Standard(s) indicated on this Certificate.

**Standard(s) for Safety:**

UL 1598 & CSA-C22.2 No. 250.0 - Luminaires  
UL 8750 - Light Emitting Diode (LED) Equipment for Use in  
Lighting Products  
CSA-C22.2 No. 250.13 - Light Emitting Diode (LED)  
Equipment for Lighting Applications

**Additional Information:**

See the UL Online Certifications Directory at  
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Mark. Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program  
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



# CERTIFICATE OF COMPLIANCE

**Certificate Number** E328008  
**Report Reference** E328008-20160826  
**Issue Date** 2020-SEPTEMBER-22

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Light-emitting-diode (LED) Luminaires, Surface-Mounted - FM9WRXR (b), FM19WRXR (b), FM11WRXR (b), FM15WRXR (b)

Light-emitting-diode (LED) Luminaires, Surface-Mounted, Wet location - 2APVTLD-20LY (d), 4APVTLD-40LY (d), 4APVTLD-54LY (d), 4VTLD40YC (g)

LED Surface Mounted Luminaire - FE0650LPCH, FE0650LPCWH, FE0650LPC, FE0650LPCW, LEL10BPCI, LEL10WPCI, 2ST1L1040R, 2ST2L2040R, 4ST1L2040R, 4ST2L4040R, 8ST2L8040R, 2WP1540R, 4WP3040R, FM9WRCCR (i), FM11WRCCR (i), FM15WRCCR (i), FM19WRCCR (i), FM11WSCCR (i), FM15WSCCR (i), 2WP1540C, 4WP3040C, FM9WSCCR (I), FM19WSCCR (I)

(b) - Where "x" in the model designation represents the color temperature of the LED, it can be 30, 40, 50, represent 3000K, 4000K, 5000K, respectively.

(d) - Where "Y" in the model designation represents the color temperature of the LED, it can be "827", "830", "835", "840", "850", "860", represent 2700K, 3000K, 4000K, 3500K, 5000K, 6000K respectively.

(g) - Where Y in the model designation represents the color temperature of the LED, it can be 27, 30, 35, 40, 50, 60, represent 2700K, 3000K, 4000K, 3500K, 5000K, 6000K respectively.

(i) - Where CC can be any number representing different color temperature.

(I) - Where CCR: CC = CCT select (3000K, 4000K, 5000K); R = Retail.

LED Surface Mounted Luminaire

2ST1L10XXR(e), 2ST2L20XXR (e), 4ST1L20XXR (e)  
4ST2L40XXR (e), 8ST2L80XXR (e)

(e) Where the suffix XX represents the CRI and CCT of the product. 27 = 80 CRI & 2700K CCT, 30 = 80 CRI & 3000K CCT, 35 = 80 CRI & 3500K CCT, 40 = 80 CRI & 4000K CCT, 50 = 80 CRI & 5000K CCT, 57 = 80 CRI & 5700K CCT, 65 = 80 CRI & 6500K CCT.



Bruce Mahrenholz, Director North American Certification Program  
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



# CERTIFICATE OF COMPLIANCE

**Certificate Number** E328008  
**Report Reference** E328008-20160826  
**Issue Date** 2020-SEPTEMBER-22

LED Surface Mounted Luminaire

2ST2L20xx(n), 4ST2L40xx(n), 8ST2L80xx(n), 2ST2L20Syyyy(n), 4ST2L40Syyyy(n), 8ST2L80Syyyy(n)

(n) - Where 'xx' can be '27', '30', '35', '40', or '50' representing CRI and CCT, '27'=80CRI 2700K, '30'=80CRI 3000K, '35'=80CRI 3500K, '40'=80CRI 4000K, '50'=80CRI 5000K. Where 'yyyy' can be '3550' or '4050' representing CRI and CCT options, '3550'=80CRI and 3500K or 5000K, '4050'=80CRI and 4000K or 5000K



Bruce Mahrenholz, Director North American Certification Program  
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

