

Project		Catalog #		Type	
Prepared by		Notes		Date	



Portfolio

LDS6 | EU6 | 6LBS - VividTune & BioUp

6" round, new construction shallow downlight
Tunable White, BioUp & Dim-to-Warm

Typical Applications

Office • Education • Healthcare • Hospitality • Retail •
Code-Compliance Areas • Sports Venues

Interactive Menu


- Order Information [page 2](#)
- Product Specifications [page 3](#)
- Energy Data [page 4](#)
- Connected System [page 5](#)
- Product Warranty



Top Product Features

- 800-3000 lumens; ENERGY STAR® qualified
- Easy disconnect for LED engine replacement and installation
- Optional snap in driver for ease of replacement
- Standard 0-10V driver dims to 1%
- D2W™ option from 3000K to 1850K
- Tunable White CCT range: W2N = 2700K to 6500K or 2000K to 5000K / BioUp = 2700K to 5000K
- Options to meet Trade Agreements Act requirements

Dimensional and Mounting Details



[CLICK HERE](#)
dimension information

Single Line Order Information

SAMPLE ORDER NUMBER: **LDS6C10D2WD010TR1H = LDS6C10D010 + EU6C08259030D2W + 6LBS1H**

(all components in multiple packages in same shipment)

Invoice will indicate separate fixture components (housing, trim, module) which will ship complete from a single CLS facility in separate cartons.

To receive separate components (housing, trim, module) shipment, click on the "Multi-Line Ordering Information Option" button to the right.



Housing	Lumen ⁽¹⁾	Color Control	CCT ⁽⁷⁾
LDS6C =LED Downlight 6" Nominal Aperture LDS6CCP =LED Downlight 6" Nominal Aperture, Chicago Plenum For TAA use Multi-line Ordering	08 =800 Lumens ⁽²⁴⁾ 10 =1000 Lumens ⁽²⁵⁾ 15 = 1500 Lumens 20 = 2000 Lumens 25 = 2500 lumens 30 = 3000 Lumens ⁽²⁷⁾	D2W = Dim to warm for 800-2500; 90CRI, 3000K W2N2765 = Tunable White for 1000-3000 lumens, 2700K-6500K (D5LT & DE010 drivers only), 90CRI ⁽¹⁰⁾ W2N2050 = Tunable White for 1000-3000 lumens, 2000K-5000K (D5LT & DE010 drivers only), 90CRI ⁽¹⁰⁾ B2750 =BioUp Tubable White for 800-2000 lumens, 2700K-5000K (D5LT & DE010 drivers only) B =BioUp Static CCT for 800-2000 lumens, specify CCT 3500K, 4000K or 5000K (D5LT & DE010 drivers only)	Static BioUp 35 =3500K 40 =4000K 50 =5000K

Voltage	Driver	Driver Options	Hanger Bars
Dim-to Warm Blank =120-277V 800-2500 lumens 3 =347V (D010 driver 800-2500 lumens)	Dim-to Warm D010 =0-10V 1% dimming D010TR =0-10V or (120V) phase cut 1% dimming DE010 =0-10V linear 0.1% dimming D5LT =DALI T6 Logarithmic 0.1% Dimming DMX =DMX/RDM Logarithmic 0.1% Dimming ⁽¹⁴⁾ DMXC5 =DMX/RDM Logarithmic 0.1% Dimming with RJ45 connection ⁽¹⁴⁾ DLE =Lutron Ecosystem 1-100% dimming DLVP =Low voltage dimming 1-100% for use with DLVP system ⁽³⁾	Blank = Integral driver RC100 =Remote 100ft ^{(3) (32)} RC75 =Remote 75ft ^{(3) (32)} RC50 =Remote 50ft ^{(3) (32)} RC25 =Remote 25ft ⁽³⁾ RC15 =Remote 15ft ⁽³⁾ RC5 =Remote 5ft ⁽³⁾ RC2 =Remote 2ft ⁽³⁾ PD = Plug in Driver ⁽²²⁾	Blank = Without hanger bars B26 = C-channel Bar Hanger, 26" Long, Pair
Tunable White Blank =1000 lumens 1 =120V 1500-3000 lumens (integral driver only) 2 =277V 1500-3000 lumens (integral driver only) 3 =347V Step down transformer (Limited to 1000 lumens with remote driver)	Tunable White DE010W2N2765 =0-10V 0.1% Dimming, 2700-6500K DE010W2N2050 =0-10V 0.1% Dimming, 2000-5000K D5LTW2N2765 =DALI T6 0.1% Dimming, 2700-6500K D5LTW2N2050 =DALI T6 0.1% Dimming, 2000-5000K		
BioUp Tunable White Blank =800 lumens 1 =120V 1000-2000 lumens (integral driver only) 2 =277V 1000-2000 lumens (integral driver only) 3 =347V Step down transformer (Limited to 800 lumens with remote driver)	BioUp Tunable White DE010B2750 =0-10V 0.1% dimming, tunable white 2700-6500K DE010B35 = 0-10V 0.1% dimming, static white 3500K DE010B40 = 0-10V 0.1% dimming, static white 4000K DE010B50 = 0-10V 0.1% dimming, static white 5000K D5LTB2750 =DALI T6 0.1% dimming, tunable white 2700-6500K D5LTB35 = DALI T6 0.1% dimming, static white 3500K D5LTB40 = DALI T6 0.1% dimming, static white 4000K D5LTB50 = DALI T6 0.1% dimming, static white 5000K		

Trim Distribution	Trim Flange	Trim Finish	Options ^{(3) (16) (23)}
S =Shallow, Spun Aluminum PS =Non-Conductive Shallow (dead front), white ^{(11) (12)} CS =Cast Shallow, Die Cast Aluminum	0 =White Polymer Trim Ring 1 =Self-flanged ⁽¹³⁾ 2 =White Painted Self-flanged 4 =Knife edge rimless use with die cast only ^{(8) (6)}	LI =Specular Clear ⁽⁹⁾ H =Semi-Specular Clear ⁽⁹⁾ WMH =Warm Haze ⁽⁹⁾ WH =Wheat ⁽⁹⁾ GPH =Graphite Haze ⁽⁹⁾ B =Specular Black ⁽⁹⁾ MW =Matte White (Antimicrobial) MB =Matte Black ⁽⁸⁾ MMS =Matte Metallic Silver ⁽⁸⁾	EMBOD6ST =Bodine® 6W Self Test Emergency Module with Remote Test Switch IEMBOD6ST =Bodine® 6W Self Test Emergency Module with Integral Test Switch (offered with Shallow (S) trim) WPN = WaveLinX PRO Wireless Node without sensor ^{(21) (29)} WLN = WaveLinX LITE Wireless Node without sensor (not compatible with Tuneable White) ^{(23) (29)}

Accessories (Order separately) ⁽²⁰⁾			
TRM6P =White Metal Trim Ring ⁽²⁾ LGSKT6IP66 =IP66 Gasket Kit PRR6 =Rimless Plaster Ring ⁽²⁾ RKP6 =Knife Edge plaster Ring ⁽⁶⁾	RPM6MW =Rimless Millwork Ring, Matte White ⁽²⁾ RPM6MB =Rimless Millwork Ring, Matte Black ⁽²⁾ RKM6MW =Knife Edge Millwork Ring, Matte White ⁽⁵⁾ RKM6MB =Knife Edge Millwork Ring, Matte Black ⁽⁵⁾ HSA6 =Slope Adapter for 6" Aperture Housings, Specify Slope ⁽²⁸⁾	Bar Hangers HB50 =C-channel Bar Hanger, 50" Long, Pair RMB22 =Wood Joist Bar Hanger, 22" Long, Pair	Connected Lighting Systems ^{(3) (15)} WPST = Field installed WaveLinX PRO Sensor Kit ⁽¹⁸⁾ WLST = Field installed WaveLinX LITE Sensor Kit ⁽¹⁷⁾

Notes:

- Nominal Lumens will vary depending on selected color, CRI, driver and reflector finish. Reference IES files.
- Order trim with polymer trim ring.
- Not available with Chicago Plenum.
- ULUS listed only.
- Order die cast trim with flange type 4
- Requires knife edge accessory ring.
- Not required for W2N and D2W.
- Available only on CS distributions.
- Not available on PS or CS distributions.
- Limited to 1000 lumens with remote driver
- PS available in self-flanged MW finish only.
- Offered up to 2000 lumens
- Flange is the same finish as the reflector
- DMX fixtures default to full on upon loss of DMX signal.
- Refer to system specifications for additional information, features, and benefits. Use with 0-10V driver.
- Non-IC
- WLST = WaveLinX LITE tilemount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinX LITE system specifications)

- WPST = WaveLinX PRO wireless sensor kit for daylight dimming, PIR motion sensing, and optional RLTS - RealTime Location Services, use with 0-10V only.
- Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Offered with shallow (S) spun trim.
- Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.
- WPN = WaveLinX PRO wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with D010 or DE010 drivers only.
- Not available with DLVP
- 120V-277V
- IC rated
- Tunable white IC rated with 1000 lumens
- Not recommended for use with Wall Wash

- W2N for 3000 lumens and BioUp for 2000 lumens is marked spacing and must be installed with the following minimum spacing.
 - Center to center of adjacent luminaires: 36"
 - Center of luminaire to side of building member: 36"
 - Minimum overhead: 0.5'
- WLN = WaveLinX LITE wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with D010 or DE010 drivers only.
- Not compatible with 347V or Chicago plenum.
- Not available for W2N /BioUp
- Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others)
- Not available with Lutron drivers

Product Specifications

Lower Shielding Reflector

- Painted die cast aluminum, spun aluminum or nonconductive injection molded lower reflector with a lensed upper optical chamber providing superior lumen output with minimal source brightness
- Spun reflectors are offered in all Portfolio anodized finishes
- Reflector is retained with two torsion springs holding the flange tight to the finished ceiling surface
- Plaster lathing ring accessory offered for flush reflector transition

Plaster Frame

- Galvanized steel plaster frame designed for ceiling thickness from ½ to 1-1/4-inch

Universal Mounting Bracket

- Accepts 1/2" Electric Metallic Tube (EMT), C-channel and bar hangers
- Adjusts 5" vertically from above and below the ceiling

Junction box

- Four 1/2" and two 3/4" trade size pry outs positioned to allow straight conduit runs
- Lever connectors for simple push in wiring
- Listed for (4) #12 AWG (two in, two out) 90°C conductors and feed thru branch wiring for type IC and Plug in drivers for 120/277V only. For all other cases (8) #12 AWG (four in, four out) 90°C conductors and feed thru branch wiring for 120/277V only

Thermal

- Aluminum heat sink conducts heat away from the LED module for improved performance and longer life

LED System

- Contains a plurality of high brightness white LED's combined with a high reflectance upper reflector and convex transitional lens producing even distribution without pixilation
- Auto resetting, thermally protected, LED's are turned off when safe operating temperatures are exceeded
- Quick disconnect allows for tool-less replacement of LED engine from below ceiling
- W2N: L70 55,000 hours
- Color variation within 2-step MacAdam ellipses
- **D2W™** – dim-to-warm shifts CCT from 3000K to 1850K as fixture dims mimicking halogen sources.
- **W2N** - Tunable white CCT range 2700K to 6500K or 2000K to 5000K, 90 CRI. Standard

- **BioUp** - Tunable white CCT range 2700K to 5000K Provides the biological effectiveness of natural sunlight, with color temperatures that are more comfortable for indoor environments

Driver

- Standard 120-277V 0-10V dimming driver provides flicker free dimming from 100% to 1%
- Optional 120V leading edge/0-10V, <1% 0-10V, Fifth Light, DMX or Lutron® Ecosystem
- Distributed low voltage power system combines power, lighting, and controls with ease of installation.
- Optional magnetically guided snap in driver for ease of maintenance.

Emergency Option

- 6W battery provides 90 minutes of standby lighting, meeting most life safety codes for egress lighting
- UL 924 listed

Connected Lighting System

Two WaveLinx connected solutions to choose from. Refer to WaveLinx system specifications and application guides for details.

WaveLinx PRO Tilemount Sensor Kit

- WaveLinx PRO WPST tilemount sensor kit offers daylight dimming, PIR motion sensing, scene and zone configuration, automatic commissioning; and optional RLTS - Real Time Location Services available.

WaveLinx PRO Wireless Node

- WaveLinx PRO WPN wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only. **Note:** Not compatible with 347V or Chicago plenum.

WaveLinx LITE Tilemount Sensor Kit

- WaveLinx LITE WLST tilemount sensor kit offers daylight dimming and PIR motion sensing, scene and grouping configuration.

WaveLinx LITE Wireless Node

- WaveLinx LITE WLN wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only. **Note:** Not compatible with 347V or Chicago plenum.

WaveLinx Tilemount Sensor Kits Application

- The WPST and WLST tilemount sensor kits include a control module mounted on the luminaire junction box via 1/2" knock-out, and a tilemount sensor on 54-inch whip; for ceiling installation by direct-mount spring clips or via mounting bracket in octagon ceiling boxes.
- The WPST and WLST tilemount sensor kits may be ordered as factory installed on the luminaire, or ordered separately as a field installed accessory kit.
- **Note: WaveLinx PRO devices are only compatible with the WaveLinx PRO system.**
- **Note: WaveLinx LITE devices are only compatible with the WaveLinx LITE system.**

Code Compliance

- Thermally protected
- cULus Certified to UL 1598 / C22.2 No. 250.0 suitable for wet locations with covered ceiling
- IP66 rated when used with IP66 gasket kit accessory
- Use IP66 gasket with non conductive reflector for steam room applications up to 2000 lumens and 40°C.
- Optional City of Chicago environmental air (CCEA) marking for plenum applications
- FCC CFR Title 47 Part 15 Class B at 120VAC and Class A at 277VAC
- Insulated ceiling (IC) rated up to 800 lumens (D2W); 1000 lumens (W2N). All others are non-IC rated (insulation must be kept 3" from top and sides of housing).
- Can be used for State of California Title 24 high efficacy LED compliance under JA8, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2016 JA8 High Efficacy Lighting
- RoHS compliant
- Photometric testing completed in accordance with IES LM-79
- LED life testing completed in accordance with IES LM-80-08 and TM-21-11 standards

Warranty

- Five year warranty www.cooperlighting.com/legal

Energy and Performance Data

D010 DRIVER ENERGY DATA

Series	800 lumen		1000 lumen		1500 lumen		2000 lumen		2500 lumen		3000 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V
Input Current (A)	0.085	0.041	0.084	0.042	0.135	0.063	0.189	0.084	0.276	0.121	0.276	0.121
Input Power (W)	10.15	10.52	10.04	10.43	16.17	16.56	22.58	22.63	32.98	32.57	32	32.57
In-rush (A)	3.6	8.3	3.6	8.4	2.3	9.5	2.1	9.7	2.5	11.8	3.6	11.8
Inrush duration (µs)	220	135	226	136	230	125	243	132	215	111	220	111
THDi (%)	5.57	9.63	7.78	9.24	4.75	9.93	8.03	7.44	9.86	6.57	5.57	6.57
PF	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.94	≥ 0.99	≥ 0.96	≥ 0.99	≥ 0.97	≥ 0.99	≥ 0.99

Minimum starting temperature -30°C (-22°F)*
(Nominal input 120-277VAC & 100% of rated output power)

Sound Rating: Class A standards


Notes:

Emergency Battery packs are rated for a minimum starting temperature of 0°C.

Beam Angles

Trim	Beam Angle
6LBSH	SHALLOW 85° BEAM (H)
6LBSLI	SHALLOW 70° BEAM (LI)

Dimensional and Mounting Details



CATALOG #	VIVIDTUNE		MAX HEIGHT		
	Flange DIAMETER or WIDTH [IN]	INSIDE DIAMETER [IN]	D2W	W2N	BIOUP
			800-2500 LUMENS	1000-3000 LUMENS	800-2000 LUMENS
6LBS	6.94	5.62	5.6	5.6	5.6
6LBPS	6.94	5.66	5.6	5.6	5.6
6LBCS	6.94	5.66	5.6	5.6	5.6

Connected Solutions



WaveLinx LITE Wireless Node - WLN


WaveLinx LITE devices only compatible with the WaveLinx LITE system.

- Intuitive Android™ or Apple® iOS® app for basic system code compliant set up and configuration via Bluetooth
- Up to 28 unique areas per project site (WaveLinx LITE Bluetooth network)
- Up to 50 devices for an area, any one of 16 control zones, up to 6 occupancy sets, and custom lighting scenes
- Refer to the WaveLinx system specifications for details
- Not available with BioUp or Tunable White


WaveLinx mobile app settings



WaveLinx LITE Wireless Node (WLN) Wiring Diagram



WaveLinx LITE Bluetooth Enabled System



WaveLinx PRO Wireless Node - WPN


WaveLinx PRO devices only compatible with the WaveLinx PRO system.




- WaveLinx Wireless functionality configures zones and customizes settings from one secure mobile app
- Automatic code commissioning that meets the strictest codes
- Fixtures and sensors integrate with WaveLinx Area Controller, Wall Stations, and Control Devices
- Stand-Alone Offices or Entire Building Network Installations




WaveLinx mobile app settings



WaveLinx PRO Wireless Node (WPN) Wiring Diagram



WaveLinx CORE Building Management Integration



Proven Research. Industry Recognized.

BioUp Melanopic Lighting



See better



Feel better



Function better



See [BioUp brochure](#) for more details



ANSI/IES RP-46-23


RECOMMENDED PRACTICE:
SUPPORTING THE PHYSIOLOGICAL
AND BEHAVIORAL EFFECTS
OF LIGHTING IN INTERIOR
DAYTIME ENVIRONMENTS
AN AMERICAN NATIONAL STANDARD

ANSI/IES RP-46-23 / TM18 published March 2024 based on over 40 years of research.

"...circadian clock synchronization is paramount to the body's efficient and appropriate functioning." – TM18



BioUp solutions maximize WELL points for Circadian Lighting Design (L03):



Use BioUp to achieve Equivalent Melanopic Lux (EML) thresholds for circadian design and earn nearly 20% of WELL building lighting points.

MDER, M-EDI and **EML** are key metrics used to quantify non-visual performance of indoor lighting systems.





See [BioUp white paper](#) for more details

30% boost Biological impact compared to traditional LED sources

MDER - Melanopic Daylight Efficacy Ratio (MDER) measures the amount of light stimulating to the melanopsin receptors.

Standard 4000K LED
MDER = .62

BioUp 4000K LED
MDER = .82




CCT	LED @ ~83 CRI	BioUp Static		BioUp Dynamic	
		MDER	CRI	MDER	CRI
2700K	0.45	-	-	0.43	95
3000K	0.50	-	-	0.57	94
3500K	0.57	0.71	90	0.71	90
4000K	0.65	0.84	87	0.84	87
5000K	0.79	1.00	84	1.00	84

BioUp enhances the LED spectrum with cyan light at 475nm increasing the biological impact of the light to enhance our circadian rhythm which regulates our sleep/wake cycle, daytime engagement, and mood – **all without distorting visual color impression.**

Static (non-tunable)

Static BioUp is used when simple Melanopic Lighting is desired at all times.

Arrow in graph shows BioUp spectrum boost is at 475nm where non-visual biological response is enhanced.



3500K or **4000K** or **5000K**


Cyan light component always present



> no CCT control needed

Dynamic - (Tunable)

Dynamic BioUp is used when Melanopic Lighting is desired to adjust during the day.



Warmer CCT Without Cyan content ← → Cooler Light With Cyan content

2700K – 5000K



> Control with Wavelinx, 2ch 0-10V, or DALI

Multi-line Order Information

SAMPLE ORDER NUMBER: **LDS6C10D010TREM6**

Invoice will indicate separate fixture components (housing, trim, module) and may ship from multiple CLS facilities in separate cartons.

 Single line Ordering Information Option

Domestic Preferences ⁽¹⁾	Housing	Lumens ^{(2) (14)}	Color Control
[Blank] =Standard BAA =Buy American Act TAA =Trade Agreements Act	LDS6C =LED Downlight 6" Nominal Aperture LD6CCP =LED Downlight 6" Nominal Aperture, Chicago Plenum	08 =800 lumens 10 =1000 lumens 15 =1500 lumens	20 =2000 lumens ⁽³⁾ 25 =2500 lumens 30 =3000 lumens ⁽³⁾
			Blank =W2N or BioUp D2W =Dim to warm for 1000-2500 lumens lumens

Voltage	Driver	Driver Options	Options ^{(6) (25) (27) (28)}
Dim-to Warm Blank =120-277V 800-2500 lumens 3 =347V (D010 driver 800-2500 lumens)	Dim-to Warm D010 =0-10V 1% dimming D010TR =0-10V or (120V) phase cut 1% dimming DE010 =0-10V linear 0.1% dimming D5LT =DALI T6 Logarithmic 0.1% Dimming DMX =DMX/RDM Logarithmic 0.1% Dimming ⁽¹⁴⁾ DMXC5 =DMX/RDM Logarithmic 0.1% Dimming with RJ45 connection ⁽¹⁴⁾ DLE =Lutron Ecosystem 1-100% dimming DLVP =Low voltage dimming 1-100% for use with DLVP system ⁽³⁾	Blank =Integral driver R =Remote driver (order remote driver separately) ⁽⁶⁾ PD =Plug in Driver ⁽⁸⁾	EMBOD6ST =Bodine® 6W Self Test Emergency Module with Remote Test Switch IEMBOD6ST =Bodine® 6W Self Test Emergency Module with Integral Test Switch ⁽¹⁴⁾ EMV7 =7W Low Voltage Emergency Module with Remote Test Switch ⁽⁷⁾ EMV14 =14W Low Voltage Emergency Module with Remote Test Switch ⁽⁷⁾ ETRD =Emergency transfer device ⁽²⁹⁾ WPN = WaveLinX PRO Wireless Node without Sensor ^{(15) (36)} WLN = WaveLinX LITE Wireless Node without Sensor (not compatible with Tunable White) ^{(35) (36)}
Tunable White Blank =1000 lumens 1 =120V 1500-3000 lumens (integral driver only) 2 =277V 1500-3000 lumens (integral driver only) 3 =347V Step down transformer (Limited to 1000 lumens with remote driver)	Tunable White DE010W2N2765 =0-10V 0.1% Dimming, 2700-6500K DE010W2N2050 =0-10V 0.1% Dimming, 2000-5000K D5LTW2N2765 =DALI T6 0.1% Dimming, 2700-6500K D5LTW2N2050 =DALI T6 0.1% Dimming, 2000-5000K		
BioUp Tunable White Blank =800 lumens 1 =120V 1000-2000 lumens (integral driver only) 2 =277V 1000-2000 lumens (integral driver only) 3 =347V Step down transformer (Limited to 800 lumens with remote driver)	BioUp Tunable White DE010B2750 =0-10V 0.1% dimming, tunable white 2700-6500K DE010B35 = 0-10V 0.1% dimming, static white 3500K DE010B40 = 0-10V 0.1% dimming, static white 4000K DE010B50 = 0-10V 0.1% dimming, static white 5000K D5LTB2750 =DALI T6 0.1% dimming, tunable white 2700-6500K D5LTB35 = DALI T6 0.1% dimming, static white 3500K D5LTB40 = DALI T6 0.1% dimming, static white 4000K D5LTB50 = DALI T6 0.1% dimming, static white 5000K		

SAMPLE ORDER NUMBER: **EU6C08259030D2W**

Domestic Preferences ⁽¹⁾	Power Module	Lumen Levels ⁽²⁾	Color
[Blank] =Standard BAA =Buy American Act TAA =Trade Agreements Act	EU6C =6-inch Universal LED Module	BioUp 0820B =800, 1000, 1500, 2000 lumens, 90 CRI ⁽³⁰⁾	9035 = Static 3500K 9040 =Static 4000K 9050 =Static 5000K 902750 =BioUp Tunable White 2700K-5000K
		Dim 2 Warm 08259030D2W =800-2500 lumen, 90 CRI, Dim 2 Warm ⁽³⁰⁾	
		Tunable white 1030W2N902765 =1000, 1500, 2000, 2500, 3000 lumens, 90 CRI, tunable white 2700K-6500K ⁽³¹⁾ 1030W2N902050 =1000, 1500, 2000, 2500, 3000 lumens, 90 CRI, tunable white 2000K-5000K ⁽³¹⁾	

SAMPLE ORDER NUMBER: **6LBM2H**

Domestic Preferences ⁽¹⁾	Trim	Reflector	Flange	Finish
[Blank] =Standard BAA =Buy American Act (spun trim only)	6LB =6-inch Reflector	S =Shallow spun aluminum PS =Non-Conductive Shallow (dead front), white ^{(16) (17)} CS =Cast shallow, die cast aluminum	0 =White polymer trim ring 1 =Self flanged ⁽¹⁸⁾ 2 =White painted self flanged 4 =Knife edge rimless use with die cast only ⁽¹⁹⁾	L =Specular Clear ⁽²⁰⁾ H =Semi-Specular Clear ⁽²⁰⁾ WMH =Warm Haze ⁽²⁰⁾ WH =Wheat ⁽²⁰⁾ GPH =Graphite Haze ⁽²⁰⁾
				B =Specular Black ⁽²⁰⁾ MW =Matte White MB =Matte Black ⁽²¹⁾ MMS =Matte Metallic Silver ⁽²¹⁾

Continued on next page.

Multi-line Order Information

REQUIRED if Remote Driver (R) is specified

SAMPLE ORDER NUMBER: **RC10010D010TREM7**

Domestic Preferences ⁽¹⁾	Remote Drivers ⁽⁶⁾	Lumens ^{(2) (14)}	Color Control
[Blank] =Standard TAA =Trade Agreements Act	RC100 =Remote 100ft ⁽⁸⁾ RC75 =Remote 75ft ⁽⁸⁾ RC50 =Remote 50ft ⁽⁸⁾ RC25 =Remote 25ft	RC15 =Remote 15ft RC5 =Remote 5ft RC2 =Remote 2ft	08 =800 lumens 10 =1000 lumens 15 =1500 lumens 20 =2000 lumens ⁽²⁾ 25 =2500 lumens 30 =3000 lumens ⁽³⁾

Voltage	Driver	Options ^{(6) (25) (27) (28)}
Dim-to Warm Blank =120-277V 800-2500 lumens 3 =347V (D010 driver 800-2500 lumens)	Dim-to Warm D010 =0-10V 1% dimming D010TR =0-10V or (120V) phase cut 1% dimming DE010 =0-10V linear 0.1% dimming D5LT =DALI T6 Logarithmic 0.1% Dimming DMX =DMX/RDM Logarithmic 0.1% Dimming ⁽⁵⁾ DMXC5 =DMX/RDM Logarithmic 0.1 % Dimming with RJ45 connection ⁽⁵⁾ DLE =Lutron Ecosystem 1-100% dimming DLVP =Low voltage dimming 1-100% for use with DLVP system ⁽⁶⁾	EMBOD =Bodine® Emergency Module with Remote Test Switch ⁽¹⁰⁾ EMBOD6ST =Bodine® 6W Self Test Emergency Module with Remote Test Switch EM7 =7W Emergency Module with Remote Test Switch EM14 =14W Emergency Module with Remote Test Switch EMBOD7ST =Bodine® Self Test Emergency Module with Remote Test Switch ⁽¹⁰⁾ EMV7 =7W Low Voltage Emergency Module with Remote Test Switch ⁽⁷⁾ EMV14 =14W Low Voltage Emergency Module with Remote Test Switch ⁽⁷⁾ ETRD =Emergency transfer device ⁽²⁹⁾ WPST =Factory installed Wavelinx PRO Sensor Kit ^{(11) (13)} WLST =Factory installed Wavelinx LITE Sensor Kit ^{(11) (12)} WPN = WaveLinX PRO Wireless Node without Sensor ^{(15) (84)} WLN = WaveLinX LITE Wireless Node without Sensor (not compatible with Tuneable White) ^{(35) (84)}
Tunable White Blank =1000 lumens 3 =347V Step down transformer (Limited to 1000 lumens)	Tunable White DE010W2N2765 =0-10V 0.1% Dimming, 2700-6500K DE010W2N2050 =0-10V 0.1% Dimming, 2000-5000K D5LTW2N2765 =DALI T6 0.1% Dimming, 2700-6500K D5LTW2N2050 =DALI T6 0.1% Dimming, 2000-5000K	
BioUp Tunable White Blank =800 lumens 3 =347V Step down transformer (Limited to 800 lumens)	BioUp Tunable White DE010B2750 =0-10V 0.1% dimming, tunable white 2700-6500K DE010B35 = 0-10V 0.1% dimming, static white 3500K DE010B40 = 0-10V 0.1% dimming, static white 4000K DE010B50 = 0-10V 0.1% dimming, static white 5000K D5LTB2750 =DALI T6 0.1% dimming, tunable white 2700-6500K D5LTB35 = DALI T6 0.1% dimming, static white 3500K D5LTB40 = DALI T6 0.1% dimming, static white 4000K D5LTB50 = DALI T6 0.1% dimming, static white 5000K	

Accessories (Order separately) ⁽²²⁾			
TRM6P =White Metal Trim Ring ⁽²³⁾ LGSKT6IP66 =IP66 Gasket Kit PRR6 =Rimless Plaster Ring ⁽²⁴⁾ RKP6 =Knife Edge plaster Ring ⁽²⁴⁾	RPM6MW =Rimless Millwork Ring, Matte White ⁽²³⁾ RPM6MB =Rimless Millwork Ring, Matte Black ⁽²³⁾ RKM6MW =Knife Edge Millwork Ring, Matte White ⁽²⁴⁾ RKM6MB =Knife Edge Millwork Ring, Matte Black ⁽²⁴⁾ HSA6 =Slope Adapter for 6" Aperture Housings, Specify Slope ⁽³²⁾	Bar Hangers TAA-HB26 =C-channel Bar Hanger, 26" Long, Pair ⁽¹⁾ HB26 =C-channel Bar Hanger, 26" Long, Pair HB50 =C-channel Bar Hanger, 50" Long, Pair RMB22 =Wood Joist Bar Hanger, 22" Long, Pair	Connected Lighting Systems ^{(6) (11)} WPST = Field installed WaveLinX PRO Sensor Kit ⁽¹³⁾ WLST = Field installed WaveLinX LITE Sensor Kit ⁽¹²⁾

Notes:

- Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analysed under domestic preference requirements. Offered with shallow (S) spun aluminum.
- Nominal Lumens will vary depending on selected color, CRI, driver and reflector finish. Referenc IES files.
- W2N for 3000 lumens and BioUp for 2000 lumens is marked spacing and must be installed with the following minimum spacing.
- Center to center of adjacent luminaires: 36"
- Center of luminaire to side of building member: 36"
- Minimum overhead: 0.5"
- DMX fixtures default to full on upon loss of DMX signal.
- Not available with Chicago Plenum.
- ULus listed only
- Offered up to 2500 lumens with D2W and 3000 with W2N and 2000 with BioUp
- Not available for W2N/BioUp

- Refer to system specifications for additional information, features, and benefits. Order either factory installed option or accessory. Use with 0-10V driver.
- WLST = WaveLinX LITE tilemount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinX LITE system specifications)
- WPST = WaveLinX PRO wireless sensor kit for daylight dimming, PIR motion sensing, and optional RLTS - Real Time Location Services, use with 0-10V only.
- IC rated up to 800 lumens for D2W and BioUp and 1000 lumens for W2N
- WPN = WaveLinX PRO wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor, Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only.
- PS available in self-flanged MW finish only
- Offered up to 2000 lumens
- Flange is the same finish as the reflector
- Requires knife edge ring
- Anodized or spun reflectors
- Die cast only

- Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.
- Order trim with polymer trim ring.
- Order die cast trim with flange type 4
- For remote driver order emergency module with the remote driver
- 120V-277V
- Non-IC
- Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others)
- IC rated for 800 lumens
- IC rated for 1000 lumens
- WLN = WaveLinX LITE wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with D010 or DE010 drivers only.
- Not compatible with 347V or Chicago plenum.

Continued on next page.