

# CERTIFICATE OF COMPLIANCE

**Certificate Number** UL-US-L76559-12-03309102-5  
**Report Reference** E76559-20190330  
**Date** 14-Dec-2023

**Issued to:** Cooper Lighting, LLC  
1121 HIGHWAY 74 S  
PEACHTREE CITY, GA 30269-3019  
United States

**This is to certify that representative samples of** IFFX - Luminaire Fittings  
See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the Standard(s) indicated on this Certificate.


**Standard(s) for Safety:** UL 1598, 5th Ed., Issue Date: 2021-03-26, Revision Date: 2021-06-18

**Additional Information:** See the UL Online Certifications Directory at <https://iq.ulprospector.com> for additional information

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.

  
Deborah Jennings-Conner, VP Regulatory Services

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>




# CERTIFICATE OF COMPLIANCE

**Certificate Number** UL-US-L76559-12-03309102-5  
**Report Reference** E76559-20190330  
**Date** 14-Dec-2023

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Model	Category Description
HC56R	Luminaire Fittings - Rough In Sections
HC56R, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HC56RCP, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HC56RCP	Luminaire Fittings - Rough In Sections
HC6, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver	Luminaire Fittings - Rough In Sections

  
 Deborah Jennings-Conner, VP Regulatory Services




UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

# CERTIFICATE OF COMPLIANCE

**Certificate Number**    UL-US-L76559-12-03309102-5  
**Report Reference**     E76559-20190330  
**Date**                      14-Dec-2023

dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	
HC605	Luminaire Fittings - Rough In Sections
HC607	Luminaire Fittings - Rough In Sections
HC6CP, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HC6R, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HC6RCP, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HCSQ6	Luminaire Fittings
HCSQ6CP	Luminaire Fittings

  
 Deborah Jennings-Conner, VP Regulatory Services



UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

# CERTIFICATE OF COMPLIANCE

**Certificate Number** UL-CA-L76559-32-03309102-5  
**Report Reference** E76559-20190330  
**Date** 14-Dec-2023

**Issued to:** Cooper Lighting, LLC  
1121 HIGHWAY 74 S  
PEACHTREE CITY, GA 30269-3019  
United States

**This is to certify that representative samples of** IFFX7 - Luminaire Fittings Certified for Canada  
See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the Standard(s) indicated on this Certificate.

**Standard(s) for Safety:** CSA C22.2 NO. 250.0:21, 5th Ed., Issue Date: 2021-03-26,  
Revision Date: 2021-06-18

**Additional Information:** See the UL Online Certifications Directory at  
<https://iq.ulprospector.com> for additional information

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.

*Deborah Jennings-Conner*

Deborah Jennings-Conner, VP Regulatory Services

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



# CERTIFICATE OF COMPLIANCE

**Certificate Number** UL-CA-L76559-32-03309102-5  
**Report Reference** E76559-20190330  
**Date** 14-Dec-2023

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Model	Category Description
HC56R	Luminaire Fittings - Rough In Sections
HC56RCP	Luminaire Fittings - Rough In Sections
HC6, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HC605	Luminaire Fittings - Rough In Sections
HC607	Luminaire Fittings - Rough In Sections
HC6CP, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HC6R, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm	Luminaire Fittings - Rough In Sections

*Deborah Jennings-Conner*  
 Deborah Jennings-Conner, VP Regulatory Services




UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

# CERTIFICATE OF COMPLIANCE

**Certificate Number** UL-CA-L76559-32-03309102-5  
**Report Reference** E76559-20190330  
**Date** 14-Dec-2023

fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	
HC6RCP, followed by 05 = 0500 lm fixed output (0.150 A), 07 = 07050 lm fixed output (0.200 A), 10 = 1000 lm fixed output (0.250 A), 15 = 1500 lm fixed output (0.350 A), 20 = 2000 lm fixed output (0.500 A), 25 = 2500 lm fixed output (0.650 A), 30 = 3000 lm fixed output (0.700 A), 35 = 3500 lm fixed output (0.875 A), 40 = 4000 lm fixed output (1.050 A), 45 = 4500 lm fixed output (1.140 A), 50 = 5000 lm fixed output (1.230 A), 55 = 5500 lm fixed output (1.320 A), 60 = 6000 lm fixed output (1.400 A) followed by D010 = Driver dimming type (e.g. 0-10V) followed by REM7 or REM14 = Emergency Battery type (optional)	Luminaire Fittings - Rough In Sections
HCSQ6	Luminaire Fittings
HCSQ6CP	Luminaire Fittings

  
 Deborah Jennings-Conner, VP Regulatory Services



UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>