

| | | | | | |
|-------------|--|-----------|--|------|--|
| Project | | Catalog # | | Type | |
| Prepared by | | Notes | | Date | |



HALO

SMX14 Edgeless Surface Mount LED Downlights

The SMX series redefines the surface downlighting experience. With a fully luminous lens face, this series provides exceptional light quality with a sleek, edgeless design that blends effortlessly into any ceiling. The SMX fixtures are engineered to offer a versatile downlighting solution with selectable lumens and color temperatures including dim-to-warm in flicker-free phase cut or 0-10V dimming options. The innovative mounting method ensures a hassle-free installation that seats the fixture securely against the ceiling in either junction boxes or recessed housings. Upgrade your lighting experience with the SMX series and enjoy a seamless blend of style and functionality.

Typical Applications

Residential • Multifamily • Hospitality • Healthcare • Retail

Interactive Menu

- Order Information [page 2](#)
- Product Specifications [page 3](#)
- Energy Data [page 4](#)
- Photometric Data [page 5](#)
- Product Warranty

Product Certification¹



Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.



Product Features



Top Product Features

- 14" Surface Mount Edgeless Design in Round or Square
- Fully luminous edge-to-edge lens with no front face flange
- **Phase Cut Dimming - 6-Position Switch:** 5-color Field SeleCCTable (2700K,3000K,3500K,4000K,5000K) + Dim-to-Warm (3000K dims to 1800K); 90+ CRI
- **0-10V Dimming - 5-Position Switch:** 5-color Field SeleCCTable (2700K,3000K,3500K,4000K,5000K); 90+ CRI
- **Brightness:** Lumen Select 1200/1600/2000 lm (nominal)
- **Dimming:** Dims to less than 5% with compatible dimmers in either phase cut LE/TE, 120V or 0–10V, 120–277V
- Mounting bracket, hardware
- Edgeless Decorative Overlays (sold separately)
- AIR-TITE, wet location-listed, IC-rated
- 50,000 hrs of maintenance-free operation
- 5-year warranty

Dimensional and Mounting Details



additional product diagrams

Order Information



| Catalog Number | Description | Lumens (nominal) | CCT | Finish | Driver Compatibility | Packaging |
|----------------|--|-------------------------------------|--|-------------|--------------------------|-------------------------|
| SMX14RLSFSD2W | 14" Round Surface Mount LED Downlight | Lumen Selectable: 1200/1600/2000 lm | 90+ CRI, Field Selectable CCT: Dim-to-Warm/2700/3000/3500/4000/5000K | Matte White | Phase Cut LE/TE 5%; 120V | Plastic-free recyclable |
| SMX14RLSFS010 | 14" Round Surface Mount LED Downlight | Lumen Selectable: 1200/1600/2000 lm | 90+ CRI, Field Selectable CCT: 2700/3000/3500/4000/5000K | Matte White | 0-10V 5%; 120-277V | Plastic-free recyclable |
| SMX14SLSFSD2W | 14" Square Surface Mount LED Downlight | Lumen Selectable: 1200/1600/2000 lm | 90+ CRI, Field Selectable CCT: Dim-to-Warm/2700/3000/3500/4000/5000K | Matte White | Phase Cut LE/TE 5%; 120V | Plastic-free recyclable |
| SMX14SLSFS010 | 14" Square Surface Mount LED Downlight | Lumen Selectable: 1200/1600/2000 lm | 90+ CRI, Field Selectable CCT: 2700/3000/3500/4000/5000K | Matte White | 0-10V 5%; 120-277V | Plastic-free recyclable |

| Accessories | | |
|----------------|-------------------------------|-----------------------|
| Catalog Number | Description | Finish |
| SMX14RTRMMW | 14" Round Decorative Overlay | Paintable Matte White |
| SMX14RTRMB | 14" Round Decorative Overlay | Matte Black |
| SMX14RTRMSN | 14" Round Decorative Overlay | Satin Nickel |
| SMX14STRMMW | 14" Square Decorative Overlay | Paintable Matte White |
| SMX14STRMB | 14" Square Decorative Overlay | Matte Black |
| SMX14STRMSN | 14" Square Decorative Overlay | Satin Nickel |

Designer Trims



Compatible Junction Boxes²

| | |
|---|--|
|  <p>Octagon Steel Light Fixture w/Fan Box 4" x 4" x 2-1/8"</p> |  <p>Round Old Work Box (Plastic) 4-1/4" Diameter flange (3-1/2" I.D.) x 2-3-4"</p> |
|  <p>Square Steel Deep Box 4" x 4" x 2-1/8"</p> |  <p>Round New Work Fixture Box (Plastic) w/Bar Hanger 4" x 2-3/16"</p> |
|  <p>Round New Work Fixture Box (Plastic) 4" Diameter x 2-3-16"</p> |  <p>TP316 For non-metallic cable 4" x 4" x 2-1/8"</p> |
|  <p>Round New Work Ceiling Box (Plastic) 3-1/2" Diameter x 2-3-4"</p> |  <p>TP317 For metal clad cable 4" x 4" x 2-1/8"</p> |

2. This is a representative list of compatible junction boxes only. Information contained in this literature about other manufacturers' products is from published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Cooper Lighting Solutions makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must determine that site conditions are suitable to allow proper installation of the mounting bracket in the box.

Product Specifications

Module

- The LED surface mount downlight consists of an LED array, optical assembly, driver, and edgeless trim
- Achieves L70 at 50,000 hrs in IC (insulation contact) and non-IC applications

Selectable System

- Use the CCT select switch to choose between Dim-to-Warm (D2W), 2700K, 3000K, 3500K, 4000K, and 5000K CCT
 - Note:** D2W only available for phase cut fixtures
- Dim-to-Warm option starts at 3000K and warms to 1800K as the fixture dims
- Factory default is set to 3000K
- Use the 3-position Lumen Select switch to choose the brightness level (Low, Medium, High)
- Lumen Select factory default is to the highest lumen option

LED Array

- Mid-power LED array provides a uniform light source with high efficiency and no pixilation
- 90+ CRI minimum, R9 greater than 50
- Color accuracy at 3SCDM at the endpoints provides color consistency and uniformity

Driver

- Integral 120V 60Hz constant current driver provides noise-free, high-efficiency operation
- Phase Cut Dimming: Continuous, flicker-free dimming from 100% to 5% with compatible leading or trailing edge (LE/TE) 120V phase cut dimmers; (See Dimming Guide for compatible dimmers.)
- 0-10V Dimming: Continuous, flicker-free dimming from 100% to 5% with compatible 0-10V 120-277V dimmer; (See Dimming Guide for compatible dimmers.)

- Tip: For optimal dimming performance, consider dimmers with low-end trim adjustment; Note that some dimmers require a neutral wire in the box.
- Wiring: Includes optional inline electrical orange LED Quick Connect

Electrical Junction Box Mounting

- Twist and lock steel mounting bracket to fit snugly to the ceiling
- Installs from below the ceiling in most 30 (3-1/2") and 40 (4") standard round/octagonal junction boxes
- May be used in compatible electrical junction boxes in direct contact with insulation
- Installer must ensure compatibility of fit, wiring, and proper mounting in the electrical junction box. This includes all applicable national and local electrical along with building coded NEMA LSD 57-2013.
- Reference installation instructions for complete mounting steps

Gasket

- Closed-cell gasket achieves restrictive airflow requirements without additional caulking.

Decorative Overlays (sold separately)

- Overlays cover the edge of the fixture while maintaining the edgeless design and are sold as an accessory for a designer finish
 - Paintable Matte White
 - Satin Nickel
 - Matte Black




Compliance

- cULus certified for US and Canada
- Wet Location listed for showers and covered outdoor ceilings
- Airtight per ASTM-E283
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant*
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy LED compliance under JA8*, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2022 JA8 High Efficacy Lighting

Warranty

- Five year limited warranty, consult website for details. www.cooperlighting.com/warranty

Dimensional and Mounting Details



Energy Data

| | 120V (Triac) | | 120V-277V (0-10V) | | | |
|-------------------|---------------|----------------|-------------------|---------------|---------------|---------------|
| | Round | Square | Round | | Square | |
| | SMX14RLSFS2W | SMX14SLSFS2W | SMX14RLSFS010 | | SMX14SLSFS010 | |
| Lumens | 1200 | 1200 | 1200 | 1200 | 1200 | 1200 |
| Input Voltage (V) | 120V | 120V | 120V | 277V | 120V | 277V |
| Input Current (A) | 0.1324A | 0.13137A | 0.1202A | 0.054A | 0.12043A | 0.054A |
| Input Power (W) | 15.33W | 15.2W | 14.35W | 14.207W | 14.37W | 14.11W |
| Efficiency | 83.23% | 83.10% | 84.10% | 83.10% | 84.60% | 83.90% |
| Inrush (A) | 1.55A@56usec | 1.52A@64.8usec | 2.96A@38usec | 4.5A@62usec | 2.96A@38usec | 4.5A@62usec |
| THDi (%) | 11.80% | 11.80% | 6.30% | 17.10% | 6.80% | 17.10% |
| PF | 0.964 | 0.963 | 0.964 | 0.925 | 0.994 | 0.924 |
| T Ambient | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C |
| Sound Rating | <22dBA | <22dBA | <22dBA | <22dBA | <22dBA | <22dBA |
| Efficacy(LPW) | 95.09 | 93.01 | 97.85 | 97.85 | 97.42 | 97.42 |
| Lumens | 1600 | 1600 | 1600 | 1600 | 1600 | 1600 |
| Input Voltage (V) | 120V | 120V | 120V | 277V | 120V | 277V |
| Input Current (A) | 0.17437A | 0.17267A | 0.17087A | 0.076A | 0.17083A | 0.071A |
| Input Power (W) | 20.43W | 20.22W | 20.41W | 20.7W | 20.41W | 20.87W |
| Efficiency | 82.89% | 83.02% | 84.70% | 85% | 85.20% | 85.10% |
| Inrush (A) | 1.55A@56usec | 1.52A@64.8usec | 2.96A@38usec | 4.5A@62usec | 2.96A@38usec | 4.5A@62usec |
| THDi (%) | 10.60% | 10.60% | 7.40% | 11.30% | 7.40% | 11.30% |
| PF | 0.976 | 0.976 | 0.976 | 0.961 | 0.995 | 0.961 |
| T Ambient | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C |
| Sound Rating | <22dBA | <22dBA | <22dBA | <22dBA | <22dBA | <22dBA |
| Efficacy(LPW) | 92.77 | 91.26 | 94.97 | 94.97 | 94.73 | 94.73 |
| Lumens | 2000 | 2000 | 2000 | 2000 | 2000 | 2000 |
| Input Voltage (V) | 120V | 120V | 120V | 277V | 120V | 277V |
| Input Current (A) | 0.22180A | 0.22027A | 0.21513A | 0.088A | 0.2151A | 0.094A |
| Input Power (W) | 26.16W | 25.96W | 25.69W | 25.9W | 25.68W | 25.78W |
| Efficiency | 82.20% | 82.08% | 84.60% | 85.40% | 85.20% | 85.50% |
| Inrush (A) | 1.55A@56usec | 1.52A@64.8usec | 2.96A@38usec | 4.5A@62usec | 2.96A@38usec | 4.5A@62usec |
| THDi (%) | 10.40% | 10.20% | 9.20% | 8.50% | 9.40% | 8.50% |
| PF | 0.983 | 0.982 | 0.983 | 0.978 | 0.995 | 0.977 |
| T Ambient | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C | -30 to +40 °C |
| Sound Rating | <22dBA | <22dBA | <22dBA | <22dBA | <22dBA | <22dBA |
| Efficacy(LPW) | 89.64 | 88.45 | 92.11 | 92.11 | 91.96 | 91.96 |


| SMX14RLSFS2W (Equivalent to 125W Incandescent) | | | | |
|--|-------|--------|------|-----|
| CCT | Watts | Lumens | LPW | CRI |
| 2700K | 26.4 | 2250 | 85.2 | 92 |
| 3000K | 26.5 | 2300 | 86.8 | 93 |
| 3500K | 26.5 | 2350 | 88.7 | 94 |
| 4000K | 26.5 | 2400 | 90.6 | 94 |
| 5000K | 26.4 | 2445 | 92.6 | 92 |

| SMX14SLSFS2W (Equivalent to 125W Incandescent) | | | | |
|--|-------|--------|------|-----|
| CCT | Watts | Lumens | LPW | CRI |
| 2700K | 26.2 | 2210 | 84.4 | 92 |
| 3000K | 26.3 | 2250 | 85.6 | 93 |
| 3500K | 26.3 | 2290 | 87.1 | 94 |
| 4000K | 26.3 | 2325 | 88.4 | 94 |
| 5000K | 26.2 | 2365 | 90.3 | 93 |

| SMX14RLSFS010 (Equivalent to 125W Incandescent) | | | | |
|---|-------|--------|------|-----|
| CCT | Watts | Lumens | LPW | CRI |
| 2700K | 26.0 | 2270 | 87.3 | 92 |
| 3000K | 26.1 | 2310 | 88.5 | 94 |
| 3500K | 26.1 | 2345 | 89.8 | 94 |
| 4000K | 26.0 | 2385 | 91.7 | 94 |
| 5000K | 26.0 | 2420 | 93.1 | 92 |

| SMX14SLSFS010 (Equivalent to 125W Incandescent) | | | | |
|---|-------|--------|------|-----|
| CCT | Watts | Lumens | LPW | CRI |
| 2700K | 25.9 | 2220 | 85.7 | 93 |
| 3000K | 25.9 | 2260 | 87.3 | 93 |
| 3500K | 25.9 | 2300 | 88.8 | 95 |
| 4000K | 25.9 | 2340 | 90.3 | 94 |
| 5000K | 25.7 | 2390 | 93.0 | 93 |


Photometric Data




SMX14RLSFSD2W-2000LM-3000K

Spacing criterion:
(0-180) 1.27 | (90-270) 1.27 |
(Diagonal) 1.39
Beam Angle: 115°
Field Angle: 162°
Lumens: 2300
Input Watts: 26.5 W
Efficacy: 86.8 LPW
UGR: 20
Test Report: P869662

| Zonal Lumen | Lumens | % Lumens |
|-------------|--------|----------|
| 0-30 | 613 | 26.7 |
| 0-40 | 1009 | 43.9 |
| 0-60 | 1804 | 78.4 |
| 0-90 | 2300 | 100 |




| | |
|----------|-----------|
| TM-30-15 | Rf = 92 |
| | Rg = 99 |
| CRI/CIE | Ra = 95.3 |
| | R9 = 71.5 |




SMX14SLSFSD2W-2000LM-3000K

Spacing criterion:
(0-180) 1.27 | (90-270) 1.27 |
(Diagonal) 1.39
Beam Angle: 115°
Field Angle: 162°
Lumens: 2250
Input Watts: 26.3 W
Efficacy: 85.6 LPW
UGR: 19
Test Report: P869692

| Zonal Lumen | Lumens | % Lumens |
|-------------|--------|----------|
| 0-30 | 601 | 26.7 |
| 0-40 | 988 | 43.9 |
| 0-60 | 1765 | 78.5 |
| 0-90 | 2250 | 100 |



| | |
|----------|-----------|
| TM-30-15 | Rf = 92 |
| | Rg = 99 |
| CRI/CIE | Ra = 95.5 |
| | R9 = 72.9 |




SMX14RLSFS010-2000LM-3000K

Spacing criterion:
(0-180) 1.27 | (90-270) 1.27 |
(Diagonal) 1.39
Beam Angle: 115°
Field Angle: 162°
Lumens: 2310
Input Watts: 26.1 W
Efficacy: 88.5 LPW
UGR: 20
Test Report: P869647

| Zonal Lumen | Lumens | % Lumens |
|-------------|--------|----------|
| 0-30 | 616 | 26.7 |
| 0-40 | 1013 | 43.9 |
| 0-60 | 1811 | 78.4 |
| 0-90 | 2310 | 100 |




| | |
|----------|-----------|
| TM-30-15 | Rf = 92 |
| | Rg = 99 |
| CRI/CIE | Ra = 95.3 |
| | R9 = 71.5 |



SMX14SLSFS010-2000LM-3000K

Spacing criterion:
(0-180) 1.27 | (90-270) 1.27 |
(Diagonal) 1.39
Beam Angle: 115°
Field Angle: 162°
Lumens: 2260
Input Watts: 25.9 W
Efficacy: 87.3 LPW
UGR: 19
Test Report: P869677

| Zonal Lumen | Lumens | % Lumens |
|-------------|--------|----------|
| 0-30 | 604 | 26.7 |
| 0-40 | 993 | 43.9 |
| 0-60 | 1773 | 78.5 |
| 0-90 | 2260 | 100 |



| | |
|----------|-----------|
| TM-30-15 | Rf = 92 |
| | Rg = 99 |
| CRI/CIE | Ra = 95.5 |
| | R9 = 72.9 |

