

Supplemental Energy and Performance Data: 100W-200W

Nominal Power (Watts)	100	110	120	130	140	150	160	170	180	190	200
Actual Power (Watts)	103W	113	123	133	143	153	163	173	183	193	203
Wattage Label	100	110	120	130	140	150	160	170	180	190	200
Input Current @ 120V (A)	0.86	0.94	1.02	1.10	1.18	1.26	1.34	1.42	1.50	1.59	1.70
Input Current @ 277V (A)	0.37	0.42	0.45	0.49	0.52	0.56	0.59	0.62	0.66	0.69	0.73
Input Current @ 347V (A)	0.30	0.33	0.36	0.39	0.41	0.44	0.47	0.50	0.53	0.56	0.59
Input Current @ 480V (A)	0.21	0.24	0.26	0.28	0.30	0.32	0.34	0.36	0.38	0.40	0.42

70 CRI, 2200K												
Nominal Power (Watts)		100	110	120	130	140	150	160	170	180	190	200
T2R	Lumens	15,419	16,752	18,015	19,339	20,497	21,664	22,837	23,936	25,050	26,156	27,439
	Lumens per Watt	150	149	148	147	145	144	142	141	139	138	135
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
T2U	Lumens	15,425	16,758	18,022	19,346	20,505	21,672	22,845	23,945	25,059	26,165	27,449
	Lumens per Watt	150	149	148	147	145	144	142	141	139	138	135
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
T3	Lumens	15,402	16,733	17,995	19,317	20,474	21,640	22,811	23,909	25,022	26,126	27,408
	Lumens per Watt	149	149	148	146	145	144	142	141	139	138	135
	BUG Rating	B2 U0 G2	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
T4W	Lumens	15,015	16,313	17,542	18,832	19,960	21,096	22,238	23,308	24,393	25,469	26,719
	Lumens per Watt	146	145	144	143	141	140	138	137	136	134	131
	BUG Rating	B2 U0 G2	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
5WQ	Lumens	15,099	16,404	17,641	18,938	20,072	21,214	22,363	23,439	24,530	25,613	26,869
	Lumens per Watt	146	146	145	143	142	141	139	138	136	135	132
	BUG Rating	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3

70 CRI, 2700K												
Nominal Power (Watts)		100	110	120	130	140	150	160	170	180	190	200
T2R	Lumens	17,005	18,475	19,868	21,328	22,605	23,892	25,186	26,398	27,627	28,846	30,261
	Lumens per Watt	165	164	163	162	160	158	157	155	153	152	149
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
T2U	Lumens	18,482	19,875	21,336	22,614	23,901	25,195	26,408	27,637	28,857	30,272	31,380
	Lumens per Watt	164	163	162	160	158	157	156	154	152	149	147
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B4 U0 G4	B4 U0 G4
T3	Lumens	16,986	18,454	19,846	21,304	22,580	23,865	25,157	26,369	27,596	28,814	30,227
	Lumens per Watt	165	164	163	161	160	158	157	155	153	152	148
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4
T4W	Lumens	16,559	17,990	19,347	20,769	22,013	23,266	24,525	25,706	26,902	28,089	29,467
	Lumens per Watt	161	160	159	157	156	154	153	151	149	148	145
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4
5WQ	Lumens	16,652	18,091	19,455	20,885	22,136	23,396	24,663	25,850	27,053	28,247	29,633
	Lumens per Watt	162	161	159	158	157	155	153	152	150	149	145
	BUG Rating	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3

70 CRI, 3000K												
Nominal Power (Watts)		100	110	120	130	140	150	160	170	180	190	200
T2R	Lumens	17,622	19,145	20,588	22,102	23,425	24,759	26,099	27,356	28,629	29,892	31,359
	Lumens per Watt	171	170	169	167	166	164	162	161	159	157	154
	BUG Rating	B3 U0G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
T2U	Lumens	17,629	19,152	20,596	22,110	23,434	24,768	26,109	27,366	28,639	29,903	31,370
	Lumens per Watt	171	170	169	168	166	164	162	161	159	157	154
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B4 U0 G4	B4 U0 G4
T3	Lumens	17,602	19,124	20,565	22,077	23,399	24,731	26,070	27,325	28,597	29,859	31,324
	Lumens per Watt	171	170	169	167	166	164	162	161	159	157	154
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4
T4W	Lumens	17,160	18,643	20,048	21,522	22,811	24,109	25,414	26,638	27,878	29,108	30,536
	Lumens per Watt	166	166	164	163	161	160	158	157	155	153	150
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4
5WQ	Lumens	17,256	18,748	20,161	21,643	22,939	24,245	25,557	26,788	28,034	29,271	30,708
	Lumens per Watt	167	167	165	164	162	161	159	158	156	154	151
	BUG Rating	B4 U0 G2	B4 U0 G2	B4 U0 G2	B4 U0 G2	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3

70 CRI, 4000K												
Nominal Power (Watts)		100	110	120	130	140	150	160	170	180	190	200
T2R	Lumens	18,503	20,102	21,618	23,207	24,597	25,997	27,404	28,723	30,060	31,387	32,927
	Lumens per Watt	179	179	177	176	174	172	171	169	167	165	162
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B4 U0 G4
T2U	Lumens	18,510	20,110	21,626	23,215	24,606	26,006	27,414	28,734	30,071	31,398	32,939
	Lumens per Watt	180	179	177	176	174	172	171	169	167	165	162
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B4 U0 G4	B4 U0 G4	B4 U0 G4
T3	Lumens	18,482	20,080	21,594	23,181	24,569	25,968	27,373	28,691	30,026	31,351	32,890
	Lumens per Watt	179	178	177	176	174	172	170	169	167	165	161
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4
T4W	Lumens	18,018	19,575	21,051	22,598	23,951	25,315	26,685	27,970	29,272	30,563	32,063
	Lumens per Watt	175	174	173	171	170	168	166	165	163	161	157
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4
5WQ	Lumens	18,119	19,685	21,169	22,725	24,086	25,457	26,835	28,127	29,436	30,735	32,243
	Lumens per Watt	176	175	174	172	170	169	167	166	164	162	158
	BUG Rating	B4 U0 G2	B4 U0 G2	B4 U0 G2	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3

70 CRI, 5000K												
Nominal Power (Watts)		100	110	120	130	140	150	160	170	180	190	200
T2R	Lumens	16,869	18,503	20,102	21,618	23,207	24,597	25,997	27,404	28,723	30,060	31,387
	Lumens per Watt	181	179	179	177	176	174	172	171	169	167	165
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3
T2U	Lumens	18,510	20,110	21,626	23,215	24,606	26,006	27,414	28,734	30,071	31,398	32,939
	Lumens per Watt	180	179	177	176	174	172	171	169	167	165	162
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B4 U0 G4	B4 U0 G4	B4 U0 G4
T3	Lumens	18,482	20,080	21,594	23,181	24,569	25,968	27,373	28,691	30,026	31,351	32,890
	Lumens per Watt	179	178	177	176	174	172	170	169	167	165	161
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4
T4W	Lumens	18,018	19,575	21,051	22,598	23,951	25,315	26,685	27,970	29,272	30,563	32,063
	Lumens per Watt	175	174	173	171	170	168	166	165	163	161	157
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4
5WQ	Lumens	18,119	19,685	21,169	22,725	24,086	25,457	26,835	28,127	29,436	30,735	32,243
	Lumens per Watt	176	175	174	172	170	169	167	166	164	162	158
	BUG Rating	B4 U0 G2	B4 U0 G2	B4 U0 G2	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3

Supplemental Energy and Performance Data: 210W-300W

Nominal Power (Watts)	210	220	230	240	250	260	270	280	290	300
Actual Power (Watts)	213W	223W	233W	243W	253W	263W	273W	283W	293W	303W
Wattage Label	210	220	230	240	250	260	270	280	290	300
Input Current @ 120V (A)	1.78	1.86	1.93	2.01	2.09	2.17	2.25	2.34	2.42	2.50
Input Current @ 277V (A)	0.77	0.82	0.86	0.89	0.92	0.96	0.99	1.03	1.06	1.10
Input Current @ 347V (A)	0.62	0.66	0.68	0.71	0.74	0.77	0.79	0.83	0.86	0.88
Input Current @ 480V (A)	0.44	0.48	0.50	0.52	0.54	0.56	0.57	0.60	0.62	0.64

70 CRI, 2200K											
Nominal Power (Watts)		210	220	230	240	250	260	270	280	290	300
T2R	Lumens	28,443	29,445	30,425	31,364	32,275	33,186	33,742	35,060	35,935	36,733
	Lumens per Watt	133	133	132	131	129	128	125	125	124	123
	BUG Rating	B3 U0 G3	B3 U0 G3	B3 U0 G3	B3 U0 G3	B4 U0 G3	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T2U	Lumens	28,454	29,456	30,436	31,376	32,287	33,198	33,755	35,073	35,949	36,747
	Lumens per Watt	134	133	132	131	129	128	125	125	124	123
	BUG Rating	B3 U0 G3	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T3	Lumens	28,411	29,413	30,391	31,329	32,239	33,148	33,704	35,020	35,895	36,692
	Lumens per Watt	133	133	131	130	129	128	125	125	124	123
	BUG Rating	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4
T4W	Lumens	27,697	28,673	29,627	30,542	31,428	32,315	32,857	34,140	34,993	35,770
	Lumens per Watt	130	129	128	127	126	125	122	122	121	120
	BUG Rating	B3 U0 G3	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4
5WQ	Lumens	27,853	28,834	29,793	30,713	31,605	32,497	33,042	34,332	35,189	35,971
	Lumens per Watt	131	130	129	128	127	125	123	123	121	120
	BUG Rating	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G4	B5 U0 G4	B5 U0 G4

70 CRI, 2700K											
Nominal Power (Watts)		210	220	230	240	250	260	270	280	290	300
T2R	Lumens	31,369	32,474	33,554	34,591	35,595	36,599	37,213	38,666	39,631	40,512
	Lumens per Watt	147	146	145	144	143	141	138	138	137	135
	BUG Rating	B3 U0 G3	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T2U	Lumens	32,486	33,567	34,603	35,608	36,613	37,227	38,680	39,646	40,527	41,730
	Lumens per Watt	146	145	144	143	141	138	138	137	135	170
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B2 U0 G2
T3	Lumens	31,333	32,438	33,517	34,552	35,555	36,558	37,171	38,622	39,587	40,466
	Lumens per Watt	147	146	145	144	143	141	138	138	137	135
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T4W	Lumens	30,546	31,622	32,674	33,683	34,661	35,639	36,237	37,651	38,592	39,449
	Lumens per Watt	143	143	141	140	139	137	135	135	133	132
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
5WQ	Lumens	30,717	31,800	32,858	33,872	34,856	35,839	36,440	37,863	38,809	39,671
	Lumens per Watt	144	143	142	141	140	138	135	135	134	133
	BUG Rating	B5 U0 G3	B5 U0 G3	B5 U0 G3	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4

70 CRI, 3000K											
Nominal Power (Watts)		210	220	230	240	250	260	270	280	290	300
T2R	Lumens	32,506	33,652	34,771	35,845	36,886	37,926	38,562	40,068	41,069	41,981
	Lumens per Watt	153	152	150	149	148	146	143	143	142	140
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T2U	Lumens	32,518	33,665	34,784	35,858	36,900	37,941	38,577	40,083	41,084	41,997
	Lumens per Watt	153	152	150	149	148	146	143	143	142	140
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T3	Lumens	32,470	33,614	34,733	35,805	36,845	37,884	38,519	40,023	41,023	41,934
	Lumens per Watt	152	152	150	149	148	146	143	143	142	140
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T4W	Lumens	31,654	32,769	33,859	34,905	35,918	36,932	37,551	39,017	39,992	40,880
	Lumens per Watt	149	148	146	145	144	142	140	139	138	137
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
5WQ	Lumens	31,831	32,953	34,050	35,101	36,120	37,139	37,762	39,236	40,216	41,110
	Lumens per Watt	149	149	147	146	145	143	140	140	139	137
	BUG Rating	B5 U0 G3	B5 U0 G3	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4

70 CRI, 4000K											
Nominal Power (Watts)		210	220	230	240	250	260	270	280	290	300
T2R	Lumens	34,132	35,335	36,510	37,637	38,730	39,823	40,491	42,071	43,122	44,080
	Lumens per Watt	160	159	158	157	155	154	151	150	149	147
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T2U	Lumens	34,144	35,348	36,524	37,651	38,745	39,838	40,506	42,087	43,138	44,097
	Lumens per Watt	160	159	158	157	155	154	151	150	149	147
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T3	Lumens	34,093	35,295	36,469	37,595	38,687	39,778	40,445	42,024	43,074	44,031
	Lumens per Watt	160	159	158	157	155	153	150	150	149	147
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T4W	Lumens	33,236	34,408	35,552	36,650	37,714	38,778	39,429	40,968	41,991	42,924
	Lumens per Watt	156	155	154	153	151	150	147	146	145	143
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
5WQ	Lumens	33,423	34,601	35,752	36,856	37,926	38,996	39,650	41,198	42,227	43,165
	Lumens per Watt	157	156	155	153	152	150	147	147	146	144
	BUG Rating	B5 U0 G3	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4

70 CRI, 5000K											
Nominal Power (Watts)		210	220	230	240	250	260	270	280	290	300
T2R	Lumens	32,927	34,132	35,335	36,510	37,637	39,823	40,491	42,071	43,122	44,080
	Lumens per Watt	162	160	159	158	157	154	151	150	149	147
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T2U	Lumens	34,144	35,348	36,524	37,651	38,745	39,838	40,506	42,087	43,138	44,097
	Lumens per Watt	160	159	158	157	155	154	151	150	149	147
	BUG Rating	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T3	Lumens	34,093	35,295	36,469	37,595	38,687	39,778	40,445	42,024	43,074	44,031
	Lumens per Watt	160	159	158	157	155	153	150	150	149	147
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
T4W	Lumens	33,236	34,408	35,552	36,650	37,714	38,778	39,429	40,968	41,991	42,924
	Lumens per Watt	156	155	154	153	151	150	147	146	145	143
	BUG Rating	B3 U0 G4	B3 U0 G4	B3 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4	B4 U0 G4
5WQ	Lumens	33,423	34,601	35,752	36,856	37,926	38,996	39,650	41,198	42,227	43,165
	Lumens per Watt	157	156	155	153	152	150	147	147	146	144
	BUG Rating	B5 U0 G3	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4	B5 U0 G4